Note: This datasheet may be out of date.
Please download the latest datasheet of NTSD1XV103FPB50 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-us/products/productdetail?partno=NTSD1XV103FPB50

NTSD1XV103FPB50


Discontinued RoHS REACH

Applications

Unsuitable Applications	Please be sure to read and comply with these "Precautions for use."
Specific Applications	Industrial Equipment Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product.

Appearance & Shape





* NTSD1XM202/NTSD1WB203/NTSD1WC303 Types

Type	L (mm)
NTSD1_FPB30	30
NTSD1_FPB40	40
NTSD1_FPB50	50

Packaging Information

Packaging	Specifications	Standard Packing Quantity
-	Bulk(Bag)	200

Features

1. Electric insulation on lead wire
2. Excellent bending resistance due to suitable hardness of surface coating
3. Easy handling due to most suitable hardness of surface of coating
4. +/-1% of resistance and +/-0.5% of B-Constant is realized due to technical advantages of the material and manufacturing process.

Attention
1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

Note: This datasheet may be out of date.
Please download the latest datasheet of NTSD1XV103FPB50 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-us/products/productdetail?partno=NTSD1XV103FPB50

NTSD1XV103FPB50

Specifications

Resistance (25℃)	10kΩ
Resistance Value Tolerance (at 25℃)	±1%
B-Constant (25/50℃)	3900K
B-Constant (25/50℃) Tolerance	±0.5%
B-Constant(25/80℃) (Reference Value)	3930K
B-Constant(25/85℃) (Reference Value)	3934K
B-Constant(25/100℃) (Reference Value)	3944K
Maximum Operating Current (25℃)	0.12mA
Rated Electric Power (25℃)	15.0mW
Typical Dissipation Constant (25℃)	1.5mW/℃
Operating Temperature Range	-40℃ to 125℃
Thermal Time Constant	7s
Lead Shape	Insulation type
Shape	Lead
Mass	0.16g
MSL	N


Attention
1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

Note: This datasheet may be out of date.
Please download the latest datasheet of NTSD1XV103FPB50 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-us/products/productdetail?partno=NTSD1XV103FPB50

NTSD1XV103FPB50

Product Data



Temperature Tolenrance-Temperature Characteristics

Attention
1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.