CHIP FERRITE BEAD BLM21

1. Scope

This reference specification applies to chip ferrite bead BLM21_SZ series for automotive electronics based on AEC-Q200 except for power trains and safeties.

2. Part Numbering

(Ex.)		•						
BL	M	21	AG	121	S	Z	1	D
Product	Туре	Dimension	Characteristics	Impedance	Performance	Category	Numbers of	Packaging
ID		(L × W)		(Typical value at 100 MHz)			circuit	D: taping (ø180 mm reel, paper tape)
								L: taping (ø180 mm reel,
								plastic tape)

3. Part Number and Rating

Operating temperature range	-55°C to +125°C
Storage temperature range	-55°C to +125°C

Customer	Murata	Impedance (Ω) at 100 MHz		Rated current*1 (mA)		DC resistance (Ω) max.		Remark	ESD rank
Part number	Part number		Тур.	Ambient temperature 85°C	Ambient temperature 125°C	Initial values	Values after testing	Remark	2: 2 kV
	BLM21PG220SZ1D	22±25%	22	6000	3300	0.009	0.018	For DC power line	2
	BLM21PG300SZ1D	20 min.	30	4000	2300	0.014	0.028	For DC power line	2
	BLM21PG600SZ1D	60±25%	60	3500	1900	0.02	0.04	For DC power line	2
	BLM21PG121SZ1D	120±25%	120	3000	1550	0.03	0.06	For DC power line	2
	BLM21PG221SZ1D	220±25%	220	2000	1250	0.045	0.09	For DC power line	2
	BLM21PG331SZ1D	330±25%	330	1500	1000	0.07	0.14	For DC power line	2
	BLM21SN300SZ1D	30±10Ω	30	8500	6000	0.004	0.005	For DC power line	2
	BLM21SP700SZ1D	70±25%	70	6000	4000	0.009	0.012	For DC power line	2
	BLM21SP111SZ1D	110±25%	110	5000	3300	0.013	0.016	For DC power line	2
	BLM21SP181SZ1D	180±25%	180	4000	2600	0.020	0.025	For DC power line	2
	BLM21SP331SZ1D	330±25%	330	2800	1900	0.040	0.051	For DC power line	2
	BLM21SP471SZ1D	470±25%	470	2500	1700	0.050	0.063	For DC power line	2
	BLM21SP601SZ1D	600±25%	600	2300	1500	0.060	0.074	For DC power line	2
	BLM21SP102SZ1D	1000±25%	1000	1600	1100	0.120	0.144	For DC power line	2
	BLM21BB050SZ1D	5±25%	5	-	1000	0.02	0.04	For high speed signal line	2

Spec No.: JENF243A 9114H-01

Reference Only

P2/11

Customer	omer Murata		Impedance (Ω) urata at 100 MHz		Rated current ^{*1} (mA)		istance max.		ESD
Part number	Part number		Тур.	Ambient temperature 85°C	Ambient temperature 125°C	Initial values	Values after testing	Remark	rank 2: 2 k∨
	BLM21BB600SZ1D	60±25%	60	-	800	0.13	0.23	For high speed signal line	2
	BLM21BB750SZ1D	75±25%	75	-	700	0.16	0.26	For high speed signal line	2
	BLM21BB121SZ1D	120±25%	120	-	600	0.19	0.29	For high speed signal line	2
	BLM21BD121SZ1D	120±25%	120	-	350	0.25	0.35	For high speed signal line	2
	BLM21BB151SZ1D	150±25%	150	-	600	0.21	0.31	For high speed signal line	2
	BLM21BD151SZ1D	150±25%	150	-	350	0.25	0.35	For high speed signal line	2
	BLM21BB201SZ1D	200±25%	200	-	500	0.26	0.36	For high speed signal line	2
	BLM21BB221SZ1D	220±25%	220	-	500	0.26	0.36	For high speed signal line	2
	BLM21BD221SZ1D	220±25%	220	-	350	0.25	0.35	For high speed signal line	2
	BLM21BB331SZ1D	330±25%	330	-	400	0.33	0.43	For high speed signal line	2
	BLM21BD331SZ1D	330±25%	330	-	300	0.3	0.4	For high speed signal line	2
	BLM21BD421SZ1D	420±25%	420	-	300	0.3	0.4	For high speed signal line	2
	BLM21BB471SZ1D	470±25%	470	-	400	0.40	0.50	For high speed signal line	2
	BLM21BD471SZ1D	470±25%	470	-	300	0.35	0.45	For high speed signal line	2
	BLM21BD601SZ1D	600±25%	600	-	300	0.35	0.45	For high speed signal line	2
	BLM21BD751SZ1D	750±25%	750	-	250	0.4	0.5	For high speed signal line	2
	BLM21BD102SZ1D	1000±25%	1000	-	250	0.4	0.5	For high speed signal line	2
	BLM21BD152SZ1D	1500±25%	1500	-	250	0.45	0.55	For high speed signal line	2
	BLM21BD182SZ1D	1800±25%	1800	-	250	0.5	0.6	For high speed signal line	2
	BLM21BD222SZ1L	1600 min.	2250	-	250	0.6	0.7	For high speed signal line	2
	BLM21BD222TZ1D	2200±25%	2200	-	200	0.6	0.7	For high speed signal line	2
	BLM21BD272SZ1L	2700±25%	2700	-	200	0.8	0.9	For high speed signal line	2
	BLM21AG121SZ1D	120±25%	120	-	1000	0.09	0.19	For general use	2
	BLM21AG151SZ1D	150±25%	150	-	1000	0.09	0.19	For general use	2
	BLM21AG221SZ1D	220±25%	220	-	900	0.12	0.22	For general use	2


Spec No 1.	JENF243A	9114H-01
0000110		01141101

Customer	Murata	Impedance (Ω) at 100 MHz		Rated current*1 (mA)		DC resistance (Ω) max.		Remark	ESD
Part number	Part number		Тур.	Ambient temperature 85°C	Ambient temperature 125°C	Initial values	Values after testing	Reliark	rank 2: 2 k∨
	BLM21AG331SZ1D	330±25%	330	-	800	0.15	0.25	For general use	2
	BLM21AG471SZ1D	470±25%	470	-	700	0.18	0.28	For general use	2
	BLM21AG601SZ1D	600±25%	600	-	700	0.2	0.3	For general use	2
	BLM21AG102SZ1D	1000±25%	1000	-	600	0.27	0.37	For general use	2
	the diagram below, d perating temperature.		oplied to	o the rated cur	rent of the BL	M21PG,	BLM21S	N, BLM21SP se	eries
		Rated Current							

4. Testing Conditions

5	
Unless otherwise specified	Temperature: ordinary temperature (15°C to 35°C) Humidity: ordinary humidity [25% to 85% (RH)]
	Temperature: 20°C±2°C Humidity: 60% to 70% (RH) Atmospheric pressure: 86 kPa to 106 kPa

5. Appearance and Dimensions



Equivalent circuit

85

Operating Temperature (°C)

125

₩} -0 o

(Resistance element becomes dominant at high frequencies.) no polarity

Unit mass (typical value): 0.010 g 0.014 g (only BLM21BD222SZ1□/BLM21BD272SZ1□)

6. Marking

No marking.

P3/11

7. Electrical Performance

No.	Item	Specification	Test method
7.1	Impedance		Measuring equipment: Keysight 4291A or the equivalent Measuring frequency: 100 MHz±1 MHz Measuring fixture: Keysight 16192A or the equivalent
7.2	DC resistance	Meet chapter 3 ratings.	Measuring equipment: digital multimeter Substrate wiring resistance is excluded.

8. AEC-Q200 Requirement

8.1 Performance [(based on table 13 for filter EMI suppressors/filters) AEC-Q200 Rev.D issued June 1, 2010]

		AEC-Q200		N4 webs and			
No.	Stress	Test method		- Murata specification/deviation			
3	High temperature	1000 h at 125°C Set for 24 h at room condition, then		eet table A after testing. able A			
	exposure	measured.		Appearance	No damage		
				Impedance change (at 100 MHz)	Within ±30% (within ±50% for BLM21SN)		
				DC Resistance	Meet chapter 3 ratings.		
4	Temperature cycling	1000 cycles -55°C to +125°C Set for 24 h at room condition, then measured.	M	Meet table A after testing.			
5	Destructive physical analysis	Per EIA469 No electrical tests	N	o defects			
7	Biased humidity	1000 h at 85°C, 85% (RH). Apply max rated current. Set for 24 h at room condition, then measured.	M	Meet table A after testing.			
8	Operational life	Apply 125°C 1000 h Set for 24 h at room condition, then measured.	lf	Meet table A after testing. If the rated current of parts exceed 1A, the operating temperature should be 85 °C.			
9	External visual	Visual inspection	N	o abnormalities			
10	Physical dimension	Meet chapter 5, "Appearance and Dimensions".	N	o defects			
12	Resistance to solvents	Per MIL-STD-202 Method 215	N	ot applicable			
13	Mechanical shock	Per MIL-STD-202 Method 213		eet table B after testing able B			
		Condition F: 1500 g's (14.7 N), 0.5 ms, half sine		Appearance	No damage		
		1000 g S (14.7 W), 0.5 mS, nan Sine		Impedance change (at 100 MHz)	Within ±30%		
				DC Resistance	Meet chapter 3 ratings.		
14	Vibration	5 g's (0.049 N) for 20 min, 12 cycles each of 3 orientations Test from 10 Hz to 2000 Hz	М	eet table B after testing			
15	Resistance to soldering heat	No-heating Solder temperature 260°C±5°C Immersion time 10 s		Pre-heating: 150°C±10°C, 60 s to 90 s Meet table A after testing.			
17	ESD	Per AEC-Q200-002		eet table A after testing. SD rank: Refer to chapt			
18	Solderability	Per J-STD-002	M 9(ethod b: not applicable 5% of the terminations is	s to be soldered.		


Spec No.: JENF243A 9114H-01

		AEC-Q200	Murata anapiliaatian/daviatian
No.	Stress	Test method	Murata specification/deviation
19	Electrical characterization	Measured: impedance	No defects
20	Flammability	Per UL-94	Not applicable
21	Board flex	Epoxy-PCB (1.6 mm) Deflection 2 mm (min.) 60 s minimum holding time	Meet table B after testing.
22	Terminal strength	Per AEC-Q200-006	No defects
30	Electrical transient conduction	Per ISO-7637-2	Not applicable


9. Specification of Packaging

9.1 Appearance and dimensions of tape (8 mm width/paper tape)

8 mm width/paper tape(except BLM21BD222SZ1L, BLM21BD272SZ1L)



• 8 mm width/plastic tape(only BLM21BD222SZ1L, BLM21BD272SZ1L)



* The dimensions of the cavity are measured at its bottom.

9.2 Taping specifications

Packing quantity (Standard quantity)	4000 pcs/reel (except BLM21BD222SZ1L, BLM21BD272SZ1L) 3000 pcs/reel (only BLM21BD222SZ1L, BLM21BD272SZ1L)
Packing method	The products are placed in cavities of a carrier tape and sealed by a cover tape (top tape and bottom tape when the cavities of the carrier tape are punched type).
Feed hole position	The feed holes on the carrier tape are on the right side when the cover tape (top tape when the cavities of the carrier tape are punched type) is pulled toward the user.
Joint	The carrier tape and cover tape (top tape when the cavities of the carrier tape are punched type) are seamless.
Number of missing products	Number of missing products within 0.025% of the number per reel or 1 pc., whichever is greater, and are not continuous. The specified quantity per reel is kept.


P5/11

9.3 Break down force of tape

C	Covertene (ortentene)	Applied to paper carrier tape	5 N min.
	Cover tape (or top tape)	Applied to Plastic carrier tape	10 N min.
	Bottom tape (only when the cavities of the c	arrier tape are punched type)	5 N min.


9.4 Peeling off force of tape

Speed of peeling off	300 mm/min
Peeling off force	Paper tape: 0.1 N to 0.6 N (The lower limit is for typical value.)
	Plastic tape: 0.2 N to 0.7 N (The lower limit is for typical value.)
	cover tape (or top tape)



9.5 Dimensions of leader section, trailer section and reel

A vacant section is provided in the leader (start) section and trailer (end) section of the tape for the product. The leader section is further provided with an area consisting only of the cover tape (or top tape). (See the diagram below.)



9.6 Marking for reel

Customer part number, Murata part number, inspection number (*1), RoHS marking (*2), quantity, etc.

*1 Expres	sion of insp 0000 (2)	$\frac{\diamond \diamond \diamond}{(3)}$	 (1) Factory code (2) Date First digit: year/last digit of year Second digit: month/Jan. to Sep.→1 to 9, Oct. to Dec.→O, N, D Third, Fourth digit: day (3) Serial No.
*2 Expres ROHS		HS marking: (△) (2)	(1) RoHS regulation conformity(2) Murata classification number


9.7 Marking on outer box (corrugated box)

Customer name, purchasing order number, customer part number, Murata part number, RoHS marking (*2), quantity, etc.

Spec No.: JENF243A 9114H-01

Reference Only





Dimensions of outer box (mm)			Standard reel quantity
W	D	Н	in outer box (reel)
186	186	93	5
* Above outer box size is typical. It depends on a quantity of an order.			

10. ACaution

10.1 Restricted applications

Please contact us before using our products for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property.

	(2) Aerospace equipment	equipment	control equipment
(5) Medical equipment	(6) Transportation equipment (trains, ships, etc.)	(7) Traffic signal equipment	(8) Disaster/crime prevention equipment
(9) Data-processing equipment	(10) Applications of similar cor reliability requirements to the the above		

10.2 Precautions on rating

Avoid using in exceeded the rated temperature range, rated voltage, or rated current. Usage when the ratings are exceeded could lead to wire breakage, burning, or other serious fault.

10.3 Fail-safe

Be sure to provide an appropriate fail-safe function on your product to prevent a second damage that may be caused by the abnormal function or the failure of our product.

10.4 Inrush current

If an inrush current (or pulse current or rush current) that significantly exceeds the rated current is applied to the product, overheating could occur, resulting in wire breakage, burning, or other serious fault.

10.5 Corrosive gas

Please refrain from use since contact with environments with corrosive gases (sulfur gas [hydrogen sulfide, sulfur dioxide, etc.], chlorine, ammonia, etc.) or oils (cutting oil, silicone oil, etc.) that have come into contact with the previously stated corrosive gas environment will result in deterioration of product quality or an open from deterioration due to corrosion of product electrode, etc. We will not bear any responsibility for use under these environments.

11. Precautions for Use


This product is designed to be mounted by soldering. If you want to use other mounting method, for example, using a conductive adhesive, please consult us beforehand.

Also, if repeatedly subjected to temperature cycles or other thermal stress, due to the difference in the coefficient of thermal expansion with the mounting substrate, the solder (solder fillet part) in the mounting part may crack.

The occurrence of cracks due to thermal stress is affected by the size of the land where mounted, the solder volume, and the heat dissipation of the mounting substrate. Carefully design it when a large change in ambient temperature is assumed.

11.1 Land dimensions


The following diagram shows the recommended land dimensions for flow and reflow soldering: <Applied to types excluding BLM21PG, BLM21S□ types>



Spec No.: JENF243A 9114H-01

Reference Only

<Applied to BLM21PG, BLM21S types>



	Flo	w	Reflov	V			
а	1.1	1	1.2				
b	3.5	5	2.4				
С	0.9	5	1.25				
				(in n	nm)		
Ту	Туре		Rated current		Patt	ern thickness dimension d	
-	•		(A)		8 µm	35 µm	70 µm
BLM:	21PG		to 2		1.25	1.25	1.25
BLM:	21PG	3	3 to 4		2.4	1.25	1.25
BLM:	LM21PG		6		6.4	3.3	1.65
BLM2	BLM21S		1 to 8.5		-	6.8	3.4
						please pay a s may deterio	
							(in m

(in mm)

11.2 Flux and solder used

 Use a rosin-based flux. Do not use a highly acidic flux with a halide content exceeding 0.2(wt)% (chlorine conversion value). Do not use a water-soluble flux.
 Use Sn-3.0Ag-0.5Cu solder. Standard thickness of solder paste: 100 μm to 200 μm

If you want to use a flux other than the above, please consult our technical department.


11.3 Soldering conditions (flow, reflow)

 Pre-heating should be in such a way that the temperature difference between solder and product surface is limited to 150°C max.

Cooling into solvent after soldering also should be in such a way that the temperature difference is limited to 100°C max. Insufficient pre-heating may cause cracks on the product, resulting in the deterioration of product quality. • Standard soldering profile and the limit soldering profile is as follows.

The excessive limit soldering conditions may cause leaching of the electrode and/or resulting in the deterioration of product quality.


(1) Flow



	Standard profile	Limit profile
Pre-heating	150°C/60 s min.	150°C/60 s min.
Heating	250°C/4 s to 6 s	265°C±3°C/5 s
Number of flow cycles	2 times	2 times

Spec No.: JENF243A 9114H-01

(2) Reflow



	Standard profile	Limit profile
Pre-heating	150°C to 180°C/90 s±30 s	150°C to 180°C/90 s±30 s
Heating	Above 220°C/30 s to 60 s	Above 230°C/60 s max.
Peak temperature	245°C±3°C	260°C/10 s
Number of reflow cycles	2 times	2 times

11.4 Reworking with soldering iron


The following requirements must be met to rework a soldered product using a soldering iron.

Item	Requirement	
Pre-heating	150°C/approx. 1 min	
Tip temperature of soldering iron	350°C max.	
Power consumption of soldering iron	80 W max.	
Tip diameter of soldering iron	ø3 mm max.	
Soldering time	3 s (+1 s, -0 s)	
Number of reworking operations	2 times max.	
* Avoid a direct contact of the tip of the soldering iron with the product. Such a		

direction contact may cause cracks in the ceramic body due to thermal shock.

11.5 Solder volume

Solder shall be used not to be exceeded the upper limits as shown below.



An increased solder volume increases mechanical stress on the product. Exceeding solder volume may cause the failure of mechanical or electrical performance.

11.6 Product's location

The following shall be considered when designing and laying out PCBs.

(1) PCB shall be designed so that products are not subject to mechanical stress due to warping the board.

[Products direction]

Products shall be located in the sideways direction (length: a < b) to the mechanical stress.

(Poor example) (Good example)



MURATA MFG CO., LTD

Spec No.: JENF243A 9114H-01


(2) Components location on PCB separation

It is effective to implement the following measures, to reduce stress in separating the board.

It is best to implement all of the following three measures; however, implement as many measures as possible to reduce stress.

Contents of measures	Stress level	
 Turn the mounting direction of the component parallel to the board separation surface. 	A > D*1	
(2) Add slits in the board separation part.	A > B	
(3) Keep the mounting position of the component away from the board separation surface.	A > C	
*1 A > D is valid when stress is added vertically to the perforation as with hand separation.		


If a cutting disc is used, stress will be diagonal to the PCB, therefore A > D is invalid.



(3) Mounting components near screw holes

When a component is mounted near a screw hole, it may be affected by the board deflection that occurs during the tightening of the screw.

Mount the component in a position as far away from the screw holes as possible.



11.7 Handling of substrate

After mounting products on a substrate, do not apply any stress to the product caused by bending or twisting to the substrate when cropping the substrate, inserting and removing a connector from the substrate or tightening screw to the substrate. Excessive mechanical stress may cause cracking in the product.



Bending

Twisting

11.8 Cleaning

Excessive ultrasonic oscillation during cleaning can cause the PCBs to resonate, resulting in cracked chips or broken solder joints. Before starting your production process, test your cleaning equipment / process to insure it does not degrade this product.

11.9 Storage and transportation

Storage period	Use the product within 6 months after delivery. If you do not use the product for more than 6 months, check solderability before using it.
Storage conditions	 The products shall be stored in a room not subject to rapid changes in temperature and humidity. The recommended temperature range is -10°C to +40°C. The recommended relative humidity range is 15% to 85%. Keeping the product in corrosive gases, such as sulfur, chlorine gas or acid may cause the poor solderability. Do not place the products directly on the floor; they should be placed on a palette so that they are not affected by humidity or dust. Avoid keeping the products in a place exposed to direct sunlight, heat or vibration. Do not keep products in bulk packaging. Bulk storage could result in collisions between the products or between the products and other parts, resulting in chipping or wire breakage. Avoid storing the product by itself bare (i.e. exposed directly to air).
Transportation	Excessive vibration and impact reduces the reliability of the products. Exercise caution when handling the products.

11.10 Resin coating (including moisture-proof coating)

When the product is coated/molded with resin, its electrical characteristics may change.

A wire breakage issue may occur by mechanical stress caused by the resin, amount/cured shape of resin, or operating condition etc.

Some resins contain impurities or hydrolyzable chlorine, which could result in corrosion of the conducting materials, leading to wire breakage.

So, please pay your careful attention when you select resin in case of coating/molding the products with the resin. Prior to use the coating resin, please make sure no reliability issue is observed by evaluating products mounted on your board.

11.11 Mounting conditions

Check the mounting condition before using.

Using mounting conditions (nozzles, equipment conditions, etc.) that are not suitable for products may lead to pick up errors, misalignment, or damage to the product.

11.12 Operating environment

Do not use this product under the following environmental conditions as it may cause deterioration of product quality.

- (1) In the corrodible atmosphere such as acidic gases, alkaline gases, chlorine, sulfur gases, organic gases and etc. (the sea breeze, Cl2, H2S, NH3, SO2, NO2, etc)
- (2) In the atmosphere where liquid such as organic solvent, may splash on the products.
- (3) In the atmosphere where the temperature/humidity changes rapidly and it is easy to dew.

11.13 Mounting density

If this product is placed near heat-generating products, be sure to implement sufficient heat-dissipating measures. If this product is subjected to a significant amount of heat from other products, this could adversely affect product quality, resulting in a circuit malfunction or failure of the mounted section. Also, be sure that the product is used in a manner so that the heat that the product is subjected to from other products does not exceed the upper limit of the rated operating temperature for the product.

12. **A**Note

- (1)Please make sure that your product has been evaluated in view of your specifications with our product being mounted to your product.
- (2)You are requested not to use our product deviating from the reference specifications.
- (3)The contents of this reference specification are subject to change without advance notice.
 - Please approve our product specifications or transact the approval sheet for product specifications before ordering.