


Datasheet of SAW Device

SAW Dual Filter for Band34_Band39 / 1in2out Unbalanced / LH /1511

Murata PN: SAWFD1G90KE0F0A

Feature
Low Insertion Loss



Note : This Murata SAW Component is Consumer grade product and applicable for Cellular phone or similar end devices. Please also read Important Notice at the end of this document.


_	Revision
F	F



General Information

- Operating temperature	: -20 to +85 deg.C							
- Storage temperature	: -40 to +85 deg.C							
- Input Power	: +13 dBm 2000 h							
- D.C. Volatage between the terminals	: 3V (25+/-2 deg.C)							
- Minimum Resistance between the terminals	: 10M ohm							
- RoHS compliance	: Yes							
- ESD (ElectroStatic Discharge) sensitive device								







Electrical Characteristic < Low Freq. Filter >

	aciei	1311							1
						racteri	stics		
Low Freq. Filter						(-20 to +85 deg.C)		Unit	Note
					min.	typ.*	max.		
Center Frequency						1900		MHz	
Insertion Loss	1880.	to	1920.	MHz		1.6	2.1	dB	
Ripple Deviation	1880.	to	1920.	MHz		0.5	1.0	dB	
VSWR	1880.	to	1920.	MHz		1.3	1.8		
Absolute Attenuation	10.	to	1710.	MHz	36	40		dB	
	1710.	to	1785.	MHz	40	45		dB	
	1795.	to	1820.	MHz	37	42		dB	
	1820.	to	1850.	MHz	37	42		dB	
	1950.	to	1980.	MHz	8.0	19.0		dB	
	1980.	to	2025.	MHz	36	40		dB	
	2025.	to	6000.	MHz	30	33		dB	
	2400.	to	2500.	MHz	42	47		dB	
	4900.	to	5950.	MHz	30	33		dB	
	5640.	to	5760.	MHz	30	34		dB	
	7520.	to	7680.	MHz	30	34		dB	
	9400.	to	9600.	MHz	20	26		dB	
	11280.	to	11520.	MHz	17	23		dB	
	6000.	to	12750.	MHz	15	21		dB	
1									
1						İ			
1									
1									
1									
1						İ			
1									
1									
1						İ			
1									
1									
1									
1									
L	1				I		1		* Typical value at 25+2deg C

* Typical value at 25±2deg.C




Electrical Characteristic < High Freq. Filter >

Characteristics Note Center Frequency min. VP.* max. MHz Note Center Frequency 2010. 0.2025. MHz 118 2.3 dB MHz dB dB dB dB dB dB dB dB dB dB dB dB dB dB dB dB dB dB dB dB dB dB dB dB dB dB		acter	າວແບ	, `	підп				-	
Instrum Instrum Instrum Instrum Instrum Center Enquency 2010 0 2025 MHz 1				Characteristics				N. /		
Center Frequency 2017 5 MHz Ripple Deviation 2010 10 2025 MHz 0.4 0.8 dB Ripple Deviation 2010 10 2025 MHz 0.4 0.8 dB Absolute Attenuation 10 10 1265 MHz 14 18 me 100 10 1925 MHz 14 18 me me 1100 10 1925 MHz 14 48 dB me me 1125 10 1980 MHz 14 48 dB me	High	Freq. Filt	ter						Unit	Note
Insertion Loss 2010 to 2025 MHz 1.9 2.3 dB Ripple Devide 2010 to 2025 MHz 1.4 1.8 0.4 0.8 dB VSWR 2010 to 2025 MHz 1.4 1.8 0.8 dB Common state VSWR 2010 to 2025 MHz 1.4 1.8 0.8 GSM1800 Tx 0.8 1710 to 1785 MHz 4.1 4.5 0.8 GSM1800 Tx 0.8 2050 to 2036 to 1.4 4.4 5.0 dB ISMSG 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6						mın.		max.		
Ripple Deviation 2010 to 2025 MHz 14 1.8 Absolute Attenuation 10 to 1255 MHz 14 1.8 Absolute Attenuation 10 to 1255 MHz 14 1.4 1.8 205 to 1385 MHz 14 1.4 1.8 205 to 1385 MHz 14 1.5 dB GSM1800 Tx 205 to 110 to 10000 MHz 34 38 dB 2010 to 2500 MHz 42 44 dB ISMSG 2035 to 2100 MHz 14 14 dB ISMSG 2040 to 2500 MHz 12 17 dB ISMSG 2030 to 10125 MHz 10 14 dB ISMSG 10050 to 12750 MHz 10 14 dB ISM	Center Frequency									
VŠWR 2010 to 2025 MHz 1 1.8 Absolute Attenuation 10 1925 MHz 37 41 dB GSM1800 Tx 1710 to 1785 MHz 41 45 dB GSM1800 Tx 1250 to 1286 MHz 41 45 dB GSM1800 Tx 2050 to 2085 MHz 40 18.0 dB 1200 2050 to 2085 MHz 40 18.0 dB 1200 1200 1200 1200 1200 14 48 38 dB 140 14 <td< td=""><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></td<>										
Absolute Attenuation 10. to 1925. MH2 37. 41. dB GSM1800 Tx 1925. to 1980. MH2 11 225. dB GSM1800 Tx 1925. to 1980. MH2 11 225. dB GSM1800 Tx 1925. to 1980. MH2 41. 48. dB CSM1800 Tx 2005. to 2100. MH2 44. 38. dB CSM1800 Tx 2006. to 2100. MH2 42. 46. dB ISM24G 4000. 0 550. MH2 42. 46. dB ISM24G 6030. to 10125. MH2 10. 14. 48. dB dB 10050. to 10125. MH2 10. 14. 48. dB dB<	Ripple Deviation								dB	
1710 to 1785 MH2 41 45 dB GSM1800 Tx 1925 to 2085 MH2 40 180 dB 2085 to 2010 MH2 43 38 dB 2085 to 2010 MH2 34 39 dB 2010 to 6030 MH2 44 50 dB ISM243 2000 to 5500 MH2 44 50 dB ISM54 6030 to 6075 MH2 45 52 dB 10050 to 10125 MH2 10 14 dB 10050 to 10125 MH2 10 14 dB 10050 to 12750 MH2 10 14 dB 10050 to 12750 MH2 10 14 dB 10050 to 12750 MH2 10 14 dB 10050 to 12750 MH2 10 14 dB 10050 to to to to to 10050 to to to to to 10050 <td></td> <td></td> <td></td> <td></td> <td></td> <td>07</td> <td></td> <td>1.8</td> <td>-15</td> <td></td>						07		1.8	-15	
1925. io 1980. MHz 11 25 4B 2056. io 2110. MHz 34 38 4B 2110. io 5000. MHz 34 39 4B 2400. io 2500. MHz 42 46 4B ISM24G 4900. io 5500. MHz 42 46 4B ISM26G 6030. io 6075. MHz 14 45 52 4B ISM26G 6030. io 6075. MHz 12 17 4B ISM26G ISM26G 6000. io 10125. MHz 12 17 4B ISM26G ISM36G 6000. io 12150. MHz 12 17 4B ISM26G ISM36G 6000. io 12150. MHz 10 14 4B ISM26G ISM36G 6000. io 12150. MHz 10 14 ISM2 ISM36G ISM36G 6000. io 12150. MHz 10 ISM36G ISM36G ISM36G ISM36G ISM36G <	Absolute Attenuation				MHZ					00144000 T.
2050. 10. 2045. MHz 34 38 48 2110. 10. 6000. MHz 34 38 48 2400. 10. 2500. MHz 42 46 18 ISM24G 4000. 10. 5950. MHz 44 50 48 ISM5G 6030. 10. 6950. MHz 24 46 52 48 8040. 10. 8100. MHz 28 35 48 10 10550. 10. 14. 10 14 48 10 14 10260. 10. 12750. MHz 10 14 48 10 10260. 10. 12750. MHz 10 14 18 14 10 12750. MHz 10 14 18 14 14 10 12750. MHz 10 14 14 14 14 10 12750. MHz 10 14 14 14 14 14										GSM1800 IX
2085. 10. 2410. <										
2110. 10. 6000. MH2 34 39 dB 2400. 10. 5900. MH2 44 50 dB ISM5G 6030. 10. 6075. MH2 24 52 dB ISM5G 8040. 10. 8100. MH2 28 35 dB ISM5G 10050. 10.12150. MH2 10 14 dB ISM5G 12080. 10.12150. MH2 12 17 dB ISM5G 6000. 10.12150. MH2 12 17 dB ISM5G 6000. 10.12150. MH2 10 14 dB ISM5G 6000. 10.12150. MH2 10 ISM5G ISM5G ISM5G 6000. 10.12150. ISM5G										
2400 to 2500 MHz 44 50 dB ISM2.4G 6030 to 8075 MHz 45 52 dB 8040 to 8076 MHz 28 35 dB 10050 to 10125 MHz 10 14 dB 12060 to 12150 MHz 12 17 dB 8000 to 12750 MHz 10 14 dB 8000 to 12750 MHz 10 14 dB 8000 to 12750 MHz 10 14 dB 8000 to 12750 MHz 10 14 8000 to 12750 MHz 10 14 8000 to 12750 MHz 10 14 8000 to 12 12							30			
4900. to 5950. MHz 44 50 dB Image: strain										ISM2.4G
6030 10 MHz 45 52 dB 3040 to 100 MHz 28 35 dB 10050 to 10125 MHz 10 14 dB 12080 to 12150 MHz 12 17 dB 6000 to 12150 MHz 12 17 dB 6000 to 12750 MHz 12 14 dB 6000 to 12750 MHz 10 14 dB 6000 to 12750 MHz 10 14 dB 6000 to 10 14 dB 10 10 6000 to 10 14 dB 10 10 6000 to 10 10 10 10 10 6000 to 10 10 10 10 10 7 10 10 10 10<										
8040 io 8100. MHz 28 35 dB 10265 to 12150. MHz 12 17 dB 8000. to 12150. MHz 10 14 dB 8000. to 12750. MHz 10 14 dB 9000. to 10 14 dB 10 10 9000. to 10 10 10 10 10 10 9000. 10					MHz					101100
10050. 10 1025. MHz 12 17 dB 6000. 10 12750. MHz 10 14 dB			to		MHz					
12060. 12150. MHz 12 17 4B 6000. 10 12750. MHz 10 14 dB										
6000. 10 12750. MHz 10 14 dB										<u> </u>
				12750.						
										<u> </u>
Image: Problem intermediateImage:										
Image: state of the state of										
Image: state of the state of										
Image: Problem intermediate										
Image: Section of the section of th										
Image: state of the state of										
Image: Section of the section of th										
Image: Section of the section of th										
Image: state of the state of										
Image: state of the state of										
Image: state of the state of										
Image: state of the state of										
Image: state of the state of										
Image: state of the state of										
Image: state of the state of										
Image: state of the state of										
Image: set of the										
Image: sector of the sector										
Image: set of the						-				<u> </u>
Image: second						-				
										<u> </u>
										1
Image: state of the state										
Image: state of the state										
Image: state of the state										
Image: state of the state										
Image: Sector of the sector										
Image: Second second										
										ļ


* Typical value at 25±2deg.C



Electrical Characteristic




< Low Freq. Filter >






Electrical Characteristic











Dimensions of Tape & Reel unit: mm


Carrier Tape



Tape



Reel





Important Notice (1/2)

PLEASE READ THIS NOTICE BEFORE USING OUR PRODUCTS.

Please make sure that your product has been evaluated and confirmed from the aspect of the fitness for the specifications of our product specified in the front page of this product specifications (the "Product" or "Products") when our Product is mounted to your product. All the items and parameters in this product specification/datasheet/catalog have been prescribed on the premise that our Product is used for the purpose, under the condition and in the environment specified in this specification. You are requested not to use our Product deviating from the condition and the environment specified in this specification.

Please note that the only warranty that we provide regarding the Product is its conformance to the specifications provided herein. Accordingly, we shall not be responsible for any defects in products or equipment incorporating such Products, which are caused under the conditions other than those specified in this specification.

WE HEREBY DISCLAIMS ALL OTHER WARRANTIES REGARDING THE PRODUCTS, EXPRESS OR IMPLIED, INCLUDING WITHOUT LIMITATION ANY WARRANTY OF FITNESS FOR A PARTICULAR PURPOSE, THAT THEY ARE DEFECT-FREE, OR AGAINST INFRINGEMENT OF INTELLECTUAL PROPERTY RIGHTS.

The Product shall not be used for any application which requires especially high reliability or accuracy in order to prevent defect which incurs high possibility of damage to the third party's life, body or property such as the applications listed below as item (a) to (j) (the "Prohibited Application"). You acknowledge and agree that, if you use our Products in the Prohibited Applications, we will not be responsible for any damage caused by such use.

Furthermore, YOU AGREE TO INDEMNIFY AND DEFEND US AND OUR AFFILIATES AGAINST ALL CLAIMS, DAMAGES, COSTS, AND EXPENSES THAT MAY BE INCURRED, INCLUDING WITHOUT LIMITATION, ATTORNEY FEES AND COSTS, DUE TO THE USE OF OUR PRODUCTS IN THE PROHIBITED APPLICATIONS.

- (a) Aircraft equipment.
- (b) Aerospace equipment
- (c) Undersea equipment.
- (d) Power plant control equipment
- (e) Medical equipment.
- (f) Transportation equipment (vehicles, automotive, trains, ships, etc.).
- (g)Traffic signal equipment.
- (h)Disaster prevention / crime prevention equipment.
- (i) Burning / explosion control equipment
- (j) Application of similar complexity and/ or reliability requirements to the applications listed in the above.

For the avoidance of doubt, the Product is not automotive grade, and will not support such requests for automotive as below, also not support other specific requests for automotive.

- AEC-Q200
- PPAP
- IATF16949,VDA6.3
- Zero Defect program
- Long product life cycle
- Automotive 8D failure analysis and report



Important Notice (2/2)

We expressly prohibit you from analyzing, breaking, Reverse-Engineering, remodeling altering, and reproducing our product. Our product cannot be used for the product which is prohibited from being manufactured, used, and sold by the regulations and laws in the world.

Please do not use the Product in molding condition.

This product is ESD (ElectroStatic Discharge) sensitive device. When you install or measure this, you should be careful not to add antistatic electricity or high voltage. Please be advised that you had better check anti serge voltage.

We do not warrant or represent that any license, either express or implied, is granted under any our patent right, copyright, mask work right, or our other intellectual property right relating to any combination, machine, or process in which our Products or services are used. Information provided by us regarding third-party products or services does not constitute a license from us to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from us under our patents or other intellectual property.

Please do not use our Products, our technical information and other data provided by us for the purpose of developing of mass-destruction weapons and the purpose of military use. Moreover, you must comply with "foreign exchange and foreign trade law", the "U.S. export administration regulations", etc.

Please note that we may discontinue the manufacture of our products, due to reasons such as end of supply of materials and/or components from our suppliers.

Customer acknowledges that Murata will, if requested by you, conduct a failure analysis for defect or alleged defect of Products only at the level required for consumer grade Products, and thus such analysis may not always be available or be in accordance with your request (for example, in cases where the defect was caused by components in Products supplied to Murata from a third party).

The Product shall not be used in any other application/model than that of claimed to Murata.

Customer acknowledges that engineering samples may deviate from specifications and may contain defects due to their development status.

We reject any liability or product warranty for engineering samples.

In particular we disclaim liability for damages caused by

•the use of the engineering sample other than for evaluation purposes, particularly the installation or integration in the Product to be sold by you,

·deviation or lapse in function of engineering sample,

• improper use of engineering samples.

We disclaim any liability for consequential and incidental damages. If you can't agree the above contents, you should inquire our sales.