

Datasheet of SAW Device

SAW Duplexer

for Band11 / Unbalanced / LR /1814

Murata PN: SAYEY1G43BA0F0A

■ Feature > LTE-A



Note : This Murata SAW Component is Consumer grade product and applicable for Cellular phone or similar end devices. Please also read Important Notice at the end of this document.

F




- Operating temperature : -30 to +85 deg.C
- Storage temperature : -40 to +85 deg.C
- Input Power : +29 dBm 5000 h +55 deg.C
- D.C. Volatage between the terminals : 3V (25+/-2 deg.C)
- Minimum Resistance between the terminals : 10M ohm
- RoHS compliance
- ESD (ElectroStatic Discharge) sensitive device

The input power shall be applied to Tx-port within own Tx passband frequency range.

: Yes









Electrical Characteristic < TX→ANT. >

$TX \to ANT.$					aracteris to +85 de		Unit	Note	
				min.	typ.*	max.	•••••		
Center Frequency						1437.9		MHz	
Insertion Loss	1427.9	to	1447.9	MHz		1.3	1.8	dB	
Ripple Deviation	1427.9	to	1447.9	MHz		0.4	1.2	dB	
VŚWR	1427.9	to	1447.9	MHz		1.3	1.8		Ant.
		to	1447.9	MHz		1.2	1.8		TX
Absolute Attenuation	10.	to	1390.	MHz	29	34		dB	
		to	1409.	MHz	3.0	13.0		dB	
		to	830.	MHz	34	39		dB	B18 Tx CA
	859.	to	894.	MHz	33	38		dB	B26
		to	960.	MHz	33	38		dB	B8
		to	1495.9	MHz	46	59		dB	B11 Rx
	1559.	to	1563.	MHz	38	44 43		dB	COMPASS
	1565.42 1573.37	to	1573.38		38 38	43		dB	Lower-side GPS
	1573.37	<u>to</u>	1577.47 1585.42		38	43		dB dB	Regular GPS
	1597.55	10 to	1605.89		38	43		dB dB	Uppe-sider GPS GLONASS
		to	1680.	MHz	38	43		dB	
		to	1879.9	MHz	35	43		dB	B9
		to	1919.6	MHz	35	41		dB	
	2010.	to	2025.	MHz	33	39		dB	B34
	2110.	to	2170.	MHz	30	37		dB	B1 RX
	2400.	to	2484.	MHz	27	32		dB	ISM2.4G
		to	2905.8	MHz	24	29		dB	2f
		to	4358.7	MHz	20	27		dB	3f
	4900.	to	5950.	MHz	8.0	14.0		dB	ISM 5G
	5671.	to	5832.	MHz	8.0	14.0		dB	WLAN co-ex
	-								
	-								
									1
									1
	<u> </u>								1

* Typical value at 25±2deg.C



Electrical Characteristic < ANT. → RX >

Center Frequency	IT. \rightarrow RX					aracteris	SUCS		
		ANT. \rightarrow RX				Characteristics (-30 to +85 deg.C)			Note
					min.	typ.*	max.		
luce entire a la ce :						1485.9		MHz	
Insertion Loss	1475.9	to	1495.9	MHz		1.7	2.0	dB	
Ripple Deviation	1475.9	to	1495.9	MHz		0.3	1.2	dB	
VŚWR	1475.9	to	1495.9	MHz		1.6	2.0		ANT.
	1475.9	to	1495.9	MHz		1.5	2.0		RX
Absolute Attenuation	10.	to	1427.9	MHz	32	43		dB	
			48.	MHz	50	96		dB	RX - TX
	814.	to	849.	MHz	40	49		dB	B26 Tx CA
	880.	to	915.	MHz	40	49		dB	B8 Tx CA
	1427.9	to	1447.9	MHz	45	61		dB	ТХ
	1452.	to	1460.	MHz	5.0	22.0		dB	(RX + TX) / 2
	1581.	to	6000.	MHz	35	45		dB	
	1920.	to	1980.	MHz	40	49		dB	B1 TX CA
	2400.	to	2500.	MHz	45	56		dB	ISM2.4
	4427.7	to	4487.7	MHz	45	57		dB	3f
	4900.	to	5950.	MHz	40	49		dB	ISM 5G
	7380.	to	7480.	MHz	30	46		dB	5f
	8855.	to	8975.	MHz	25	31		dB	6f
	10331.	to	10471.	MHz	10	16		dB	7f
	11807.	to	11967.	MHz	8.0	15.0		dB	8f
	6000.	to	12750.	MHz	8.0	15.0		dB	
ŀ									
					1		1		1

* Typical value at 25±2deg.C




Electrical Characteristic $< TX \rightarrow RX. >$


	$TX \to RX$	$X \rightarrow RX$			stics eg.C)	Unit	Note
				typ.*			
solation	1427.9 to 14	47.9 MHz	55	65		dB	ТХ
Solation		95.9 MHz		62		dB	RX
	1574. to 15	77. MHz	40	64		dB	GPS
		05.8 MHz	40	54		dB	2f
	4283.7 to 43	58.7 MHz		50		dB	3f
	4200.7 [0 40					40	
			1				
			1	<u> </u>			
			1				
			1	<u> </u>			
			1				
				<u> </u>			
				L			
				L			
						ļ	
				<u> </u>			
				ļ			
			1				


* Typical value at 25±2deg.C



Electrical Characteristic











Electrical Characteristic












Electrical Characteristic











Dimensions of Tape & Reel unit: mm


Carrier Tape



Tape



Reel





Important Notice (1/2)

PLEASE READ THIS NOTICE BEFORE USING OUR PRODUCTS.

Please make sure that your product has been evaluated and confirmed from the aspect of the fitness for the specifications of our product specified in the front page of this product specifications (the "Product" or "Products") when our Product is mounted to your product. All the items and parameters in this product specification/datasheet/catalog have been prescribed on the premise that our Product is used for the purpose, under the condition and in the environment specified in this specification. You are requested not to use our Product deviating from the condition and the environment specified in this specification.

Please note that the only warranty that we provide regarding the Product is its conformance to the specifications provided herein. Accordingly, we shall not be responsible for any defects in products or equipment incorporating such Products, which are caused under the conditions other than those specified in this specification.

WE HEREBY DISCLAIMS ALL OTHER WARRANTIES REGARDING THE PRODUCTS, EXPRESS OR IMPLIED, INCLUDING WITHOUT LIMITATION ANY WARRANTY OF FITNESS FOR A PARTICULAR PURPOSE, THAT THEY ARE DEFECT-FREE, OR AGAINST INFRINGEMENT OF INTELLECTUAL PROPERTY RIGHTS.

The Product shall not be used for any application which requires especially high reliability or accuracy in order to prevent defect which incurs high possibility of damage to the third party's life, body or property such as the applications listed below as item (a) to (j) (the "Prohibited Application"). You acknowledge and agree that, if you use our Products in the Prohibited Applications, we will not be responsible for any damage caused by such use.

Furthermore, YOU AGREE TO INDEMNIFY AND DEFEND US AND OUR AFFILIATES AGAINST ALL CLAIMS, DAMAGES, COSTS, AND EXPENSES THAT MAY BE INCURRED, INCLUDING WITHOUT LIMITATION, ATTORNEY FEES AND COSTS, DUE TO THE USE OF OUR PRODUCTS IN THE PROHIBITED APPLICATIONS.

- (a) Aircraft equipment.
- (b) Aerospace equipment
- (c) Undersea equipment.
- (d) Power plant control equipment -
- (e) Medical equipment.
- (f) Transportation equipment (vehicles, automotive, trains, ships, etc.).
- (g)Traffic signal equipment.
- (h)Disaster prevention / crime prevention equipment.
- (i) Burning / explosion control equipment
- (j) Application of similar complexity and/ or reliability requirements to the applications listed in the above.

For the avoidance of doubt, the Product is not automotive grade, and will not support such requests for automotive as below, also not support other specific requests for automotive.

- AEC-Q200

- PPAP
- IATF16949,VDA6.3
- Zero Defect program
- Long product life cycle
- Automotive 8D failure analysis and report



Important Notice (2/2)

We expressly prohibit you from analyzing, breaking, Reverse-Engineering, remodeling altering, and reproducing our product. Our product cannot be used for the product which is prohibited from being manufactured, used, and sold by the regulations and laws in the world.

Please do not use the Product in molding condition.

This product is ESD (ElectroStatic Discharge) sensitive device. When you install or measure this, you should be careful not to add antistatic electricity or high voltage. Please be advised that you had better check anti serge voltage.

We do not warrant or represent that any license, either express or implied, is granted under any our patent right, copyright, mask work right, or our other intellectual property right relating to any combination, machine, or process in which our Products or services are used. Information provided by us regarding third-party products or services does not constitute a license from us to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from us under our patents or other intellectual property.

Please do not use our Products, our technical information and other data provided by us for the purpose of developing of mass-destruction weapons and the purpose of military use. Moreover, you must comply with "foreign exchange and foreign trade law", the "U.S. export administration regulations", etc.

Please note that we may discontinue the manufacture of our products, due to reasons such as end of supply of materials and/or components from our suppliers.

Customer acknowledges that Murata will, if requested by you, conduct a failure analysis for defect or alleged defect of Products only at the level required for consumer grade Products, and thus such analysis may not always be available or be in accordance with your request (for example, in cases where the defect was caused by components in Products supplied to Murata from a third party).

The Product shall not be used in any other application/model than that of claimed to Murata.

Customer acknowledges that engineering samples may deviate from specifications and may contain defects due to their development status.

We reject any liability or product warranty for engineering samples.

In particular we disclaim liability for damages caused by

•the use of the engineering sample other than for evaluation purposes, particularly the installation or integration in the Product to be sold by you,

·deviation or lapse in function of engineering sample,

• improper use of engineering samples.

We disclaim any liability for consequential and incidental damages. If you can't agree the above contents, you should inquire our sales.