

Datasheet of SAW Device


SAW Duplexer

for Band8 / Unbalanced / LR /1814

Murata PN: SAYEY897MBA0B0A

Feature

- > LTE-A
- ➤ Low Insertion Loss & High Isolation
- > TC-SAW



Note: This Murata SAW Component is Consumer grade product and applicable for Cellular phone or similar end devices.

Please also read Important Notice at the end of this document.

Revision G



General Information

Operating temperatureStorage temperature: -20 to +85 deg.C: -40 to +85 deg.C

- Input Power : +29 dBm 5000 h +55 deg.C

- D.C. Volatage between the terminals : 3V (25+/-2 deg.C)

Minimum Resistance between the terminals : 10M ohm
 RoHS compliance : Yes
 ESD (ElectroStatic Discharge) sensitive device


The input power shall be applied to Tx-port within own Tx passband frequency range.



Package Dimensions & Recommended Land Pattern

unit: mm

Dimensions



Marking: Laser Printing

*: Month code

\$: Date code

1:6

2:G

3:A

Terminal Number

(6): Ant


(3):TX

(1): RX


Others: GND

Notice) Please refer to Measurement Circuit for Port information in detail.

Land Pattern



Measurement Circuit (Top Thru View)



R1:50 ohm	L1 :8.2nH(Ideal inductor)
	:9.1nH(LQP03TN9N1)
	<reference></reference>
R2:50 ohm	L2 :24nH(Ideal inductor)
R3 : 50 ohm	



Electrical Characteristic < TX→ANT. >

$TX \rightarrow ANT.$						Characteristics (-20 to +85 deg.C)			Note
Contax Fraguenay				min.	typ.*	max.	N 41 1		
Center Frequency Insertion Loss	880.		915.	N / I I		897.5 2.3	3.0	MHz dB	
insertion Loss		to to	914.75	MHz MHz		2.3	3.0	dВ	
		to to	912.5	MHz		1.8	2.2	dB _{INT}	Any 4.5MHz
Ripple Deviation		to	915.	MHz		1.5	2.3	dB dB	Arry 4: Siviriz
VSWR		to	915.	MHz		1.5	2.0	ub_	TX
		to	915.	MHz		1.5	2.0		ANT.
Absolute Attenuation		to	716.	MHz	30	37		dB	
		to	728.	MHz	35	37		dB	
	728.	to	793.	MHz	30	37		dB	
	832.	to	862.	MHz	30	40		dB	B20 TX
		to	960.	MHz	44	56		dB	
	1559.	to	1563.	MHz	33	39		dB	COMPASS
	1565.42		1573.37	MHz	33	38		dB	Lower GPS
		to	1577.47	MHz	33	38		dB	Regular GPS
		to	1585.42	MHz	33	37		dB	Upper GPS
		to.	1605.89 1785.	MHz	33 30	39 46		dB dB	GLONASS
		to to	1840.	MHz MHz	40	46		dB dB	B3 TX 2f
		to to	1880.	MHz	38	50		dB	21
		to to	1980.	MHz	30	46		dB	B1 TX
	2110.	to	2170.	MHz	27	41		dB	1
		to	2500.	MHz	35	39		dB	ISM2.4
		to	2494.	MHz	35	39		dB	WLAN co-ex
		to	2745.	MHz	33	38		dB	3f
	3520.	to	3660.	MHz	20	33		dB	4f
		to	4575.	MHz	20	31		dB	5f
		to	5950.	MHz	20	28		dB	ISM5G, 6f
	6160.	<u>to</u>	6405.	MHz	15	25		dB	7f
	7040. 7920.	to	7320. 8235.	MHz MHz	9.0	14.0 11.0		dB dB	8f 9f
		<u>to</u> to	9150.	MHz	2.0	11.0		dB	10f
	9680.	to	10065.	MHz	2.0	12.0		dB	11f
	10560.	to	10980.	MHz	2.0	7.0		dB	12f
	11440.	to	11895.	MHz	2.0	7.0		dB	13f
	12320.	to	12750.	MHz	2.0	9.0		dB	14f
						ļ			

^{*} Typical value at 25±2deg.C



Electrical Characteristic < ANT.→RX >

		<u> </u>		11 11 1		rootori	otico		1
ANT. → RX					Characteristics (-20 to +85 deg.C)			.	
						_		Unit	Note
0	<u> </u>				min.	typ.*	max.		
Center Frequency	005		000	N 41 1-		942.5	0.0	MHz	
Insertion Loss	925. 925.25	to	960. 959.75	MHz MHz		2.5 2.4	3.8 3.5	dB dB	
	923.23		957.5	MHz		1.9	2.7	dB _{INT}	Any 4.5MHz
Ripple Deviation	925.	to to	960.	MHz		1.3	3.0	dB dB	Ally 4.5WIIIZ
VSWR	925.	to	960.	MHz		1.7	2.2	ub.	RX
	925.	to	960.	MHz		1.8	2.2		ANT.
Absolute Attenuation	10.	to	880.	MHz	45	64		dB	
			45.	MHz	50	109		dB	RX - TX
	835.	to	870.	MHz	40	67		dB	2TX - RX
	880.	to	915.	MHz	45	58		dB	TX
	902.5	to	910.	MHz	30	61		dB	(RX + TX) / 2
	980.	to	1045.	MHz	25	28		dB	D// D/
	1427.	to	1448.	MHz	40	72		dB	B11 TX
	1710. 1805.	to	1785. 1920.	MHz	40 40	66 64		dB dB	B3 TX
	1920.	to_	1920.	MHz MHz	40	63		dB dB	RX + TX, 2f B1 TX
	2400.	to	2500.	MHz	40	59		dВ	ISM2.4
	2500.	to to	2570.	MHz	40	60		dB	B7 TX
	2685.	to	2790.	MHz	40	58		dB	RX + 2TX
	2775.	to	2880.	MHz	40	58		dB	3f
	2880.	to	3700.	MHz	35	55		dB	
	3700.	to	3840.	MHz	40	55		dB	4f
	4625.	to	4800.	MHz	40	53		dB	5f
	4900.	to	5950.	MHz	40	53		dB	ISM 5G, 6f
	6475.	to	6720.	MHz	20	55		dB	7f
	7400.	to	7680.	MHz	15	53		dB	8f
	8325.	to	8640.	MHz	15	57		dB	9f
	9250.	to	9600.	MHz	15	43		dB	10f
	10175.	to	10560.	MHz	15	34		dB	11f
	11100.		11520.	MHz	15	27		dB	12f
	12025.	to	12480.	MHz	15	26		dB	13f
						<u> </u>			
						1			
						1			

^{*} Typical value at 25±2deg.C



Electrical Characteristic < TX→RX. >


						racteri to +85 d	stics		
T.	$X \rightarrow RX$	$X \to RX$						Unit	Note
Isolation					min.	typ.*	max.		
1301dt1011	882.5	to	912.5	MHz	55	64		dB _{INT}	Any 4.5MHz Any 4.5MHz
	927.5	to	957.5	MHz	55	61		dB _{INT}	Any 4.5MHz
									* T + 05 0 0


^{*} Typical value at 25±2deg.C



Electrical Characteristic

< TX→ANT. >









Electrical Characteristic











Electrical Characteristic

 $< TX \rightarrow RX. >$









Dimensions of Tape & Reel unit: mm


Carrier Tape



Tape



Reel





Important Notice (1/2)

PLEASE READ THIS NOTICE BEFORE USING OUR PRODUCTS.

Please make sure that your product has been evaluated and confirmed from the aspect of the fitness for the specifications of our product specified in the front page of this product specifications (the "Product" or "Products") when our Product is mounted to your product. All the items and parameters in this product specification/datasheet/catalog have been prescribed on the premise that our Product is used for the purpose, under the condition and in the environment specified in this specification. You are requested not to use our Product deviating from the condition and the environment specified in this specification.

Please note that the only warranty that we provide regarding the Product is its conformance to the specifications provided herein. Accordingly, we shall not be responsible for any defects in products or equipment incorporating such Products, which are caused under the conditions other than those specified in this specification.

WE HEREBY DISCLAIMS ALL OTHER WARRANTIES REGARDING THE PRODUCTS, EXPRESS OR IMPLIED, INCLUDING WITHOUT LIMITATION ANY WARRANTY OF FITNESS FOR A PARTICULAR PURPOSE, THAT THEY ARE DEFECT-FREE, OR AGAINST INFRINGEMENT OF INTELLECTUAL PROPERTY RIGHTS.

The Product shall not be used for any application which requires especially high reliability or accuracy in order to prevent defect which incurs high possibility of damage to the third party's life, body or property such as the applications listed below as item (a) to (j) (the "Prohibited Application"). You acknowledge and agree that, if you use our Products in the Prohibited Applications, we will not be responsible for any damage caused by such use.

Furthermore, YOU AGREE TO INDEMNIFY AND DEFEND US AND OUR AFFILIATES AGAINST ALL CLAIMS, DAMAGES, COSTS, AND EXPENSES THAT MAY BE INCURRED, INCLUDING WITHOUT LIMITATION, ATTORNEY FEES AND COSTS, DUE TO THE USE OF OUR PRODUCTS IN THE PROHIBITED APPLICATIONS.

- (a) Aircraft equipment.
- (b) Aerospace equipment
- (c) Undersea equipment.
- (d) Power plant control equipment
- (e) Medical equipment.
- (f) Transportation equipment (vehicles, automotive, trains, ships, etc.).
- (g)Traffic signal equipment.
- (h)Disaster prevention / crime prevention equipment.
- (i) Burning / explosion control equipment
- (j) Application of similar complexity and/ or reliability requirements to the applications listed in the above.

For the avoidance of doubt, the Product is not automotive grade, and will not support such requests for automotive as below, also not support other specific requests for automotive.

- AEC-Q200
- PPAP
- IATF16949, VDA6.3
- Zero Defect program
- Long product life cycle
- Automotive 8D failure analysis and report



Important Notice (2/2)

We expressly prohibit you from analyzing, breaking, Reverse-Engineering, remodeling altering, and reproducing our product. Our product cannot be used for the product which is prohibited from being manufactured, used, and sold by the regulations and laws in the world.

Please do not use the Product in molding condition.

This product is ESD (ElectroStatic Discharge) sensitive device.

When you install or measure this, you should be careful not to add antistatic electricity or high voltage. Please be advised that you had better check anti serge voltage.

We do not warrant or represent that any license, either express or implied, is granted under any our patent right, copyright, mask work right, or our other intellectual property right relating to any combination, machine, or process in which our Products or services are used. Information provided by us regarding third-party products or services does not constitute a license from us to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from us under our patents or other intellectual property.

Please do not use our Products, our technical information and other data provided by us for the purpose of developing of mass-destruction weapons and the purpose of military use.

Moreover, you must comply with "foreign exchange and foreign trade law", the "U.S. export administration regulations", etc.

Please note that we may discontinue the manufacture of our products, due to reasons such as end of supply of materials and/or components from our suppliers.

Customer acknowledges that Murata will, if requested by you, conduct a failure analysis for defect or alleged defect of Products only at the level required for consumer grade Products, and thus such analysis may not always be available or be in accordance with your request (for example, in cases where the defect was caused by components in Products supplied to Murata from a third party).

The Product shall not be used in any other application/model than that of claimed to Murata.

Customer acknowledges that engineering samples may deviate from specifications and may contain defects due to their development status.

We reject any liability or product warranty for engineering samples.

In particular we disclaim liability for damages caused by

- •the use of the engineering sample other than for evaluation purposes, particularly the installation or integration in the Product to be sold by you,
 - deviation or lapse in function of engineering sample,
 - improper use of engineering samples.

We disclaim any liability for consequential and incidental damages.

If you can't agree the above contents, you should inquire our sales.