

## **Land Pattern**



## Temperature Profile

## ■ Reflow Soldering Profile

1. Soldering profile for Lead-free solder (96.5Sn/3.0Ag/0.5Cu)



Series	Standard Profile						Limit Profile					
	Pre-heating		Heating		Peak Temperature	Cycle of	Pre-heating		Heating		Peak	Cycle of
	Temp. (T1)	Time (t1)	Temp. (T2)	Time (t2)	(T3)		Temp. (T1)	Time (t1)	Temp. (T4)	Time (t3)	Temperature (T5)	Reflow
	°C	sec.	°C	sec.	°C	Time	°C	sec.	°C	sec.	°C	Time
SVM4	150 to 180	60 to 120	220	30 to 60	245±3	2	150 to 180	60 to 120	230	30 to 50	260 +5/-0	2

## Soldering Iron

	Standard Condition									
Series	Temperature of Soldering Iron Tip	Soldering Time	Soldering Iron Power Output	Cycle of Soldering Iron						
	°C	sec.	W	Time						
SVM4	350±10	3 max.	30 max.	1						