

PREFACE:

This application note describes the configuration of the “Rapid_ON” signal and [cold redundant features](#) of the power supplies listed below:

MPS #	Model Number	Address	Main Output	Standby Output	Airflow
M1975	D1U54T-W-1200-12-HB3AC	ADDR_SEL (External resistor)	12Vdc	12Vdc	Front to Back
M2045	D1U54T-W-1200-12-HB4TAC			12Vdc	Back to Front
M2046	D1U54T-W-1200-12-HU3AC			3.3Vdc/5Vdc	Front to Back
M2047	D1U54T-W-1200-12-HU4TAC			3.3Vdc/5Vdc	Back to Front

GENERAL NOTES:

- This product series is compliant with PMBus™ Part I and Part II Rev 1.2.
- Configuration of this signal requires write commands issued by host/system via the PMBus™.
- Refer to PMBus™ Communications Protocol Application Note [ACAN-113](#) for additional details.

RAPID_ON SIGNAL VOLTAGE LEVELS:

The signal is internally buffered by a Schmitt Trigger device. The voltage varies depending on the standby voltage (3.3V or 5.0V for example) and the QTY of PSUs connected, due to an internal 10K pull-down resistor.

Model	Standby Voltage	Rapid_ON DC voltage level vs QTY PSUs		
		QTY 2	QTY 3	QTY 4
D1U54x-x-2000-12-H HAXC	5.0 Vdc	4.49 Vdc	4.23 Vdc	3.98 Vdc
D1U54x-x-2000-12-H HBxC	3.3 Vdc	2.69 Vdc	2.79 Vdc	2.63 Vdc
D1U54x-x-2000-12-H HCxC	5.0 Vdc	2.69 Vdc	2.79 Vdc	2.63 Vdc

TWO COLD REDUNDANT MODE OPTIONS:

In order to accommodate a wide range of system applications, two cold redundant modes are supported:

1. [Automatic Mode](#): standard Intel CRPS cold redundancy protocol, up to four (4) PSUs.
2. [Manual Mode](#): PSU output on/off decision is made by the system/host based on PSU sensor readings via PMBus™, and not limited to four (4) PSUs.

General requirements for a power supply operating in either of the above CR modes:


- Turn on main output within 100µs of RAPID_ON bus being driven LOW
- Turn off main output ORing FET
- Maintain a pre-ORing capacitors charge level of at least 12.6V
- Keep PWOK asserted
- Disconnect any internal parasitic loads that would otherwise cause the output cap to discharge
- Turn off internal fan
- Pre-bias its voltage error amplifier to maximum duty cycle (preventing the loop compensation from slowing the turn on process in the event of assertion of the RAPID_ON bus.
- Disable power up soft start output circuit
- Keep the PFC stage Operating at the lowest possible operating frequency and the bulk capacitor charged
- No PMBus™ fault or warning conditions reported via STATUS commands
- PMBus™ READ_EOUT (where supported) command shall continue to increment its sample counter and update its power accumulator
- PMBus™ READ_PIN command should continue to report its input power
- If RAPID_ON bus is pulled down, the operating PSU’s must share load conventionally. The system must reassign the PSU rolls to restore CR mode. [Link back to logic table](#)

Automatic Mode (INTEL CRPS compliant)

[Link Back to CR options](#)

The output on/off control is decided by the PSU based on a comparison of the voltage level of the ISHARE bus voltage and internal fixed thresholds. Once the system successfully completes the PSU roll assignment and the bus is set to active (high), the PSUs determine the output on/off status and how many PSUs share the load.

AUTOMATIC MODE - INTEL CRPS Standard



1) For illustration purposes, the top PSU is shown with more detail than the PSUs below even though each PSU contains the same circuit detail.

2) In this CR method, configured via PMBus, the PSUs self manage the on/off state based on system assigned rolls + internal programmed values

3) The ISHARE is an analog ~ 0-8 VDC signal proportional to load current, suitably utilized by the PSU in CR mode in conjunction with internally programmed threshold values to determining the main output on/off state.

4) Only one PSU, known as "COLD_REDUNDANT_ACTIVE" provides the Rapid_ON pull-up / voltage source.

5) Rapid_ON is a two state logic signal
Low = standard redundant mode
High = CR mode

6) RPU = Pull-Up Resistor

7) RPD = Pull-Down Resistor

8) CR Bus voltage varies with the PSU model and QTY connected PSUs, since the value of RPD decreases as more units are connected to the bus

9) The 12V main outputs are connected together at the system side

PMBus™ COMMANDS FOR AUTOMATIC MODE [LINK TO PMBUS™ DEFINITIONS](#)

1) Configure the signal pin C1 for RAPID_ON the system writes the following:

1	7	1	1	8	1	1	8	1	1	8	1	1
S	Slave Address	WR	A	EAh	A	P	96h	A	P	69h	A	P

2) Assign the PSU rolls writing:

1	7	1	1	8	1	1	8	1	1
S	Slave Address	WR	A	FCh	A	P	ROLL (0h, 1h, 2h 3h or 4h)	A	P

Roll Names:

CONVENTIONAL REDUNDANCY: (BYTE 0X0h)

COLD_REDUNDANT_ACTIVE_MODE (aka MASTER): (byte 0x01h) At least one (1) PSU must be assigned this roll, aka “Always On”

COLD_STANDBY_LEVEL_1: (byte 0x02h) next unit to power load as ISHARE bus increases > threshold / third to shed as load falls

COLD_STANDBY_LEVEL_2: (byte 0x03h) next unit to power load as ISHARE bus increases > second threshold / second to shed as load falls

COLD_STANDBY_LEVEL_3: (byte 0x04h) next unit to power load as ISHARE bus increases > third threshold / first to shed as load falls

Threshold Current ON/OFF voltage and PMBus™ Roll Byte assignment Table:

Basic Logic table based on various scenarios:

Roll	PMBus™ Roll Byte	Threshold Current (Adc)		Notes	Description
		ACTIVE_ON	COLD_STANDBY		
Standard Redundancy	0x0h	N/A	N/A	Always on; ignores RAPID_ON and maintains normal operation	Turns the power supply ON into standard redundant load sharing mode. The power supply's CR_BUS# signal shall be OPEN but still pull the bus low if a fault occurs to activate any power supplies still in Cold Standby state.
Cold_Redundant_Active aka ACTIVE & MASTER	0x1h	-	-	Always on; ignores RAPID_ON and maintains normal operation (behaves same as conventional redundant)	- Defines this power supply to be the one that is always ON in a cold redundancy configuration. - Provides the Bus Pull-up
COLD_STANDBY_1	0x2h	40	18	Output turns on after at load current of 40A, remains on until load falls below 18A	Level 1 - Defines the power supply that is first to turn on in a cold redundant configuration as the load increases.
COLD_STANDBY_2	0x3h	62	37.5	Output turns on after at load current of 62, remains on until load falls below 37.5A	Level 2 - Defines the power supply that is second to turn on in a cold redundant configuration as the load increases.
COLD_STANDBY_3	0x4h	84	56.5	Output turns on after at load current of 84A, remains on until load falls below 56.5A	Level 3 - Defines the power supply that is third to turn on in a cold redundant configuration as the load increases.

Logic table of output state:

RAPID_ON Bus State	ISHARE Bus Voltage	Main output State	Cold redundant State
High	<VACTIVE_ON_threshold ¹	OFF	COLD_STANDBY
High	>VACTIVE_ON_threshold ¹	ON	ACTIVE_ON
Low	Doesn't Care	ON	Conventional Redundancy


¹ Is the PSU's internally programmed fixed [threshold limits](#) (determine the on/off status) according to direction of change.

Manual Mode:

[Link Back to CR options](#)

After the PSUs are installed and the MASTER & ACTIVE PSU is assigned, the system host controls the on/off status of the “non-master & active” PSU(s) via PMBus™ as system requires, by forcing their status as ACTIVE or COLD_STANDBY. A significant feature of this cold redundant mode is that more than four (4) PSU's can be connected.

MANUAL SYSTEM CONTROLLED CR METHOD



PMbus™ CONFIGURATION, MANUAL MODE COLD REDUNDANCY [LINK TO PMBUS™ DEFINITIONS](#)

1. Configure the multi-function signal pin C1 as "RAPID_ON" by:

	1	7		1	1	8		1	1	8		1	1	8		1	1
S	Slave Address		W	A	EAh		A	P	96h		A	P	69h		A	P	

2. Configure the PSUs for CR by assigning the PSU rolls writing:

	1	7		1	1	8		1	1	8		1	1
S	Slave Address		W	A	FCh		A	P	ROLL (0h, 55h, 0xEh)		A	P	

Roll Names:

CONVENTIONAL REDUNDANCY: (BYTE 0X0h) = DEFAULT SETTING

COLD_REDUNDANCY_FORCED_ACTIVE: (byte 0x55h) At least one (1) PSU must be assigned this roll, aka "Always On" (subsequent PSUs assigned this same roll will be known as "ACTIVE & SLAVE" and the first PSU Assigned the roll of "55" provides the bus pull-up)

COLD_REDUNDANCY_FORCED_STANDBY_X: (byte 0xEh) System makes the PSU output on/off decision and write either "55h" or "Eh" as system requires. Up to 8 PSUs can be controlled in this mode.

NOTE: If the MASTER & ACTIVE PSU to a is written to mode "0x0" by host/system, the CR bus will be forced low and all connected PSUs will end CR mode and immediately share conventionally, while COLD_STANDBY_x assigned PSUs simply enter conventional current share and do not pull down the CR bus.

GENERAL COLD REDUNDANT MODE NOTES:

- 1) A COLD_STANDBY PSU can be assigned any of the three levels, for example, if system contains 2 PSUs, the 2nd COLD_STANDBY PSU can be assigned level 1, level 2 or level 3, as system may require.
- 2) PSU extraction: extraction of a PSU will not cancel CR mode as long as it is not the ACTIVE & MASTER and does not cause OCP Fault
- 3) Power supply insertion: A previously configured COLD_STANDBY PSU can be extracted and re-inserted without issue as long as AC input remains connected as the input power maintains secondary side DSP operation. Likewise if input voltage be removed, the PSU “forgets” it’s CR roll and will power up as STD redundancy. In that situation, the other PSUs are operating in CR mode, and so the last PSU inserted will attempt to load share, but to what degree is indeterminate. Therefore that PSU roll needs to be reassigned.
- 4) Recycling of AC or DC input: ACTIVE & MASTER = will cause bus to collapse and cancel CR mode. The other PSUs will turn on their main outputs and share load conventionally. If a COLD_STANDBY unit has it’s input recycled, CR operation will continue and the connected PSUs will maintain their status/roll.. Again, upon applying the input voltage, this PSU will need it’s roll reassigned + load share degree is indeterminate.
- 5) System can cancel CR mode and force standard redundancy by re-assigning ACTIVE & MASTER PSU as Cold_Standby_x (roll byte: CMD_0x0h)
- 6) PMBus™ warnings do not clear the RAPID_ON bus or end CR Mode, only faults clear the bus.
- 7) ROLL reassignment: The PSUs can be reassigned their rolls only after clearing the RAPID_ON bus (cancelling CR mode).
- 8) “Cold_Redundant_x” Rolls – a PSU can be assigned either of the three “x” levels, useful in deployments of <4 PSUs.
- 9) The first PSU roll assigned must be assigned roll COLD_REDUNDANT_ACTIVE / ACTIVE & MASTER
- 10) Once the COLD_REDUNDANT_ACTIVE / ACTIVE & MASTER has been set, the Rapid_ON bus must be cleared in order to reassign this roll.
- 11) Conventional sharing mode is activated (CR mode cancelled) upon any of these events:
 - a. PSU fault (Assertion of the RAPID_ON signal, causing all PSU's to be on within 100uS)
 - b. Reassigning the Active & Master PSU to Cold_Redundant_x via Roll via PMBus™
 - c. Loss of input power to the COLD_REDUNDANT_ACTIVE / ACTIVE & MASTER PSU
 - d. Extracting COLD_REDUNDANT_ACTIVE / ACTIVE & MASTER PSU
- 12) Indicators of CR mode operation:

Visual indication PMBus™ register & or visual	ACTIVE_MASTER / ACTIVE & SLAVE COLD REDUNDANT ACTIVE	COLD STBY / FORCED STBY
LED (Visual)	On Solid	Blinks 2hz
Fan (PMBus™)	Fan rotation	No fan rotation
Output current main (PMBus™)	Output load detected	No load current
Main output voltage (PMBus™)	12.0 VDC output	Trimmed to 12.3 – 12.4VDC (compensates for ORING drop)

GENERAL DESCRIPTION AND POSSIBLE BENEFITS OF COLD REDUNDANCY:

Cold redundancy is a specific mode of current sharing in a redundant system where the load demand is light for prolonged periods of time. CR provides a means of shedding PSUs when load is light, while maintaining the ability to rapidly power on as demand increases, without loss of load voltage or system operations. The main potential benefit is that PSUs, because they share a higher load, operate at a higher efficiency.

Cold redundant features of this PSU series enable the host system with a method of improving efficiency under light loading conditions in redundant configurations such as 1+1, 2+1, 3+1 or 2+2 without compromising fault tolerance and redundancy.

Automatic CR mode also reduces the system CPU demand and resources since the PSUs self-manage the on/off optimization.






[Back to Overview](#)










RELATED DOCUMENTS & APPLICATION NOTES		
Document Number	Description	Link
ACAN-113	D1U54P-x-2000 Communication Protocol	Click to open URL document
D1U54T-W-1200-12-HxxxAC	Product datasheet	Click to open URL document


[Link back to Overview](#)

PMBus™ Protocol Definitions (Reference PMBus part 1 Revision V1.1)

[\(Back to configuration details\)](#)

Symbol	Meaning
	A vertical rectangle indicates a single bit sent from the host (bus master) to a slave
	A vertical rectangle with a shaded interior indicates a bit sent from a slave device to the bus master.
	A rectangle with a number over it represents one or more bits, as indicated by the number
	The START condition sent from a bus master device
	A REPEATED START condition sent from a bus master device

Symbol	Meaning
	An Acknowledge (ACK) condition send from the host
	A Not Acknowledge (NACK) condition sent from the host
	An Acknowledge (ACK) condition sent from a slave device
	A Not Acknowledge (NACK) condition sent from a slave device
	A STOP condition sent by a bus master device
	The first seven bits of the address byte, generally corresponding to the physical address of the device.
	The bit [0] of the address byte with a value of 1, indicating the device is being addressed with a read.
	The bit [0] of the address byte with a value of 0, indicating the device is being addressed with a write.
	The SMBus broadcast address to which all devices must respond. The value is 0000000b. This is always used only with the bit [0] equal to 0 (write).



Murata Power Solutions, Inc.
129 Flanders Road
Westborough, MA 01581
ISO 9001 and 14001 REGISTERED



This product is subject to the following operating requirements and the Life and Safety Critical Application Sales Policy. Refer to:

<https://www.murata-ps.com/requirements/>

Murata Power Solutions, Inc. ("Murata") makes no representation that the use of its products in the circuits described herein, or the use of other technical information contained herein, will not infringe upon existing or future patent rights. The descriptions contained herein do not imply the granting of licenses to make, use, or sell equipment constructed in accordance therewith. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm, and take appropriate remedial actions. Buyer will fully indemnify Murata, its affiliated companies, and its representatives against any damages arising out of the use of any Murata products in safety-critical applications. Specifications are subject to change without notice.

© 2020 Murata Power Solutions, Inc.