

Murata D1U74T-W-2700-12-HBxC Power Converter Modules provide PMBus digital communications features that comply with CRPS-185 2700W specifications.

This application note provides a basic overview of the PMBus features, including a list of supported commands. Please refer to the referenced documentation for additional fine details, as required.

Reference Documents:

- *Intel® PMBus Application Profile for AC/DC & DC/DC Server Power Supplies*, revision 1.31 (Reference Number: 451620)
- *Intel® CRPS-185 2700W* specifications
- *PMBus™ Power System Management Protocol Specification Part I – General Requirements, Transport And Electrical Interface*, Revision 1.2
- *PMBus™ Power System Management Protocol Specification Part II – Command Language*, Revision 1.2
- *Murata D1U86T-W-2700-12-HBxC Series Datasheet*

General PMBus Characteristics:

- PMBus Power Sourcing - Redundant Slave Device Power is sourced between adjoined power supply converter modules and makes it possible to communicate with a power supply that has lost input power. PMBus registers and other commands are possible after loss of input power as long as at least one adjoined redundant power supply installed is operating.
- 100kbs maximum supported clock/data speed
- PEC (Packet Error Checking) is supported
- Linear Data Format

Device Addressing Methods:

D1U74T-W-2700-12-HBxC contains two internal slave devices:

1. Secondary side micro-processor
2. IPMI compliant EEPROM

Address must be configured before communications between system/host and power supply is possible. Address signal pins “A1” and “A0” are provided to configure the address as defined in the following table.

| Slave Device Address Selection | | |
|--|--------------|--------------|
| Slave Address (hex) PSU μP / IPMI FRU EEPROM | A1 pin state | A0 pin state |
| B0h / A0h | Low | Low |
| B2h / A2h | Low | High |
| B4h / A4h | High | Low |
| B6h / A6h | High | High |

SUPPORTED COMMANDS:

| Cmd Code | Page | Command | Transaction Type | Bit # | Bit Name | Comments |
|----------|-------------|---|---|-------|------------------|---|
| 03h | N/A | CLEAR_FAULTS | Send Byte | | | Clear all status bits in all PAGES |
| 05h | N/A | PAGE_PLUS_WRITE | Block Write | | | Used with STATUS_INPUT, STATUS_TEMPERATURE, STATUS_IOUT Available page: 0 and 1 |
| 06h | N/A | PAGE_PLUS_READ | Block Write Block Read Process Call | | | Used with STATUS_INPUT, STATUS_TEMPERATURE, STATUS_IOUT, STATUS_WORD Available page: 0 and 1 |
| 19h | N/A | CAPABILITY | Read Byte | | | This command provides a way for a host system to determine some key capabilities of a PMBus device. Always read 90h |
| 1Ah | N/A | QUERY (used with any command) | Block Write Block Read Process Call | | | QUERY (used with any command) |
| 1Bh | N/A | SMBALERT_MASK | Reading: Block Write Block Read Process Call Writing: Write Word | | | Used with STATUS_INPUT, STATUS_TEMPERATURE, STATUS_IOUT |
| 20h | N/A | VOUT_MODE | Read Byte | | | Single data byte sets the READ_VOUT sensor to linear mode data format and supplies N = -9 exponent for translation to volts. Always read 17h |
| 30h | N/A | COEFFICIENT | Block Write Block Read Process Call | | | Used with READ_EIN |
| 3Ah | N/A | FAN_CONFIG_1_2 | Read Byte | | | Show the config of fan. Always read 90h |
| 3Bh | N/A | FAN_COMMAND_1 | Read Write Word | | | Manual fan override command fan speed value in Duty Cycle (0-100 in Linear data format) |
| 4Ah | N/A | IOUT_OC_WARN_LIMIT | Read Write Word | | | Sets the value of the output current, in Amperes, that causes an output overcurrent warning. In Linear Data format. (Allowable range: 1 - 265A (1-120A for low range input), default value: 265A (120A for low range input) |
| 51h | N/A | OT_WARN_LIMIT (Hot Spot) | Read Write Word | | | Set the temperature, in degrees Celsius, of the unit at which main output shutdown due to OTP. In the Linear Data format. (Allowable range: 0 - 134 °C, default value: 134 °C) |
| 79h | 00h, 01h | STATUS_WORD | Read Word | 6 | UNIT_OFF | Asserted when unit not providing power to the output for whatever reason |
| | | | | 5 | VOUT_OV_F | Asserted when main output shutdown due to overvoltage fault has occurred. Refer to STATUS_VOUT for details |
| | | | | 4 | IOUT_OC_F | Asserted when main output shutdown due to overcurrent fault has occurred. Refer to STATUS_IOUT for details |
| | | | | 3 | VIN_UV_F | Asserted when main output shutdown due to input undervoltage fault has occurred. This bit will not be set before main output is normally startup |
| | | | | 2 | TEMPERATURE_F_W | Asserted when an overtemperature fault or warning has occurred; Refer to STATUS_TEMPERATURE for details |
| | | | | 1 | CML_F | Asserted when a communications, memory, or logic fault has occurred |
| | | | | 0 | NONE_F_W | Other internal faults |
| | | | | 7 | VOUT | Asserted when an output failure has occurred |
| | | | | 6 | IOUT/POUT | Asserted when an output current / output power fault or warning has occurred; Refer to STATUS_IOUT for details |
| | | | | 5 | INPUT | Asserted when an Input voltage/current/power fault or warning has occurred; Refer to STATUS_INPUT for details |
| | | | | 4 | MFG_SPECIFIC_F_W | Manufacturer specific fault or warning has occurred |
| 3 | POWER_GOOD# | Asserted when the POWER_GOOD signal is negated | | | | |
| 2 | FANS | Asserted when a fan fault or warning has occurred; Refer to STATUS_FANS for details | | | | |
| 7Ah | N/A | STATUS_VOUT | Read Byte | 7 | VOUT_OV_F | Asserted when main output shutdown due to overvoltage fault has occurred. Protection threshold: refer to data sheet. |
| | | | | 4 | VOUT_UV_F | Asserted when main output shutdown due to undervoltage fault has occurred. Protection threshold: refer to data sheet. |
| 7Bh | 00h, 01h | STATUS_IOUT | Read Byte | 7 | IOUT_OC_F | Asserted when an output overcurrent fault has occurred. Protection threshold: refer to data sheet. |
| | | | | 5 | IOUT_OC_W | Asserted when an output overcurrent warning has occurred. Warning threshold = IOUT_OC_WARN_LIMIT, recovery threshold = warning threshold - 2A |
| | | | | 1 | POUT_OP_F | Asserted when Pout has exceeded limits Fault threshold = 4272W (1971W for low input range) |
| | | | | 0 | POUT_OP_W | Asserted when an output overpower warning has occurred. Warning threshold = 3180W (1468W for low input range), recovery threshold = warning threshold - 50W |

| Cmd Code | Page | Command | Transaction Type | Bit # | Bit Name | Definition |
|----------|----------|------------------------------------|------------------|-------|----------------------|---|
| 7Ch | 00h, 01h | STATUS_INPUT | Read Byte | 5 | VIN_UV_W | Asserted when an input undervoltage warning has occurred. Warning threshold = 81V, recovery threshold = 85.5V |
| | | | | 4 | VIN_UV_F | Asserted when main output shutdown due to input undervoltage fault has occurred. Protection threshold refer to data sheet. |
| | | | | 3 | VIN_UV_OFF (PSU_OFF) | Asserted when main output is OFF because of insufficient input voltage |
| | | | | 1 | IIN_OC_W | Asserted when an input overcurrent warning has occurred. Warning threshold = 17.5A, recovery threshold = 16.5A |
| | | | | 0 | PIN_OP_W | Asserted when an input overpower warning has occurred. Warning threshold = 3125W (1500W for low input range), recovery threshold = warning threshold – 50W |
| 7Dh | 00h, 01h | STATUS_TEMPERATURE | Read Byte | 7 | TEMPERATURE_OT_F | Asserted when an input over temperature fault has occurred. T1 threshold = 65C T2 threshold = 138C T3 threshold = 110C |
| | | | | 6 | TEMPERATURE_OT_W | Asserted when an input over temperature warning has occurred. T1 threshold = 61C, recovery threshold = 58C T2 threshold = OT_WARN_LIMIT, T2 recovery threshold = T2 threshold – 46C T3 threshold = 106C, recovery threshold = 82C |
| 7Eh | N/A | STATUS_CML | Read Byte | 7 | CML_CMD_F | Asserted when an invalid or unsupported command is received |
| | | | | 6 | CML_DATA_F | Asserted when invalid or unsupported data is received |
| | | | | 5 | CML_PEC_F | Asserted when a packet error checking (PEC) failed has occurred |
| 81h | 00h | STATUS_FANS_1_2 | Read Byte | 7 | FAN_1_F | Asserted when a fan fault has occurred. |
| | | | | 5 | FAN_1_W | Asserted when a fan warning has occurred. |
| 86h | N/A | READ_EIN | Block Read | | | |
| 87h | N/A | READ_EOUT | Block Read | | | |
| 88h | N/A | READ_VIN | Read Word | | | |
| 89h | N/A | READ_IIN | Read Word | | | |
| 8Bh | N/A | READ_VOUT | Read Word | | | |
| 8Ch | N/A | READ_IOUT | Read Word | | | |
| 8Dh | N/A | READ_TEMPERATURE_1 | Read Word | | | |
| 8Eh | N/A | READ_TEMPERATURE_2 | Read Word | | | |
| 8Fh | N/A | READ_TEMPERATURE_3 | Read Word | | | |
| 90h | N/A | READ_FAN_SPEED_1 | Read Word | | | |
| 96h | N/A | READ_POUT | Read Word | | | |
| 97h | N/A | READ_PIN | Read Word | | | |
| 98h | N/A | PMBUS_REVISION | Read Byte | | | Reading of the PMBus revision to which the power supply is compliant. Always read 22h |
| 99h | N/A | MFR_ID | Block Read | | | Manufacturer's ID (ASCII code): Murata-PS |
| 9Ah | N/A | MFR_MODEL | Block Read | | | Manufacturer's Model Number (ASCII code): D1U74T-W-2700-12-HBxC |

| Cmd Code | Page | Command | Transaction Type | Bit # | Bit Name | Definition |
|-----------|------|----------------------------|---|-------|----------|--|
| 9Bh | N/A | MFR_REVISION | Block Read | | | Manufacturer's model revision (ASCII code). XXXX-YYYY-0000 XXXX - Primary FW version/revision, YYYY - Secondary FW version/revision |
| 9Ch | N/A | MFR_LOCATION | Block Read/Write | | | Identify the location that manufactured the unit (ASCII code): China |
| 9Dh | N/A | MFR_DATE | Block Read/Write | | | Identify the unit's date of manufacture (ASCII code: YYWW, e.g. 1535, 15-> year, 35 -> week) |
| 9Eh | N/A | MFR_SERIAL | Block Read/Write | | | Serial Number: SSYYWWRR**** MPS 12-digit serial number |
| 9Fh | N/A | APP_PROFILE_SUPPORT | Read Byte | | | Always read 05h |
| A0h | N/A | MFR_VIN_MIN | Read Word | | | Minimum rated value of the input voltage = 90V (AC input) / 180V (DC input). |
| A1h | N/A | MFR_VIN_MAX | Read Word | | | Maximum rated value of the input voltage = 264V (AC input) / 300V (DC input). |
| A2h | N/A | MFR_IIN_MAX | Read Word | | | Maximum rated value of the input current = 18 Amps (High line AC or DC input) / 15 Amps (Low line AC input). |
| A3h | N/A | MFR_PIN_MAX | Read Word | | | Maximum rated value of the input power = 3000W (High line AC or DC input) / 1352 W (Low line AC input). |
| A4h | N/A | MFR_VOUT_MIN | Read Word | | | Minimum rated value of the output voltage = 11.59V. Linear (N = -9) supplied by command VOUT_MODE. |
| A5h | N/A | MFR_VOUT_MAX | Read Word | | | Maximum rated value of the output voltage = 12.81V. Linear (N = -9) supplied by command VOUT_MODE. |
| A6h | N/A | MFR_IOUT_MAX | Read Word | | | Maximum rated value of the output current = 225A (High line AC or DC input) / 100A (Low line AC input). |
| A7h | N/A | MFR_POUT_MAX | Read Word | | | Maximum rated value of the output power = 2700W (High line AC or DC input) / 1200W (Low line AC input). |
| A8h | N/A | MFR_TAMBIENT_MAX | Read Word | | | Maximum ambient temperature 55degC. |
| A9h | N/A | MFR_TAMBIENT_MIN | Read Word | | | Minimum ambient temperature: 0degC. |
| AAh | N/A | MFR_EFFICIENCY_LL | Block Read | | | Retrieves information about the efficiency of the device while operating at a low line condition. Vin =115V, LP = 240W, Leff = 92%, MP = 600W, Meff = 94%, HP = 1200W, Heff = 90%. |
| ABh | N/A | MFR_EFFICIENCY_HL | Block Read | | | Retrieves information about the efficiency of the device while operating at a high line condition. Vin =230V, LP = 540W, Leff = 94%, MP = 1350W, Meff = 96%, HP = 2700W, Heff = 91%. |
| C0h | N/A | MFR_MAX_TEMP_1 | Read Word | | | Maximum rated temperature (Ambient): 61degC. |
| C1h | N/A | MFR_MAX_TEMP_2 | Read Word | | | Maximum rated temperature (hot-spot sec): 134degC. |
| C2h | N/A | MFR_MAX_TEMP_3 | Read Word | | | Maximum rated temperature (hot-spot primary): 106degC. |
| D0 | N/A | MFR_COLD_REDUNDANCY_CONFIG | Read/Write Byte | | | |
| D1h-D3h | | RESERVED | RESERVED | | | |
| D4h | N/A | MFR_HW_COMPATIBILITY | Read Word | | | |
| D5h | N/A | MFR_FWUPLOAD_CAPABILITY | Read Byte | | | |
| D6h | N/A | MFR_FWUPLOAD_MODE | Read/Write Byte | | | |
| D7h | N/A | MFR_FWUPLOAD | Block Write (size = block size from image header) | | | |
| D8h | N/A | MFR_FWUPLOAD_STATUS | Read Word | | | |
| D9h | N/A | MFR_FW_REVISION | Block Read (3 bytes) | | | |
| DCh | N/A | MFR_BLACKBOX | Block Read (230 bytes) | | | |
| DDh | N/A | MFR_REAL_TIME_BLACK_BOX | Block Write/Read (4 bytes) | | | |
| DEh | N/A | MFR_SYSTEM_BLACK_BOX | Block Write/Read (40 bytes) | | | |
| E8h - EFh | | MFR_SPECIFIC_COMMANDS | | | | |
| F0h | N/A | MFR_PWOK_WARNING_TIME | Read/Write Word | | | |
| F6 - FEh | | MFR_SPECIFIC_COMMANDS | | | | |

Additional Details

The Following Section describes the returned results from the above command list.


PAGE_PLUS_WRITE / PAGE_PLUS_READ commands (05h/06h)

Link [Back to Command List](#)

PAGE_PLUS_WRITE and PAGE_PLUS_READ commands are used with the STATUS_WORD, STATUS_INPUT, STATUS_TEMPERATURE, STATUS_IOUT, and STATUS_CML to create two instances of the same command. Each instance is set by the same events but cleared by their own master in the system. The instances at PAGE 00h are controlled by the system BMC and the instances at PAGE 01h are controlled by the system ME. Below are the protocols used to read and clear the STATUS_ commands using the PAGE_PLUS_WRITE and PAGE_PLUS_READ commands.


Reading STATUS_WORD

Block Write – Block Read Process Call with PEC



Reading STATUS_TEMPERATURE, STATUS_IOUT, STATUS_INPUT, STATUS_CML


Block Write – Block Read Process Call with PEC



Reading STATUS commands with PAGE_PLUS_READ

Clearing STATUS commands (write '1' to clear a bit) STATUS_TEMPERATURE, STATUS_IOUT, STATUS_INPUT, STATUS_CML

Block Write with PEC



STATUS_WORD cannot be cleared directly It is cleared based on lower level status commands

Figure 4 Clearing STATUS commands using PAGE_PLUS_WRITE

SENSORS

The following PMBus commands are supported for the purpose of monitoring current, voltage, and power. All sensors continue providing real time data as long as the PMBus device is powered. This means in standby mode the main output(s) of the PSU shall be zero amps and zero volts. Sensors shall meet requirements from 100VAC to 127VAC and from 200VAC to 240VAC (or -36VDC to -75VDC for DC input power supplies). They shall be tested down to 5% load.

| Current / Power / Temperature Monitoring PMBus Commands | |
|---|---|
| PMBus command | Description |
| READ_EIN | New input energy counter described below. Added to PMBus rev 1.2 spec. Uses direct format for the power accumulator; unsigned integer value for the sample count. |
| READ_PIN | Input power meter based on PMBus rev 1.1 spec. Uses Linear formatting. |
| READ_IOUT | Output current in amps for the total 12V current. The other outputs are not sensed. Linear format. |
| READ_EOUT | New output energy counter described below. Added to PMBus rev 1.2 spec. Direct format for the power accumulator; unsigned integer value for the sample count. |
| READ_TEMPERATURE_1 | Returns the temperature in °C of the inlet temperature. Based on PMBus rev 1.1 spec. Linear format. |
| READ_TEMPERATURE_2 | Returns the temperature in °C of the hot spot temperature. Based on PMBus rev 1.1 spec. Linear format. |
| READ_TEMPERATURE_3 | Returns the temperature in °C of the primary heatsink temperature. Based on PMBus rev 1.1 spec. Linear format. |

Sensor Functionality in Different PSU States and Configurations

The functionality of READ_EIN and READ_EOUT in different PSU configurations is stated in the below table. The PSU must continue incrementing the sample counter even if AC power is not present to the PSU but the PMBus device in the PSU is powered from the other power supplies in parallel.

READ_EIN & READ_EOUT Functioning in differing states

| Number of PSUs in system | One PSU state (PSU ₁) | Rest of PSU states (PSU _n) | PSU ₁ Power Accumulator | PSU ₁ Sample counter |
|--------------------------|-----------------------------------|---|--|--|
| 1 or more | ON & AC present | All ON & AC present | New power values continue to add to the power accumulator based on loading condition | Sample counter increments every sample period |
| 1 or more | Stby & AC present | All ON & AC present | New power values continue to add to the power accumulator based on loading condition | Sample counter increments every sample period |
| 1 or more | OFF & no AC present | All OFF & no AC present | Reset power accumulator values to 00 when AC power is re-applied | Reset sample counter to 00 when AC power is re-applied |
| 2 or more | AC power not present | Rest of PSUs in standby mode & AC present | Continue adding 0W to accumulator every sample period | Incrementing sample counter every sample period |
| 2 or more | AC power not present | Rest of PSUs ON & AC present | Continue adding 0W to accumulator every sample period | Incrementing sample counter every sample period |

READ_PIN, READ_IOUT, and READ_TEMPERATURE shall continue to report accurate values when the PSU is in standby mode or when it has no AC power but is in parallel with another PSU(s) with AC power and standby power present.

READ_PIN (97h)

[Back to Command List](#)

The power supply shall provide input power data in watts. The data shall be reported using the PMBus linear format. The data shall be the average input power or filtered input power. If a simple average is used to provide average input power, the minimum averaging duration shall be 2 seconds. If filtering is used; the maximum filter bandwidth shall be 0.5 Hz. The accuracy shall be tested by polling with the READ_PIN command at a rate ranging from 1 sample / second to 10 samples / second.

| READ_PIN Requirements Summary | | | |
|-------------------------------|---------------------|---------------------|--|
| | MIN | MAX | Description |
| Format | PMBus linear format | | PMBus data format; refer to PMBus specification for details |
| Averaging period | 2 seconds | 10 seconds | The AC input power shall be averaged using a simple averaging method of a filtering method. This defines the max/min period for simple averaging and the bandwidth range if the filter method is used. |
| Filtering bandwidth | 0.1 Hz | 0.5 Hz | |
| Accuracy (300W – Max load) | +/-2% | | The input power data shall meet these accuracy requirements over 100-240VAC and under the defined system polling rate. |
| Accuracy (150W - 300W load) | +/-3% | | |
| Accuracy (40W – 150W load) | +/-5W | | |
| System polling rate | 1 sample/ second | 10 samples / second | The power supply shall be polled over this range of rates while testing accuracy. |

READ_IOUT (8Ch)

[Back to Command List](#)

The power supply shall provide output current data in amperes. The data shall be reported using the PMBus linear format. The data shall be the average output current or filtered output current. If a simple average is used to provide average output current, the minimum averaging duration shall be 2 seconds. If filtering is used; the maximum filter bandwidth shall be 0.5 Hz. The minimum accuracy is specified in the table below. The accuracy shall be tested by polling with the READ_IOUT command at a rate ranging from 1 sample / second to 10 samples / second.

| READ_IOUT Requirements Summary | | | |
|--------------------------------|---------------------|---------------------|--|
| | MIN | MAX | Description |
| Format | PMBus linear format | | PMBus data format; refer to PMBus specification for details |
| Averaging period | 2 seconds | 10 seconds | The output current shall be averaged using a simple averaging method of a filtering method. This defines the max/min period for simple averaging and the bandwidth range if the filter method is used. |
| Filtering bandwidth | 0.1 Hz | 0.5 Hz | |
| Accuracy (300W – Max load) | +/-2% | | The output current data shall meet these accuracy requirements over 100-240VAC and under the defined system polling rate. |
| Accuracy (150W - 300W load) | +/-3% | | |
| Accuracy (40W – 150W load) | +/- 1A | | |
| System polling rate | 1 sample/ second | 10 samples / second | The power supply shall be polled over this range of rates while testing accuracy. |

READ_EIN (86h)

Link [Back to Command List](#)

The new READ_EIN command is used to allow the system to apply its own input power filtering. This will allow the system to get faster input power data while preventing aliasing. The command returns an accumulated power value and an associated sample count of number of accumulated power values. This allows the system to calculate its own average power value each time the system polls the PSU.

| Requirements Summary | | | |
|--|--|--------|--|
| | MIN | MAX | Description |
| Format | PMBus Direct format m = 01h, R = 00h, b = 00h | | PMBus data format; refer to PMBus specification for details. |
| Psample averaging period | 4 AC cycles | | Period instantaneous input power is averaged over to calculate P _{sample} . |
| READ_EIN update period | 80/66.7ms (50/60Hz) | | Period at which the power accumulator and sample counter are updated |
| Accuracy (300W – Max load) | +/- 2% | | The input power data shall meet these accuracy requirements over 100-240VAC and under the defined system polling rate. |
| Accuracy (150W - 300W load) | +/- 3% | | |
| Accuracy (40W – 150W load) | +/- 5W | | |
| Range of System polling period | 1 sec | 100 ms | The PSU shall be polled over this range of rates while testing accuracy. |
| <p>IMPORTANT: The PSU READ_EIN update period MUST always be less than the system polling period. To make sure the PSU is compatible with all possible system polling periods; the PSU must update the READ_EIN power accumulator and sample counter at a period less than 100msec (required period is 4 AC cycles 80/67msec).</p> | | | |

READ_EOUT (87h)

Link [Back to Command List](#)


The new READ_EOUT command is used to allow the system to apply its own output power filtering. This will allow the system to get faster output power data while preventing aliasing. The command returns an accumulated power value and an associated sample count of number of accumulated power values. This allows the system to calculate its own average power value each time the system polls the PSU.

| READ_EOUT Requirements Summary | | | |
|---|--|---------------|--|
| | MIN | MAX | Description |
| Format | PMBus Direct format m = 01h, R = 00h, b = 00h | | PMBus data format; refer to PMBus specification for details. |
| Psample averaging period | Nominal 8msec | | Period instantaneous input power is averaged over to calculate P _{sample} . |
| Sampling period | Nominal 8msec | | Period at which the power accumulator and sample counter are updated |
| [P _{accum} / N] Accuracy(5% to 100% load) | ±2% | | The calculated output power data shall meet these accuracy requirements over 100-240VAC and under the defined system polling rate. |
| System polling rate | 1 sample /s | 10 samples /s | The PSU shall be polled over this range of rates while testing accuracy. |

READ_EIN & READ_EOUT Formats

The READ_EIN and READ_EOUT commands shall use the PMBus direct format to report an accumulated power value and the sample count. The PMBus coefficients m, R, and b shall be fixed values and the PSU shall report these values using the PMBus COEFFICIENT command. The coefficient m shall be set to 01h, coefficient R shall be set to 00h, and coefficient b shall be set to 00h.

READ_EIN and READ_EOUT shall use the SMBus Block Read with PEC protocol in the below format.



Cold Redundancy

Link back to [command list](#)

The following details are based on Intel’s® CRPS-185 2700W specification.

The aim of the cold redundancy feature is to ensure the optimum number of power supplies are supporting the system load in 1+1, 2+2, and 3+1 redundant configurations. PMBus manufacturer specific commands are required/used to enable, configure, and monitor this feature..

Architecture Overview:

Block diagrams below show the Cold Redundancy architecture in various redundant configurations.


When the power subsystem is operating in Cold Redundant mode, only the needed power supply to support the best power delivery efficiency are ON. Any additional power supplies; including the redundant power supply, is in Cold Standby state.

Each power supply’s CR signal pin needs to be connected to for the CR_BUS and is therefore a common bus between all power supplies sharing load in the system. CR_BUS is asserted (pulled low) when there is a fault in any power supply or the power supply’s output voltage falls below the Vfault threshold. Asserting the CR_BUS signal causes all power supplies in Cold Standby state to power ON.


Enabling power supplies to maintain best efficiency is achieved by monitoring the Load Share bus voltage and comparing it to a programmed voltage level via a PMBus command.

Whenever there is no Cold Redundant active power supply on the Cold Redundancy bus driving the CR_BUS Logic high state, all power supplies turn on no matter their defined Cold Redundant roll (active or Cold Standby), ensuring incorrect programming of the Cold Redundancy states of the power supply will never cause the power subsystem to shut-down or become over loaded. The default state of the power subsystem is all power supplies ON. There needs to be at least one power supply in Cold Redundant Active state or Standard Redundant state to allow the Cold Standby state power supplies to go into Cold Standby state.

1+1 Redundant Configuration:



Cold Redundancy 2+2 & 3+1 Configuration:



| LOGIC MATRIX FOR COLD STANDBY POWER SUPPLIES | | | |
|--|----------------|---------------|------------------------------------|
| CR_BUS | Load Share | dc/dc_active# | Cold Standby Power Supply State(s) |
| High | $< V_{CR_ON}$ | High | Cold Standby |
| Low | $< V_{CR_ON}$ | Low | Active |
| High | $> V_{CR_ON}$ | Low | Active |
| Low | $> V_{CR_ON}$ | Low | Active |

Cold Standby Power Supply Operating State

A power supply is put into Cold Standby whenever PSON# is asserted, CR_ON# is de-asserted, and COLD_RED_CONFIG value is set to 02h, 03h, or 04h. In the cold standby mode the power supply must:

1. Power ON in < 100µsec when Cold_Red bus is driven LOW
2. Turn off its output OR'ing FET
3. Keep its internal output capacitor before the output OR'ing FET charged to not less than 12.6V
4. Keep PWOK asserted
5. Disconnect any output dummy loads to prevent discharging of the recharged output capacitor
6. Power off any internal fans
7. Pre-bias its voltage error amplifier to maximum duty cycle (preventing the loop compensation from slowing up the turn on process)
8. Disable its output slow start circuit

9. Keep the PFC stage ON at lowest possible operating frequency and its output bulk capacitor charged
10. No PMBus fault or warning conditions reported via STATUS commands

Powering on Cold Standby supplies to maintain best efficiency

Power supplies in Cold Standby state shall monitor the shared voltage level of the load share signal to sense when it needs to power on. Depending upon which position (1, 2, or 3) the system defines that power supply to be in the cold standby configuration; will slightly change the load share threshold that the power supply shall power on at. The CR_BUS of any power supply may be in one of three different states; pulled low, pulled high, or tri-stated. In tri-state the CR_BUS is a high impedance to ground; only a high impedance resistor pulling the signal to ground.

| Example Load Share Threshold for Activating Supplies | | | |
|--|--|--|--------------------------------------|
| | Enable Threshold for V _{CR_ON_EN} | Disable Threshold for V _{CR_ON_DIS} | CR_BUS De-asserted / Asserted States |
| Standard Redundancy | NA; Ignore dc/dc_active# signal; power supply is always ON | | OK = Tri-state Fault = Low |
| Cold Redundant Active | NA; Ignore dc/dc_active# signal; power supply is always ON | | OK = High Fault = Low |
| Cold Standby 1 (02h) | 3.2V (40% of max) | 90% x (3.2V x 1/2) = 1.44V | OK = Tri-state Fault = Low |
| Cold Standby 2 (03h) | 5.0V (62% of max) | 90% x (5.0V x 2/3) = 3.01V | OK = Tri-state Fault = Low |
| Cold Standby 3 (04h) | 6.7V (84% of max) | 90% x (6.7V x 3/4) = 4.52V | OK = Tri-state Fault = Low |

Powering on Cold Standby supplies during a fault or over current condition

When an active power supply asserts its CR_BUS signal (pulling it low), all parallel power supplies in cold standby mode shall power on within 100µsec.

Cold Redundancy PMBus Commands

The PMBus manufacturer specific command MFR_SPECIFIC_00 is used to configure the operating state of the power supply related to cold redundancy. Command Cold_Redundancy_Config (DOh) includes the definition of the values used with the Read-Write Byte SMBus protocol with PEC.

The power supplies setup to be the cold standby power supplies; shall change to standard redundancy mode(DOh = 00h) whenever the CR_BUS is pulled low.

| Cold_Redundancy_Config (D0h) | | |
|------------------------------|--|--|
| Value | State | Description |
| 00h | Standard Redundancy (default power on state) | Turns the power supply ON into standard redundant load sharing mode. The power supply's CR_BUS signal shall be in Tri-state but still pull the bus low if a fault occurs to activate any power supplies still in Cold Standby state. |
| 01h | Cold Redundant Active ¹ | Defines this power supply to be the one that is always ON in a cold redundancy configuration. |
| 02h | Cold Standby 1 ¹ | Defines the power supply that is first to turn on in a cold redundant configuration as the load increases. |
| 03h | Cold Standby 2 ¹ | Defines the power supply that is second to turn on in a cold redundant configuration as the load increases. |
| 04h | Cold Standby 3 ¹ | Defines the power supply that is third to turn on in a cold redundant configuration as the load increases. |
| 05h | Always Standby ¹ | Defines this power supply to be always in cold redundant configuration no matter what the load condition. |
| 06h -- FFh | reserved | |


¹ When the CR_BUS transitions from a high to a low state; each PSU programmed to be in Cold Standby state shall be put into Standard Redundancy mode (Cold_redundancy_Config = 00h). For the power supplies to enter Cold Redundancy mode the system must re-program the power supplies using the Cold_Redundancy_Config command.

Cold Redundancy Bus (CR_BUS)

This is a tri-state output signal of the power supply used to communicate a fault or over current has occurred in one of the power supplies. This is used to power on all the power supplies in the system via the CR_BUS. When the signal is pulled high it allows all power supplies in cold standby mode to go into cold standby state when the load is light enough. When the signal is left open on all power supplies it forces them all cold standby power supplies ON.

| Cold Redundant States | | | |
|-----------------------|-----------------|-----------------|-----------|
| Cold Redundant Config | Operating State | PSU Fault State | CR_BUS |
| Active | On | OK | High |
| Cold Standby 1,2,3 | On | OK | Tri-state |
| Cold Standby 1,2,3 | Cold Stby | OK | Tri-state |
| Always standby | Cold Stby | OK | Tri-state |
| Active | Off | Fault | Low |
| Cold Standby 1,2,3 | On | Fault | Low |
| Cold Standby 1,2,3 | Cold Stby | Fault | Low |
| Always standby | Cold Stby | Fault | Low |

CR Signal / Bus Circuit Diagram:



| CR_BUS Signal Characteristics: | | |
|-------------------------------------|------------|------------|
| Signal Type | custom | |
| | MIN | MAX |
| Logic level low (power supply ON) | 0V | Vil_cr_bus |
| Logic level high (power supply OFF) | Vih_cr_bus | |
| Source current, Cold Red = high | Ioh_cr_bus | |
| Sink current, Cold_Red = low | | Iol_cr_bus |
| Cold_Red fault delay | | 10 μs |
| Cold_Red turn on delay | | 100 μs |

System BMC Requirements

The BMC uses the Cold_Redundancy_Config command to define/configure the power supply's roll in cold redundancy and to turn on/off cold redundancy. The BMC shall schedule a rolling change for which PSU is the Active, Cold Stby1, Cold Stby 2, and Cold Stby 3 power supply. The allows for equal loading across power supply over their life.

Events that trigger a re-configuration of the power supplies using the Cold_Redundancy_Config command.

- AC power ON
- PSON power ON
- Power Supply Failure
- Power supply inserted into system

Power Supply Turn On Function

Powering on and off of the cold standby power supplies is only controlled by each PSU sensing the Vshare bus. Once a power supply turns on after crossing the enable threshold; it lowers its threshold to the disable threshold. The system defines the 'position' of each power supply in the Cold Redundant operation. It will do this each time the system is powered on, a power supply fails, or a power supply is added to the system.

The system is relied upon to tell each power supply where it resides in the Cold Redundancy scheme. When load ramps up and crosses the CR threshold module wake up time must be <3ms (tbd)

When load ramps down and crosses the CR threshold module go-to-sleep (sdbly) time must be <5ms

