

# **Dual Output BWR Models**

Mixed Voltage, 5V and 3.3V, Independent Dual Output 30 Watt DC/DC Converters

# Discontinued

### Typical unit

### **FEATURES**


- Independently regulated 5V/3.3V outputs
- 5V @ 3A/3.3V @ 4.25A simultaneously delivered
- Independent Vout Trim pins for margining
- Independent On/Off Control pins
- 88% efficiency; 75mV ripple/noise
- Input ranges: 10-18V, 18-36V or 36-75V
- UL 1950 and EN60950-1 safety approvals
- Fully isolated, 1500Vdc guaranteed
- Input under and overvoltage shutdown
- Independent OVP; short circuit protection
- Thermal shutdown

### **PRODUCT OVERVIEW**

Murata Power Solutions' BWR series of DC/DC converters now includes two independent converters in one 2" x 2" package. The BWR-5/3-3.3/4.25 family provides both 5V at 3 Amps and 3.3V at 4.25 Amps for a combined output power of 30 Watts from input ranges of 10V to 18V (-D12A), 18 to 36V (-D24A), or 36 to 75V (-D48A).

Each output is regulated by its own control loop to provide  $\pm 1\%$  load and  $\pm 0.5\%$  line regulation. Individual trim pins and a negative or positive on/off control pin allow independent adjustment of output voltages and any combination of power-on sequencing between the 5V and 3.3V outputs. A high efficiency of 88% allows full load operation up to +65°C ambient temperature in a still air environment. Although functionally independent, both outputs are driven from synchronized PWMs to prevent asynchronously generated beat frequencies.

Housed in a plastic case, all models include input Pi filtering, input overvoltage protection, independent output short circuit and current limiting protection and independent output overvoltage protection as well as thermal shutdown. These devices meet IEC950, UL1950 and EN6950-1 safety standards. CB reports are available upon request. "D48A" models are CE marked (meet LVD requirements).



www.murata-ps.com/support

### <u>muRata</u> Ps Murata Power Solutions

## **Dual Output BWR Models**

### Mixed Voltage, 5V and 3.3V, Independent Dual Output 30 Watt DC/DC Converters

### Performance Specifications and Ordering Guide <sup>(1)</sup>

	ORDERING GUIDE												
		Output			Input								
		Vout	lout <sup>②</sup>	R/N (mVp-p) <sup>3</sup>		Regulation (Max.)		VIN Nom.	Range	lin <sup>5</sup>	Efficiency		Package (Case,
	Models <sup>©</sup>	(Volts)	(Amps)	Тур.	Max.	Line	Load <sup>@</sup>	(Volts)	(Volts)	(mA/A)	Min.	Тур.	Pinout)
Discontinued	BWR-5/3-3.3/4.25-D12A	5	3	75	100	±0.5%	±1%	12	10-18	210/2846	83%	85%	C20, P42
Discontinued		3.3	4.25	75	100	±0.5%	±1%						
Discontinued	BWR-5/3-3.3/4.25-D24A	5	3	75	100	±0.5%	±1%	24	18-36	115/1374	85.5%	88%	C20, P42
Discontinued		3.3	4.25	75	100	±0.5%	±1%						
	BWR-5/3-3.3/4.25-D48A	5	3	75	100	±0.5%	±1%	48	36-75	70/687	85.5%	0.00/	C20, P42
Discontinued		3.3	4.25	75	100	±0.5%	±1%					88%	

① Typical at TA = +25°C under nominal line voltage and "full-load" conditions.

② Any combination of 5V/3.3V current, not to exceed the published IOUT specification (30 Watts).


3 Ripple/Noise (R/N) measured over a 20MHz bandwidth with 0.47µF ceramic output capacitors.

④ Tested from 10% load to 100% load.

⑤ Nominal line voltage, no load/full load condition.

6 These are incomplete model numbers. Please refer to the part number structure when ordering.

#### PART NUMBER STRUCTURE




### **Optional Functions**

BWR 30 Watt DC/DC's are designed so a negative logic on/off control ("N" suffix) can be added in the pins 3 and 4 position.

- Standard product. No options specified. Blank
- Negative polarity on/off control Ν
- Pin length: 0.110 in. (2.79mm) ±0.010 L1
- L2 Pin length: 0.145 in. (3.68mm) ±0.010
- -Y RoHS-5 Hazardous substance compliance
- -C RoHS-6 Hazardous substance compliance
- Refer to the last page for additional options.

Note: Not all model number combinations are available. Contact Murata Power Solutions.

#### **MECHANICAL SPECIFICATIONS**



I/O Connections				
Pin	Function P42			
1	+Input			
2	-Input			
3	+5V On/Off			
4	+3.3V 0n/0ff			
5	+5V Output			
6	+5V Return			
7	+5V Trim			
8	+3.3V Return			
9	+3.3V Output			
10	+3.3V Trim			

### muRata Ps Murata Power Solutions

### **Performance/Functional Specifications**

Typical @ TA = +25°C under nominal line voltage, balanced "full-load" conditions, unless noted.

li li	nput
Input Voltage Range:	
D12A Models	10-18 Volts (12V nominal)
D24A Models	18-36 Volts (24V nominal)
D48A Models	36-75 Volts (48V nominal)
Overvoltage Shutdown:	
D12A Models	18.5-21 Volts (20V nominal)
D24A Models	37-40 Volts (38V typical)
D48A Models	77-81 Volts (79V typical)
Start-Up Threshold:	
D12A Models	9.4-10 Volts (9.6V typical)
D24A Models	16.5-18 Volts (17V typical)
D48A Models	34-36 Volts (35V typical)
Undervoltage Shutdown:	
D12A Models	7-8.5 Volts (8V typical)
D24A Models	16-17.5 Volts (16.5V typical)
D48A Models	32.5-34.5 Volts (33.5V typical)
Input Current:	Cap Ordering Cuide
Normal Operating Conditions	See Ordering Guide
Standby Mode:	10mA typical
Off, OV, UV, Thermal Shutdown	10mA typical
Input Reflected Ripple Current:	
Source Impedance	<0.1 $\Omega$ , no external input filtering
D12A Models	TBD
D24A/D48A Models	TBD
Internal Input Filter Type	Pi (0.022µF - 4.7µH - 2.46µF)
Reverse-Polarity Protection:	
D12A Models	1 minute duration, 6A maximum
D24A Models	1 minute duration, 4A maximum
D48A Models	1 minute duration, 2A maximum
<b>On/Off Control</b> (Pins 3 & 4): 3 5	
D12A, D24A & D48A Models	On = open or 13V to +VIN,
	lin = 1.6mA @ 13V
	Off = 0-0.8V, IIN = 2mA @ 0V
"N" Suffix Models ®	On = 0-1.2V, IIN = 2mA @ 0V
	Off = open.
Û	utput
	arpur
Vout Accuracy	1.50/
5V Output	±1.5% maximum ±1.5% maximum
3.3V Output	
Minimum Loading Per Specification	10% of lout maximum
Minimum Loading For Stability $ \mathbb{T} $	No load
Ripple/Noise (20MHz BW) ④	See Ordering Guide
Line/Load Regulation	See Ordering Guide
•	Ŷ
Efficiency	See Ordering Guide
Trim Range 2	±5%
Isolation Voltage:	
Input-to-Output	1500Vdc minimum
Isolation Resistance	100MΩ
Isolation Capacitance	470pF
•	
Current Limit Inception:	2.9.5.1 Ampo
5V @ 98.5% Vout 3 3V @ 98.5% Vout	3.8-5.1 Amps
3.3V @ 98.5% Vout	5.4-6.8 Amps
Short Circuit Current:	
5V Output	3.0 Amps average current
3.3V Output	3.0 Amps average current

## **Dual Output BWR Models**

# Mixed Voltage, 5V and 3.3V, Independent Dual Output 30 Watt DC/DC Converters

Qutput (c	continued)				
Overvoltage Protection:	Magnetic feedback, transorb				
5V Output 3.3V Output	6.0 Volts 4.1 Volts				
1	4.1 VOIIS				
Maximum Capacitive Loading	1000.05				
D12A Models 3.3V 5V	1000μF 680μF				
D24A, D48A Models 3.3V	1000µF				
5V	680µF				
Temperature Coefficient	±0.02% per °C				
•					
Dynamic Characteristics					
Dynamic Load Response:					
5V (50-100% load step to 1% Vout)	200µsec maximum				
3.3V (50-100% load step to 1% Vour)	200µsec maximum				
Start-Up Time: 2					
VIN to Vout	10ms				
On/Off to Vout	TBD				
Switching Frequency	355kHz (±35kHz)				
Environmental					
MTBF 6	Bellcore, ground fixed, full power				
	25°C ambient				
D12A Models	873.9 thousand hours				
D24A Models	1.32 million hours				
D48A Models	1.23 million hours				
Operating Temperature (Ambient): 2					
Without Derating:					
D12A Models	–40 to +60°C				
D24A & D48A Models	-40 to +65°C				
With Derating	To +100°C (See Derating Curves)				
Case Temperature:					
Maximum Operational	+100°C				
For Thermal Shutdown	+100°C minimum, +110°C maximum				
Storage Temperature	-40 to +120°C				
Phy	sical				
Dimensions	2" x 2" x 0.5" (50.8 x 50.8 x 12.7mm)				
Dimensions Case Material	2" x 2" x 0.5" (50.8 x 50.8 x 12.7mm) Diallyl phthalate, UL94V-0 rated				
	, ,				
Case Material	Diallyl phthalate, UL94V-0 rated				
Case Material Pin Material	Diallyl phthalate, UL94V-0 rated Gold-plated copper alloy 2.7 ounces (76.5 grams)				

① All models are specified with external 0.47µF ceramic output capacitors.

② See Technical Notes/Graphs for details.

- ③ Applying a voltage to On/Off Control (pins 3 & 4) when no input power is applied to the converter can cause permanent damage.
- ④ Output noise may be further reduced with the installation of additional external output capacitors. See Technical Notes.
- ⑤ On/Off control is designed to be driven with open collector or by appropriate voltage levels. Voltages must be referenced to the –Input (pin 2).
- 6 Demonstrated MTBF available on request.
- ⑦ For conditions with less than minimum loading, outputs remain stable. However, regulation performance will degrade.
- ⑧ Maximum applied voltage to On/Off pin (N suffix) less than 19.0V.

### muRata Ps Murata Power Solutions

	Absolute Maximum Ratings						
	Input Voltage:						
	Continuous:	D12A Models D24A Models	23 Volts 42 Volts				
	Transient (100ms	D48A Models ec): D12A Models D24A Models D48A Models					
	Input Reverse-Polari	ty Protection	Input Current must be limited. 1 minute duration. Fusing recommended.				
	D12A Models D24A Models D48A Models		6 Amps 4 Amps 2 Amps				
	Output Current 2		Current limited. Devices can withstand an indefinite output short circuit.				
	On/Off Control (Pins 3 & 4) Max. Voltages Referenced to -Input (pin 2)						
	D12A, D24A & I "N" Models	D48A Models	+VIN ±19V				
	Storage Temperature	1	-40 to +120°C				
Lead Temperature (Soldering, 10 sec.)			+300°C				
			es to any of these conditions may adversely Inder conditions other than those listed in				

## **Dual Output BWR Models**

# Mixed Voltage, 5V and 3.3V, Independent Dual Output 30 Watt DC/DC Converters




Figure 3. Trim Connections To Decrease Output Voltages Using Fixed Resistors





Figure 4. Trim Connections To Increase Output Voltages Using Fixed Resistors

Note: Resistor values are in  $k\Omega$ . Accuracy of adjustment is subject to tolerances of resistors and factory-adjusted output accuracy.  $V_0 = desired$  output voltage.

### **Typical Performance Curves**



### TECHNICAL NOTES

#### **Trimming Output Voltages**

These BWR converters have a trim capability (pins 3 & 4) that allow users to independently adjust the output voltages  $\pm 5\%$ . Adjustments to the output voltages can be accomplished via a trim pot, Figure 2, or a single fixed resistor as shown in Figures 3 and 4. A single fixed resistor can increase or decrease the output voltage depending on its connection. Fixed resistors should have absolute TCR's less than 100ppm/°C to minimize sensitivity to changes in temperature.

the Performance/Functional Specifications Table is not implied, nor recommended.

A single resistor connected from the 5V Trim pin (pin 7) to the +5V Output (pin 5), see Figure 3, will decrease the +5V output voltage. A resistor connected from the +5V Trim (pin 7) to the +5V Return (pin 6) will increase the +5V output voltage. See Figure 4.

Similarly, the 3.3V output can be adjusted using a single resistor connected from the +3.3V Trim (pin 10) to the +3.3V Output (pin 9) or to the +3.3V Return (pin 8). See Figures 3 and 4.





Figure 2. Trim Connections Using A Trim Pot



## **Dual Output BWR Models**

# Mixed Voltage, 5V and 3.3V, Independent Dual Output 30 Watt DC/DC Converters

Line Voltage (Volts)



### **Typical Performance Curves**

Line Voltage (Volts)

### muRata Ps Murata Power Solutions

## **Dual Output BWR Models**

Mixed Voltage, 5V and 3.3V, Independent Dual Output 30 Watt DC/DC Converters

### Options and Adaptations

### **Optional Functions**

The dual output BWR 30W DC/DC offer various electrical and mechanical options. Per the Ordering Guide on page 2, the trailing "A" (A-Series) in each part number pertains to the base part number. Part-number suffixes are added after the "A," indicating the selection of standard options. The resulting part number is a "standard product" and is available to any customer desiring that particular combination of options, as described below.

### Suffix Description

- **Blank** On/Off Control functions with positive polarity in pin 3 (5V) and pin 4 (3.3V) positions. The pin length remains at 0.2 inches (5.08 mm).
- N On/Off Control function with negative polarity in pin 3 (5V) and pin 4 (3.3V) positions.
- L1 Trim the pin length to  $0.110 \pm 0.010$  inches (2.79  $\pm 0.25$ mm). This option requires a 100-piece minimum order quantity.
- L2 Trim the pin length to  $0.145 \pm 0.010$  inches (3.68  $\pm 0.25$ mm). This option requires a 100-piece minimum order quantity.

### **Adaptations**


There are various additional configurations available on BWR 30W DC/DC's. Because designating each of them with a standard part-number suffix is not always feasable, such are designated by MPS in assigning a 5-digit "adaptation code" after the part-number suffixes. Once a configuration has been requested by a customer and created by MPS, the resulting product is available to any customer as a "standard" off-the-shelf product. Contact MPS directly if you are interested in your own set of options/adaptations. Our policy for minimum order quantities may apply.

Consequently, the following product is offered for sale: BWR-5/3-3.3/4.25-D48A-30721 BWR-5/3-3.3/4.25-D48A-30721-Y (RoHS-5)

Standard product, 48VIN, 5V/3A and 3.3V/4.25A outputs with modified pinout C22A/P60 (competitor-compatible pin out), positive common On/Off logic for both outputs, modified Trim function for 3.3Vout (no trim for 5Vout) and Common return pin for both outputs. Trimmed pin length to 0.110 inches (2.8 mm).

RoHS-5 compliance refers to the exclusion of the six hazardous substances in the RoHS specification with the exception of lead. Murata Power Solutions' RoHS-5 products use all the conforming RoHS materials, however our solders may contain lead.

### **MECHANICAL SPECIFICATIONS**



Murata Power Solutions, Inc. 129 Flanders Road, Westborough, MA 01581 U.S.A. ISO 9001 and 14001 REGISTERED



This product is subject to the following operating requirements and the Life and Safety Critical Application Sales Policy: Refer to: <u>http://www.murata-ps.com/requirements/</u>

Murata Power Solutions, Inc. makes no representation that the use of its products in the circuits described herein, or the use of other technical information contained herein, will not infringe upon existing or future patent rights. The descriptions contained herein do not imply the granting of licenses to make, use, or sell equipment constructed in accordance therewith. Specifications are subject to change without notice.