

1. General

1.1 Scope

This specification applies to type

: US783038E1S Lithium Ion Polymer Rechargeable Battery

1.2 Name and Code

1.2.1 Cell Name : US783038

1.2.2 Model Number : US783038E1S

1.2.3 Code : 49941960

1.3 Cell Shape and Weight

1.3.1 Cell Shape : Polymer

1.3.2 Size : Thickness 7.77 mm max
Width 29.4 mm max
Length(without Tab) 37.35 mm max

1.3.3 Weight : 17 g (typical)

1.4 Reference test current

1.0 ItA: 960 mA

1.5 Safety Regulation

Murata acquired UL1642

2. Performance

at room temperature, 3.0V cut off

Nominal Capacity (0.2ItA discharge)	990mAh	average capacity 3.65 V (average discharge voltage)
	3.61 Wh	
Rated Capacity (0.2ItA discharge)	960mAh	minimum capacity
	3.68 Wh	
Capacity at 0.5ItA	980mAh	average capacity
	3.64 Wh	
Capacity at 1.0ItA	960mAh	average capacity
	3.45 Wh	
Nominal Voltage	3.65 V	
Internal Impedance	65 mΩ	measured by AC1 kHz
Cycle Performance	80% of Initial capacity at 400 cycles	0.5 ItA discharge rate

*Standard Charge Condition

Charge Method : constant current / constant voltage


Charge Up Voltage : 4.2 ± 0.05 V

Charge Current : 0.672 A


Charge Time : 3 h

Ambiance Temperature: 23 deg.C


Charging Profile




Discharging Profile




Drain Capability




Discharging Profile



Discharge Temperature Performance



Cycle Performance



Cell Size (US783038E1S)

