



FEATURES

- Basic/supplementary isolation to UL60950²
- ANSI/AAMI ES60601-1
- Single and dual outputs
- UL 94V-0 package material
- SIP package style
- 5.2kVDC isolation 'Hi Pot Test'
- 3.3V, 5V, 12V, 15V & 24V inputs
- 3.3V, 5V, 9V, 12V & 15V output
- Internal SMD construction
- Fully encapsulated with toroidal magnetics
- Pin compatible with the MEV, NMV, NMK, MEJ2, & NMJ series

PRODUCT OVERVIEW

The MEJ1 series are single and dual output DC-DC converters in a 7 pin SIP package style offering an isolation and insulation upgrade path from the NMV & MEV1 series¹. The MEJ1 series has UL60950 and ANSI/AAMI ES60601-1 recognition, which makes it ideal for applications where safety and miniaturisation are of paramount importance.

SELECTION GUIDE

Order Code	Nominal Input Voltage	Output Voltage	Output Current	Input Current (Typ)	Load Regulation (Typ)	Load Regulation (Max)	Ripple & Noise (Typ) ³	Ripple & Noise (Max) ³	Efficiency (Min)	Efficiency (Typ)	MTTF
	V	V	mA		%		mVp-p		%	kHrs	
MEJ1S0303SC	3.3	3.3	303	410	8.5	11	42	55	67	70	3653
MEJ1S0305SC	3.3	5	200	400	9	10	33	45	68	71.5	3810
MEJ1S0503SC	5	3.3	303	280	6.5	8	20	40	66	69	4117
MEJ1S0505SC	5	5	200	270	5.5	7	24	40	68	72	4082
MEJ1S0509SC	5	9	111	265	4.5	5	20	40	70	74	3939
MEJ1S0512SC	5	12	83	260	4.5	7	22	40	71	74	3816
MEJ1S0515SC	5	15	66	260	5	6	22	40	72	75	3412
MEJ1S1203SC	12	3.3	303	110	6	7	25	45	69	72	3461
MEJ1S1205SC	12	5	200	110	5	6	21	40	71	74.5	3319
MEJ1S1209SC	12	9	111	105	4	5	18	40	73	76.5	3218
MEJ1S1212SC	12	12	83	105	3.5	5	19	40	73	76.5	3494
MEJ1S1215SC	12	15	66	105	4	5	16	40	73	77	3150
MEJ1S1505SC	15	5	200	90	5	6	23	45	70	74	3048
MEJ1S1509SC	15	9	111	85	4	5	18	40	72	76	2963
MEJ1S1512SC	15	12	83	85	4	5	20	40	72	76.5	2733
MEJ1S1515SC	15	15	66	85	4	5	19	35	73	76.5	2333
MEJ1S2405SC	24	5	200	55	5	6	23	40	71	75	3353
MEJ1S2409SC	24	9	111	55	4	7	17	40	72	77	2940
MEJ1S2412SC	24	12	83	55	4	5	19	40	72	78	2987
MEJ1S2415SC	24	15	66	55	3.5	5	17	40	74	78	2517
MEJ1D0503SC	5	±3.3	±151	280	6	8	19	40	67	70	4511
MEJ1D0505SC	5	±5	±100	275	5	6	23	35	69	72	4012
MEJ1D0509SC	5	±9	±55	265	4	6	16	35	69	74	3492
MEJ1D0512SC	5	±12	±42	260	4	5	15	30	72	74.5	3485
MEJ1D0515SC	5	±15	±33	260	4	5	13	35	71	75.5	2844
MEJ1D1203SC	12	±3.3	±151	110	5.5	6	19	40	70	73	3461
MEJ1D1205SC	12	±5	±100	110	4.5	5	18	40	72	75.5	3317
MEJ1D1209SC	12	±9	±55	110	4	5	15	35	73	77	2908
MEJ1D1212SC	12	±12	±42	110	3.5	5	14	30	74	76.5	2911
MEJ1D1215SC	12	±15	±33	110	4	5	11	35	73	77	2713
MEJ1D1505SC	15	±5	±100	90	4.5	5	19	40	72	75	3274
MEJ1D1509SC	15	±9	±55	85	4	5	14	35	73	76.5	3229
MEJ1D1512SC	15	±12	±42	85	3.5	5	13	35	73	77	2872
MEJ1D1515SC	15	±15	±33	85	3.5	5	20	35	73	76.5	2440
MEJ1D2405SC	24	±5	±100	55	4.5	5	19	40	72	76.5	3316
MEJ1D2409SC	24	±9	±55	55	3.5	5	17	35	73	78	3208
MEJ1D2412SC	24	±12	±42	55	3.5	5	12	35	74	78	3362
MEJ1D2415SC	24	±15	±33	55	3.5	5	14	35	74	78.5	2697

INPUT CHARACTERISTICS

Parameter	Conditions	Min.	Typ.	Max.	Units
Voltage range	Continuous operation, 3V input types	2.97	3.3	3.63	V
	Continuous operation, 5V input types	4.5	5	5.5	
	Continuous operation, 12V input types	10.8	12	13.2	
	Continuous operation, 15V input types	13.5	15	16.5	
	Continuous operation, 24V input types	21.6	24	26.4	
Input reflected ripple	3.3V input types		40		mA
	5V input types		24		
	12V & 15V input types		12		
	24V input types		8		

1. Calculated using MIL-HDBK-217 FN2 calculation model with nominal input voltage at full load.
 2. See safety approvals section for limitations of use.
 3. See ripple & noise test method.
 All specifications typical at T_a=25°C, nominal input voltage and rated output current unless otherwise specified.



For full details go to www.murata-ps.com/rohs



ISOLATION CHARACTERISTICS					
Parameter	Conditions	Min.	Typ.	Max.	Units
Isolation test voltage	Production tested for 1 second	5200			VDC
	Qualification tested for 1 second	7000			
	Qualification tested for 1 minute	5200			
Resistance	Viso= 500VDC		1		GΩ
Isolation capacitance			3		pF

OUTPUT CHARACTERISTICS					
Parameter	Conditions	Min.	Typ.	Max.	Units
Rated Power ²	T _A =-40°C to 85°C			1	W
Voltage Set Point Accuracy	See tolerance envelopes				
Line regulation	High V _{IN} to low V _{IN}		1.1	1.2	%/%

TEMPERATURE CHARACTERISTICS					
Parameter	Conditions	Min.	Typ.	Max.	Units
Specification	All output types (see safety approval section for limitations)	-40		85	°C
Storage		-55		125	
Case Temperature above ambient	MEJ1S1212SC, MEJ1S1512SC, MEJ1S2412SC, MEJ1D1215SC, MEJ1D1512SC, MEJ1D2412SC, MEJ1D2415SC, MEJ1S1215SC, MEJ1S1509SC, MEJ1S2409SC		13		
	MEJ1D1205SC, MEJ1D1209SC, MEJ1D2405SC, MEJ1D2409SC, MEJ1S1209SC, MEJ1S1515SC, MEJ1S2415SC, MEJ1D1212SC, MEJ1D1509SC, MEJ1S0515SC, MEJ1S2405SC, MEJ1D0512SC, MEJ1D0515SC, MEJ1D1515SC, MEJ1S1505SC, MEJ1D0505SC, MEJ1D0509SC, MEJ1D1203SC, MEJ1D1505SC, MEJ1S0509SC, MEJ1S0512SC, MEJ1S1205SC		17		
	MEJ1S0505SC, MEJ1S1203SC, MEJ1D0503SC, MEJ1S0303SC, MEJ1S0305SC, MEJ1S0503SC		21		
Cooling	Free air convection				

ABSOLUTE MAXIMUM RATINGS	
Short-circuit protection	48 Hours
Lead temperature 1mm from case for 10 seconds	260°C
Input voltage V _{IN} , MEJ1x03xxSC	5V
Input voltage V _{IN} , MEJ1x05xxSC	7V
Input voltage V _{IN} , MEJ1x12xxSC	15V
Input voltage V _{IN} , MEJ1x15xxSC	18V
Input voltage V _{IN} , MEJ1x24xxSC	28V

GENERAL CHARACTERISTICS					
Parameter	Conditions	Min.	Typ.	Max.	Units
Switching frequency	All types		50		kHz

APPLICATION NOTES

Minimum load

The minimum load to meet datasheet specification is 10% of the full rated load across the specified input voltage range. Lower than 10% minimum loading will result in an increase in output voltage, which may rise to typically double the specified output voltage if the output load falls to less than 5%.

Gate Drive Applications Advisory Note


For general guidance for product usage in gate drive applications please refer to [“gate drive application notes”](#).

Capacitive loading and start up

Typical start up times for this series, with a typical input voltage rise time of 2.2µs and output capacitance of 10µF, are shown in the table below. The product series will start into a capacitance of 47µF with an increased start time, however, the maximum recommended output capacitance is 10µF.

Start-up time		Start-up time		Start-up time	
µs		µs		µs	
MEJ1S0303SC	900	MEJ1S1509SC	2400	MEJ1D1205SC	1200
MEJ1S0305SC	2000	MEJ1S1512SC	2700	MEJ1D1209SC	3600
MEJ1S0503SC	500	MEJ1S1515SC	3800	MEJ1D1212SC	3900
MEJ1S0505SC	2000	MEJ1S2405SC	1700	MEJ1D1215SC	6000
MEJ1S0509SC	3200	MEJ1S2409SC	2300	MEJ1D1505SC	1200
MEJ1S0512SC	7500	MEJ1S2412SC	2200	MEJ1D1509SC	3200
MEJ1S0515SC	10500	MEJ1S2415SC	3600	MEJ1D1512SC	3300
MEJ1S1203SC	600	MEJ1D0503SC	700	MEJ1D1515SC	4800
MEJ1S1205SC	1200	MEJ1D0505SC	1600	MEJ1D2405SC	1100
MEJ1S1209SC	2900	MEJ1D0509SC	3700	MEJ1D2409SC	2000
MEJ1S1212SC	2900	MEJ1D0512SC	4200	MEJ1D2412SC	3300
MEJ1S1215SC	3900	MEJ1D0515SC	7000	MEJ1D2415SC	6400
MEJ1S1505SC	1100	MEJ1D1203SC	600		

Typical Start-Up Wave Form




Ripple & Noise Characterisation Method

Ripple and noise measurements are performed with the following test configuration.

C1	1µF X7R multilayer ceramic capacitor, voltage rating to be a minimum of 3 times the output voltage of the DC-DC converter
C2	10µF tantalum capacitor, voltage rating to be a minimum of 1.5 times the output voltage of the DC-DC converter with an ESR of less than 100mΩ at 100 kHz
C3	100nF multilayer ceramic capacitor, general purpose
R1	450Ω resistor, carbon film, ±1% tolerance
R2	50Ω BNC termination
T1	3T of the coax cable through a ferrite toroid
RLOAD	Resistive load to the maximum power rating of the DC-DC converter. Connections should be made via twisted wires

Measured values are multiplied by 10 to obtain the specified values.


Differential Mode Noise Test Schematic




TOLERANCE ENVELOPES

The voltage tolerance envelope shows typical load regulation characteristics for this product series. The tolerance envelope is the maximum output voltage variation due to changes in output loading.


DUAL 1203,1515, 2412, SINGLE 0303, 0305, 1203




DUAL 1209, 1509, 2409




DUAL 0515, SINGLE 1515, 2415




DUAL 1512, SINGLE 1212, 1512, 2412



DUAL 0512, SINGLE 1209, 1509




DUAL 1212, 1215, 2415, SINGLE 0509, 0512, 1215, 2409




TOLERANCE ENVELOPES


SINGLE 1205, 1505, 2405, 0515




DUAL 1205, 0505, 1505, 2405



DUAL 0509, 0503, SINGLE 0503, 0505




TEMPERATURE DERATING GRAPH




EFFICIENCY VS LOAD Single Output


3.3V Input




5V Input




12V Input







15V Input



24V Input




EFFICIENCY VS LOAD Dual Output



PACKAGE SPECIFICATIONS

MECHANICAL DIMENSIONS



All dimensions in mm ± 0.25 mm (inches ± 0.01). All pins on a 2.54 (0.1) pitch and within ± 0.25 (0.01) of true position.
* Pin not fitted on single output variants.

Weight: 4.3g

PIN CONNECTIONS


Single Output

Pin	Function
1	+Vin
2	-Vin
5	-Vout
7	+Vout

Dual Output

Pin	Function
1	+VIN
2	-VIN
5	-VOUT
6*	OV
7	+VOUT


TUBE OUTLINE DIMENSIONS



Unless otherwise stated all dimensions in mm ± 0.5 mm (inches ± 0.02).
Tube length : 20.669 \pm 0.079 (525mm \pm 2mm).

Tube Quantity : 25

RECOMMENDED FOOTPRINT DETAILS



* Hole not required for single output variants.
All dimensions in mm ± 0.25 mm (inches ± 0.01).



This product is subject to the following **operating requirements** and the **Life and Safety Critical Application Sales Policy**:

Refer to: <http://www.murata-ps.com/requirements/>

Murata Power Solutions, Inc. makes no representation that the use of its products in the circuits described herein, or the use of other technical information contained herein, will not infringe upon existing or future patent rights. The descriptions contained herein do not imply the granting of licenses to make, use, or sell equipment constructed in accordance therewith. Specifications are subject to change without notice.
© 2019 Murata Power Solutions, Inc.