

OBSOLETE PRODUCT

Last time buy: August 31, 2014.

[Click Here For Obsolescence Notice of February 2014.](#)

FEATURES

- Meets AMD K8 requirements
- DAC Programmable output voltage
- Power good output
- Differential remote sense
- Remote enable
- Supervisory functions
 - Latch off overcurrent
 - Short circuit protection
- Tri-state output when disabled
- Dynamic VID capability
- SMBus temperature monitor

DESCRIPTION

VRK81B100CS is designed to meet the fast load transients required by AMD 64-bit processors and is fully compliant with the latest AMD64™ processor power specifications. High efficiency of 85% at full load for reduced power dissipation to simplify system thermal management. Packaged in a compact design, VRK81B100CS is ideal for use in a wide variety of server applications.

This product is a direct replacement for VRK81B080CS.



Input Voltage	Output Voltage	Output Current	Efficiency
V (NOM.)	V	A	% (Typ.)
12	0.8-1.55	100	85

Conditions ¹	Min.	Typ.	Max.	Units	
Input voltage operating range	10.2	12.0	13.2	V	
Under voltage lockout	Turn-on threshold	6.5	6.9		7.3
	Turn-off threshold	5.4	6.0		6.6
	Hysteresis voltage	0.7	0.9		1.1
Maximum input current	Typical: 80A, 1.4VID, V _{IN} = 12V	11		A	
	Max: 80A, 1.55VID, V _{IN} = 12V		13		
No-load input current	Enable state, no load	100	200	400	mA
Disabled input current	Disabled state	10	20	50	
Enable - positive logic	On state range	0.8		5	V
	Off state range	-0.3		0.4	

OUTPUT CHARACTERISTICS

Parameter	Conditions ¹	Min.	Typ.	Max.	Units
Voltage set point	5-Bit DAC controlled	0.800		1.55	V
Line regulation		-5	0	5.0	mV
Load regulation			0.6		mΩ
Voltage total regulation DC		VID-50mV		VID+50mV	V
Ripple & noise ²	20MHz bandwidth, using recommended output capacitors		8.4		mVp-p
Current operating range		0		100	A
Efficiency	I _o = 100A, VID = 1.325V	82	84		%
	I _o = 80A, VID = 1.325V	83	85		
Turn-on time	V _{IN} present: enable to 90% V _{OUT}			50	mS
Recommended bulk output capacitance	560μF, 4V alum poly		8		EA
	10μF, 1206 X7R ceramic		25		

GENERAL CHARACTERISTICS

Parameter	Conditions ¹	Min.	Typ.	Max.	Units
Semiconductor junction temperature	Package rated to 150°C			115	°C
Material flammability	UL 94V-0				
MTBF	Calculated (RAC PRISM)		1.303		x10 ⁶ Hrs
Switching frequency	Per phase		300		KHz

TEMPERATURE CHARACTERISTICS

Parameter	Conditions ¹	Min.	Typ.	Max.	Units
Storage temperature range	Non-condensing	-40		70	°C
Operating temperature range	See derating graph	0		60	


PROTECTION CHARACTERISTICS

Parameter	Conditions ¹	Min.	Typ.	Max.	Units
Output overcurrent shutdown	Latching	115		120	A
Overvoltage Indication, CBOU	V _{OUT}		2.1		V

1. V_{IN} = 12VDC, T_A = 25°C, Airflow = 400LFM unless otherwise noted.

2. Output ripple voltage is specified when measured with recommended capacitance at the output of the converter.


THERMAL DERATING GRAPH



VID CODES

VID4	VID3	VID2	VID1	VID0	V _{OUT}
0	0	0	0	0	1.550
0	0	0	0	1	1.525
0	0	0	1	0	1.500
0	0	0	1	1	1.475
0	0	1	0	0	1.450
0	0	1	0	1	1.425
0	0	1	1	0	1.400
0	0	1	1	1	1.375
0	1	0	0	0	1.350
0	1	0	0	1	1.325
0	1	0	1	0	1.300
0	1	0	1	1	1.275
0	1	1	0	0	1.250
0	1	1	0	1	1.225
0	1	1	1	0	1.200
0	1	1	1	1	1.175
1	0	0	0	0	1.150
1	0	0	0	1	1.125
1	0	0	1	0	1.100
1	0	0	1	1	1.075
1	0	1	0	0	1.050
1	0	1	0	1	1.025
1	0	1	1	0	1.000
1	0	1	1	1	0.975
1	1	0	0	0	0.950
1	1	0	0	1	0.925
1	1	0	1	0	0.900
1	1	0	1	1	0.875
1	1	1	0	0	0.850
1	1	1	0	1	0.825
1	1	1	1	0	0.800
1	1	1	1	1	Shutdown

PART NUMBER CODING





PACKAGE SPECIFICATIONS

PIN ASSIGNMENT				
Pin	Signal	Pin	Signal	
1	GND	54	+12V _{IN}	
2	GND	53	+12V _{IN}	
3	GND	52	+12V _{IN}	
4	VID4	51	VID3	
5	VID2	50	VID1	
6	VID0	49	NC	
7	COREFB_H	48	CORERB_L	
8	PWRGD	47	CBOOT	
9	ENABLE	46 ¹	ADD 0	
10 ¹	SmDA	45 ¹	ADD 1	
11 ¹	SMC _L	44	VRMPRES_L	
12	SGND	43	+5V ALWAYS	
13	V _{DD} CORE+	42	V _{DD} CORE+	
14	V _{DD} CORE+	41	V _{DD} CORE+	
15	V _{DD} CORE+	40	V _{DD} CORE+	
16	GND	39	GND	
17	GND	38	GND	
18	GND	37	GND	
19	V _{DD} CORE+	36	V _{DD} CORE+	
20	V _{DD} CORE+	35	V _{DD} CORE+	
21	V _{DD} CORE+	34	V _{DD} CORE+	
22	V _{DD} CORE+	33	V _{DD} CORE+	
23	V _{DD} CORE+	32	V _{DD} CORE+	
24	V _{DD} CORE+	31	V _{DD} CORE+	
25	GND	30	GND	
26	GND	29	GND	
27	GND	28	GND	

1. Optional features. Substitute "NC" if option is not ordered.


PACKAGE SPECIFICATIONS (continued)

MECHANICAL DIMENSIONS



Recommended Interface Connector Options

- Typco/Elcon 283-0172-01303 (Solder Tail, Long)
- 283-0172-02303 (Solder Tail, Short)
- 284-0202-03003 (Surface Mount)



All dimensions in inches ± 0.03 (mm ± 0.25 mm).

Weight: 2.08oz (59g)

Murata Power Solutions, Inc.
11 Cabot Boulevard, Mansfield, MA 02048-1151 U.S.A.
ISO 9001 and 14001 REGISTERED



**This product is subject to the following operating requirements and the Life and Safety Critical Application Sales Policy:
Refer to: <http://www.murata-ps.com/requirements/>**

Murata Power Solutions, Inc. makes no representation that the use of its products in the circuits described herein, or the use of other technical information contained herein, will not infringe upon existing or future patent rights. The descriptions contained herein do not imply the granting of licenses to make, use, or sell equipment constructed in accordance therewith. Specifications are subject to change without notice. © 2014 Murata Power Solutions, Inc.