

SELECTION GUIDE

Discontinued



Input Voltage	Output Voltage	Output Current	Efficiency
V (NOM.)	V	A	% (TYP.)
12	0.8375 - 1.600	150	85

FEATURES

- Meets VRM 10.1 and VRM 10.2 Requirements
- DAC Programmable Output Voltage
- Power Good Output
- Differential Remote Sense
- Remote Enable
- Supervisory Functions
 - Output Overcurrent
 - Short Circuit Protection
 - Overtemperature Indicator
 - Output Current Level Signal
- Tri-state Output when Disabled
- Dynamic VID Capability

INPUT CHARACTERISTICS

Parameter	Conditions ¹	MIN.	TYP.	MAX.	Units
Input voltage operating range		11.4	12.0	12.60	V
Under voltage lockout	Turn-on threshold	9.7		11.0	
	Turn-off threshold	9.0		10.3	
	Hysteresis voltage	0.7		1.0	
Maximum input current	Typical: 130A 1.325VID Max: 150A 1.6VID		19	22	A
No-load input current	Enable state, no load	200	320	400	mA
Disabled input current	Disabled state	20	30	50	
Enable - positive logic	On state range	0.8		5.0	V
	Off state range	-0.3		0.4	

OUTPUT CHARACTERISTICS

Parameter	Conditions ¹	MIN.	TYP.	MAX.	Units
Voltage set point	6-Bit DAC controlled	0.8375		1.600	
Line regulation		-5	0	5	mV
Load regulation			1.25		mΩ
Voltage total regulation				VID-40	mV
Ripple & noise ²	20MHz bandwidth		6.4		mVp-p
Current operating range		0		150	A
Efficiency	Io = 130 Amps VID = 1.325	83	85		%
Turn-on time	V _{IN} present: enable to 90% V _{OUT}			50	mS
Transient Response ³	100A step, 100A/μS, ΔVo	115		135	
Remote Sense Compensation Range ⁴				300	
Recommended bulk output capacitance	UCC 4PS560MH11 or equivalent		14		EA

GENERAL CHARACTERISTICS

Parameter	Conditions ¹	MIN.	TYP.	MAX.	Units
Semiconductor junction temperature	Package rated to 150°C			110	°C
Material flammability	UL 94V-0				
MTBF	Calculated (RAC PRISM) @ 45°C		1.22		x10 ⁶ Hrs
Switching frequency	Per phase		300		KHz
Dimensions	3.8"L x 2.5"H x 0.870"W				
Weight			103		g


TEMPERATURE CHARACTERISTICS

Parameter	Conditions ¹	MIN.	TYP.	MAX.	Units
Storage temperature range	Non-condensing	-40		70	°C
Operating temperature range	See derating graph	0		60	




PROTECTION CHARACTERISTICS					
Parameter	Conditions ¹	MIN.	TYP.	MAX.	Units
Output overcurrent shutdown	Latching	155		205	A
Overvoltage Shutdown	Above VID	90		200	mV
Overtemperature Indicator	Non-Latching, at hot spots Worst case junction temperature		135		°C
Load Indicator	VID = 1.325, 0 A Load		0		V
	VID = 1.325, 100 A Load		2		
	VID = 1.325, 150A Load		3		

1. Vin = 12Vdc, Ta = 25°C, Airflow = 400LFM unless otherwise noted.
2. Output Ripple Voltage is specified when measured with Intel specified capacitance at the output of the converter.
3. Transient response is specified with Intel specified capacitors at the output of the converter.
4. If remote sense is not required or used, the Sense(+) and Sense(-) pins must be connected to Vo(+) and Vo(-) respectively.
5. VRM_PRES and VRM_ID are connected to Vss on the VRM.




PART NUMBER CODING



PIN ASSIGNMENT


1	VSS
2	VSS
3	VSS
4	VID4
5	VID2
6	VID0
7	Vo_sen+
8	PWRGD
9	OUTEN
10	Load Current
11	VRM ID
(5) 12	VRM_Pres
13	VO+
14	VO+
15	VO+
16	VSS
17	VSS
18	VSS
19	VO+
20	VO+
21	VO+
22	VSS
23	VSS
24	VSS
25	VO+
26	VO+
27	VO+



NOTE:
CHECK WITH MANUFACTURER FOR RECOMMENDED PCB LAYOUT.

54	VIN+
53	VIN+
52	VIN+
51	VID3
50	VID1
49	VID5
48	VO_SEN-
47	VR_HOT
46	LL0
45	LL1
44	N/C
(5) 43	N/C
42	VO+
41	VO+
40	VO+
39	VSS
38	VSS
37	VSS
36	VO+
35	VO+
34	VO+
33	VSS
32	VSS
31	VSS
30	VO+
29	VO+
28	VO+

MECHANICAL DIMENSIONS



Recommended Interface Connector Options
 Tyco/Elcon 283-0172-01303 (Solder Tail, Long)
 283-0172-02303 (Solder Tail, Short)
 284-0202-03003 (Surface Mount)

RoHS Compliance

The VR102B150CS-2C is in compliance with the European Union Directive 2002/95/EC (RoHS) with respect to the following substances: lead (Pb), cadmium (Cd), mercury (Hg), hexavalent chromium, polybrominated biphenyls (PBB) or polybrominated diphenyl ethers (PBDE).

RoHS Process Note

This product is not intended to go through a reflow solder process. See recommended interface connector options.

Murata Power Solutions, Inc.
 11 Cabot Boulevard, Mansfield, MA 02048-1151 U.S.A.
 ISO 9001 and 14001 REGISTERED



This product is subject to the following **operating requirements** and the **Life and Safety Critical Application Sales Policy**:
 Refer to: <http://www.murata-ps.com/requirements/>

Murata Power Solutions, Inc. makes no representation that the use of its products in the circuits described herein, or the use of other technical information contained herein, will not infringe upon existing or future patent rights. The descriptions contained herein do not imply the granting of licenses to make, use, or sell equipment constructed in accordance therewith. Specifications are subject to change without notice.
 © 2014 Murata Power Solutions, Inc.