

## UL TEST REPORT AND PROCEDURE

<b>Standard:</b>	UL 60950-1, 2nd Edition, 2014-10-14 (Information Technology Equipment - Safety - Part 1: General Requirements) CAN/CSA C22.2 No. 60950-1-07, 2nd Edition, 2014-10 (Information Technology Equipment - Safety - Part 1: General Requirements)
<b>Certification Type:</b>	Component Recognition
<b>CCN:</b>	QQGQ2, QQGQ8 (Power Supplies for Information Technology Equipment Including Electrical Business Equipment)
<b>Product:</b>	DC/DC Converter
<b>Model:</b>	OKX, OKX2, OKY, and OKY2 Series
<b>Rating:</b>	OKX or OKX2-A/B-C and OKY or OKY2-A/B-C  2 - Sequence/Tracking None if Pin 9 is deleted 2 if Pin 9 is installed  A - T indicating adjustable voltage range For W5: 0.75 - 3.63 Vdc For D12: 0.75 - 5.5 Vdc  B - Output Current 3: 0 to 3 A 5: 0 to 5 A 10: 0 to 10 A 16: 0 to 16 A  C - Input Voltage W5: 2.4 - 5.5 Vdc (5 Vdc nominal) 15.32 A Max. D12: 8.3 - 14 Vdc (12 Vdc nominal), 10.66 A Max.  Maximum output power not to exceed 52.8 W for W5 and 80 W for D12.
<b>Applicant Name and Address:</b>	MURATA POWER SOLUTIONS INC 11 CABOT BLVD MANSFIELD MA 02048 UNITED STATES

This is to certify that representative samples of the products covered by this Test Report have been investigated in accordance with the above referenced Standards. The products have been found to comply with the requirements covering the category and the products are judged to be eligible for Follow-Up Service under the indicated Test Procedure. The manufacturer is authorized to use the UL Mark on such products which comply with this Test Report and any other applicable requirements of UL LLC ('UL') in accordance with the Follow-Up Service Agreement. Only those products which properly bear the UL Mark are considered as being covered by UL's Follow-Up Service under the indicated Test Procedure.

The applicant is authorized to reproduce the referenced Test Report provided it is reproduced in its entirety.