

DC-DC converters for

# Gate drive applications

Designed with high dv/dt immunitity for safety & reliability

## DC-DC converters for gate drive applications

## Designed for reliability

Murata's series of DC-DC converters for gate drive applications have been designed and tested to withstand high dv/dt and DC link (continuous barrier withstand voltage) conditions without measurable breakdown within the isolation barrier.

Gate drive applications create challenging conditions which are not factored into the design of standard DC-DC converters. For this reason Murata has a range of converters specifically engineered and tested to ensure long term reliability and safety required in gate drive applications:

#### Applications

- Motor drives/motion control
- EV charging
- BESS
- Solar inverters
- Welding
- HVAC inversion systems
- Medical pump controllers
- Medical X-ray systems
- High power AC-DC conversion
- Electrical powered transportation
- (Water) pump and valve control

## MGJ1

#### Features

- Optimised bipolar output voltages for IGBT/SiC & MOSFET gate drives
- UL60950 reinforced insulation to a working voltage of 250Vrms
- ANSI/AAMI ES60601-1, 2 MOPP recognised
- Characterised CMTI >200kV/µS
- Continuous barrier withstand voltage 3kVDC
- 5.7kVDC isolation test voltage 'Hi Pot Test'
- Ultra-low isolation capacitance 3pF
- 5V, 12V, 15V & 24V inputs
- +15V/-3V, +15V/-5V, +15V/-9V
  & +19V/-5V outputs
- Creepage & clearance 9mm



## **MGJ1 SIP**

- Optimised output voltages for IGBT/Mosfet, SiC & GaN gate drives
- UL62368 reinforced insulation to a working voltage of 300Vrms
- ANSI/AAMI ES60601-1, 1 MOPP/2 MOOPs
  recognition pending
- Continuous barrier withstand voltage 2.4kVDC
- Characterised CMTI >200kV/µS
- Ultra low isolation capacitance 3pF
- 5.2kVDC isolation test voltage 'Hi Pot Test'
- 5V, 12V, 15V & 24V inputs
- +6V/-3V, +15V/-3V, +15V/-5V, +15V/-9V, +18V/-2.5V
  & +20V/-5V outputs
- Operation to 105°C
- Creepage & clearance 6mm



## MGJ2 surface mount

#### Features

- Optimised bipolar output voltages for IGBT/SiC & MOSFET gate drives
- Reinforced insulation to UL62368 recognition
  pending
- ANSI/AAMI ES60601-1 recognition pending
- Continuous barrier withstand voltage 2.5kV
- Characterised CMTI >200kV/µS
- Ultra low isolation capacitance 3pF
- 5.7kVDC isolation test voltage 'Hi Pot Test'
- 12V & 15V inputs
- +15V/-9V, +15V/-5V & +20V/-5V outputs
- Characterised partial discharge performance
- Creepage & clearance
  9mm

## MGJ2 through hole

#### Features

- Optimised bipolar output voltages for IGBT/SiC & MOSFET gate drives
- UL60950 reinforced insulation to a working voltage of 150Vrms
- ANSI/AAMI ES60601-1, 1 MOPP/2 MOOP's recognised
- Continuous barrier withstand voltage 2.4kVDC
- Characterised CMTI >200kV/µS
- 5.2kVDC isolation test voltage 'Hi Pot Test'
- Ultra-low isolation capacitance 3pF
- 5V, 12V, 15V & 24V inputs
- +15V/-3V, +15V/-5V, +15V/-8.7V, +15V/-15V,
  +17V/-9V, +18V/-2.5V, +18V/-5V, +20V/-3.5 &
  +20V/-5Voutputs
- Operation to 100°C
- Creepage & clearance
  2mm



## MGJ2B

#### Features

- Optimised bipolar output voltages for IGBT/SiC & Mosfet gate drives
- UL62368 reinforced insulation to a working voltage of 300Vrms
- ANSI/AAMI ES60601-1, 1 MOPP/2 MOOP's
  recognition pending
- Continuous barrier withstand voltage 2.4kV
- Characterised CMTI >200kV/µS
- Ultra low isolation capacitance 3pF
- 5.4kVDC isolation test voltage 'Hi Pot Test'
- 5V, 12V, 15V & 24V inputs
- +15V/-3V, +15V/-5V, +15V/-8.7V, +15V/-15V,
  +17V/-9V, +18V/-2.5V, +20V/-3.5V & +20V/-5V outputs
- Operation to 105°C
- Creepage & clearance
  6mm



- No opto feedback
- Optimised bipolar output voltages for IGBT/SiC & MOSFET gate drives
- UL60950 reinforced isolation to a working voltage of 250Vrms
- ANSI/AAMI ES60601-1, 1 MOPP/2 MOOP's recognised
- Continuous barrier withstand voltage 3kVDC
- Characterised CMTI >100kV/µS
- Isolation capacitance 15pF
- 5.2kVDC isolation test voltage 'Hi Pot Test'
- 5V, 12V & 24V input voltages
- Configurable dual outputs for all gate drive
  applications: +15V/-5V, +15V/-10V & +20V/-5V
- 105°C operating temperature
- Creepage & clearance 7mm

## MGJ6 SIP, DIP & Low Profile

#### Features

- Optimised bipolar output voltages for IGBT, silicon & silicon carbide gate drives
- Continuous barrier withstand voltage 3kVDC
- Characterised CMTI >100kV/µS
- Isolation capacitance 15pF
- Wide 2:1 input voltage ranges of 5V, 12V & 24V
- +15V/-5V, +15V/-10V & +20V/-5V outputs
- Creepage & clearance 8mm

## MGJ6 half, full and 3-phase

#### Features

- Two, three or four isolated output voltages for IGBT/SiC & Mosfet gate drives in half-bridge, full bridge & three phase configuration
- UL60950 reinforced isolation to a working voltage of 250Vrms
- ANSI/AAMI ES60601-1, 2 MOOP's recognised
- Continuous barrier withstand voltage 3kVDC
- Characterised CMTI >100kV/µS
- Isolation capacitance 15pF
- Wide 2:1 input voltage range of 5V, 12V & 24V
- Creepage & clearance 8mm



## MGJ6-14mm

#### Features

- No opto feedback
- Optimised bipolar output voltages for IGBT/SiC & MOSFET gate drives
- UL60950 reinforced isolation to a working voltage of 690Vrms
- IEC 61800-5-1 to a working voltage of 690Vrms
- Continuous barrier withstand voltage 3kVDC
- Characterised CMTI >100kV/µS
- Isolation capacitance 13pF
- Creepage & clearance 14mm
- 5V, 12V & 24V input voltages
- Configurable dual outputs for all gate drive applications: +15V/-5V, +15V/-10V & +20V/-5V
- 105°C operating temperature

## MGN1

- Optimised output voltages designed to meet leading GaN devices requirements
- Reinforced insulation to UL62368 recognition pending
- Continuous barrier withstand voltage 1.1kV
- Characterised CMTI >200kV/µS
- Ultra low isolation capacitance 2.5pF
- 3kVAC isolation test voltage 'Hi Pot Test'
- 5V & 12V inputs
- +8V, +12V & +6V/-3V outputs
- Characterised partial discharge performance
- Operation up to 105°C
- Creepage & clearance 6.5mm

### NXE1

#### Features

- 3.3V & 5V inputs
- 3.3V & 5V outputs
- UL60950 reinforced isolation to a working voltage of 125Vrms & basic insultaion to a working voltage of 250Vrms
- ANSI/AAMI ES60601-1, 1 MOPP recognised to a working voltage of 250Vrms
- Isolation capacitance 3pF
- 3kVDC isolation test voltage 'Hi Pot Test'
- 85°C operating temperature
- Creepage 2.5mm & clearance 2mm
- Substrate embedded transformer
- Short circuit protection
- Halogen free

## NXE2

#### Features

- 5V & 12V inputs
- 5V, 12V & 15V outputs
- UL60950 reinforced isolation to a working voltage of 125Vrms & basic insultaion to a working voltage of 250Vrms
- ANSI/AAMI ES60601-1, 1 MOOP recognised to
  a working voltage of 250Vrms
- Isolation capacitance 2.1pF
- 3kVDC isolation test voltage 'Hi Pot Test'
- Up to 100°C operating temperature
- Creepage 2.5mm & clearance 2mm
- Substrate embedded transformer
- Short circuit protection
- Halogen free



### NXJ1

#### Features

- 3.3V, 5V & 12V inputs
- 3.3V, 5V, 12V & 15V outputs
- UL60950 reinforced isolation to a working voltage of 200Vrms & basic insultaion to a working voltage of 250Vrms
- ANSI/AAMI ES60601-1, 1 MOPP recognised to a working voltage of 250Vrms
- Isolation capacitance up to 2.5pF
- 4.2kVDC isolation test voltage 'Hi Pot Test'
- Up to 110°C operating temperature
- Creepage & clearance 4mm
- Substrate embedded transformer
- Short circuit protection
- Halogen free



## NXJ2

- 5V, 12V & 24V inputs
- 5V, 12V & 15V outputs
- UL60950 reinforced isolation to a working voltage of 250Vrms
- ANSI/AAMI ES60601-1, 1 MOPP & 2 MOOP
  recognised to a working voltage of 250Vrms
- Isolation capacitance up to 2.4pF
- 5.2kVDC isolation test voltage 'Hi Pot Test'
- Up to 95°C operating temperature
- Creepage & clearance 5mm
- Substrate embedded transformer
- Short circuit protection
- Halogen free



## Cat.no. DC-DCGD23\_1 DC-DC for Gate Drives

Power	Description	Isolation capacitance	Package type	Murata series
1 Watt	1 channel, embedded transformer	ЗрF	SMD, low profile	MGJ1
1 Watt	1 channel, fixed outputs	2.5pF	SMD, low profile	MGN1
1 Watt	1 channel, fixed outputs	ЗрF	SMD, low profile	NXE1
1 Watt	1 channel, fixed outputs	2.5pF	SMD, low profile	NXJ1
1 Watt	1 channel, configurable outputs	ЗрF	THT, SIP7	MGJ1 SIP
2 Watt	1 channel, configurable outputs	ЗрF	THT, SIP7	MGJ2B
2 Watt	1 channel, fixed outputs	2.1pF	SMD, low profile	NXE2
2 Watt	1 channel, fixed outputs	2.4pF	SMD, low profile	NXJ2
2 Watt	1 channel, fixed outputs	4pF	THT, SIP7	MGJ2
2 Watt	1 channel, fixed outputs	ЗрF	SMD	MGJ2 SM
3 Watt	1 channel, configurable outputs	15pF	SMD	MGJ3T
6 Watt	1 channel, configurable outputs	15pF	SMD	MGJ6T
6 Watt	1 channel, fixed outputs	15pF	SMD low profile, THT SIP + DIP	MGJ6-LP, -SIP, -DIP
6 Watt	2 channels for Half-Bridge	15pF	SMD	MGJ6H
6 Watt	3 channels for Full-Bridge	15pF	SMD	MGJ6F
6 Watt	4 channels for 3-Bridge	15pF	SMD	MGJ6P
6 Watt	1 channel, 690VAC reinforced isolation	13pF	SMD	MGJ6W

⊠ info@murata.com ⊕ www.murata.com

## Global locations

For details please visit www.murata.com

## Cat.no. DC-DCGD23\_1 DC-DC for Gate Drives



## Note

#### 1 Export Control

#### For customers outside Japan:

No Murata products should be used or sold, through any channels, for use in the design, development, production, utilization, maintenance or operation of, or otherwise contribution to (1) any weapons (Weapons of Mass Destruction [nuclear, chemical or biological weapons or missiles] or conventional weapons) or (2) goods or systems specially designed or intended for military end-use or utilization by military end-users.

#### For customers in Japan:

For products which are controlled items subject to the "Foreign Exchange and Foreign Trade Law" of Japan, the export license specified by the law is required for export. Please contact our sales representatives or product engineers before using the products in this catalog for the applications listed below, which require especially high reliability for the prevention of defects which might directly damage a third party's life, body or property, or when one of our products is intended for use in applications other than those specified in this catalog.

- Aircraft equipment
- Undersea equipment
- ③ Medical equipment
- ④ Traffic signal equipment
- 5 Data-processing equipment
- Aerospace equipment
- ⑦ Power plant equipment
- (8) Transportation equipment (vehicles, trains, ships, etc.)
- Disaster prevention / crime prevention equipment
- Application of similar complexity and/or reliability requirements to the applications listed above

Product specifications in this catalog are as of December 2023. They are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. If there are any questions, please contact our sales representatives or product engineers.

Please read rating and & CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.

5 This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Please note that unless otherwise specified, we shall assume no responsibility whatsoever for any conflict or dispute that may occur in connection with the effect of our and/or a third party's intellectual property rights and other related rights in consideration of your use of our products and/or information described or contained in our catalogs. In this connection, no representation shall be made to the effect that any third parties are authorized to use the rights mentioned above under licenses without our consent.

No ozone depleting substances (ODS) under the Montreal Protocol are used in our manufacturing process.



### Murata Manufacturing Co., Ltd.

⊠ info@murata.com ⊕ www.murata.com