

AC/DC Front End Power Supply

PRODUCT OVERVIEW

The C1U-W-1200 is a 1200 Watt universal AC input, power-factor-corrected (PFC) front-end power supply for general applications. The main output is 12V with a standby output of either 5V or 3.3V. Packaged in a 1U low profile chassis, it is designed to deliver reliable bulk power to servers, workstations, storage systems or any 12V distributed power architecture systems requiring high power density. The highly efficient electrical and thermal design with internal cooling fans supports reliable operation conditions. The C1U-W-1200 is designed to autorecover from overtemperature faults.



FEATURES

- 1200W (110/220Vac) Output power
- 12V Main output,3.3V or 5V standby output
- Dimensions: 5.5" x 14.2" x 1.67"
- 9.2 Watts per cubic inch density
- N+1 redundancy capable (up to 3 in parallel)
- Active current sharing on main output
- Overvoltage, overcurrent, overtemperature protection
- Internal cooling fans
- RoHS compliant

SELECTION GUIDE				
Part Number	Power Output Universal Line	Main Output	Standby Output	Airflow
C1U-W-1200-12-TA1C	1200W	12V	5V	Front to back
C1U-W-1200-12-TC1C	1200W	12V	3.3V	Front to back
C1U-W-1200-12-TA2C	1200W	12V	5V	Back to front
C1U-W-1200-12-TC2C	1200W	12V	3.3V	Back to front

INPUT CHARACTERISTICS					
Parameter	Conditions	Min.	Тур.	Max.	Units
Input Voltage Operating Range		90	115/230	264	Vac
Input Frequency		47	55	63	Hz
Turn-on Input Voltage	Ramp up	78.5		86.5	Vac
Turn-off Input Voltage	Ramp down	70.5		78	
Maximum Input Current				15	Arms
Inrush Current				90	Apk
Power Factor	Output load >90%	95%			
	Output load >50%	75%			

OUTPUT V	OLTAGE CHARACTERISTIC	S				
Output Voltage	Parameter	Conditions	Min.	Тур.	Max.	Units
	Voltage Set Point Accuracy			12.12		Vdc
	Line and Load Regulation		11.75		12.48	vuc
12V	Ripple Voltage & Noise ¹	20MHz Bandwidth			120	mV p-p
	Output Current		0		98.3	Α
	Load Capacitance				40000	μF
	Voltage Set Point Accuracy			3.3		Vdc
	Line and Load Regulation		3.2		3.4	Vuc
3.3Vsb	Ripple Voltage & Noise ¹	20MHz Bandwidth			33	mV p-p
	Operating Range		0		6	Α
	Load Capacitance				1530	μF
	Voltage Set Point Accuracy			5		Vdc
5Vsb	Line and Load Regulation		4.85		5.15	vuc
	Ripple Voltage & Noise1	20MHz Bandwidth			50	mV p-p
	Operating Range		0		4	Α
	Load Capacitance				1530	μF

¹ Ripple and noise are measured with 0.1 uF of ceramic capacitance and 2 x 270 uF of OSCON capacitance on each of the power supply outputs. A short coaxial cable with 50ohm scope termination is used. See Ripple Test Setup diagram.









AC/DC Front End Power Supply

OUTPUT CHARACTERISTICS					
Parameter	Conditions	Min.	Тур.	Max.	Units
Remote Sense	Compensates for up to 0.12V of lead drop with or without remote sense connected	190			mV
Efficiency	220Vac		90.6		%
Output Rise Monotonicity	Overshoot less than 10% for all outputs, no	voltage negative	between 10% to	95% during rar	np up
Charles Time	AC ramp up		1.5		S
Startup Time	PS_On activated		150		ms
	12V Ramp 1A/µs			±600	
Transient Response	3.3Vsb Ramp 1A/µs			±165	mV
	5Vsb Ramp 1A/μs			±250	
Current sharing accuracy (up to 3 in parallel)	At 100% load			±10	%
Holdup Time		20			ms

ENVIRONMENTAL CHARACTERISTICS							
Parameter	Conditions	Min.	Тур.	Max.	Units		
Storage Temperature Range	Non-condensing	-40		70	°C		
Operating Temperature Range		0		50			
Operating Humidity	Non-condensing	10		90	%		
Storage Humidity		5		90	70		
Shock	30G non operating						
Sinusoidal Vibration	0.5G, 5 – 500 Hz						
MTBF	Telcordia SR-332 @ 30°C	200K			hrs		
WIDF	Demonstrated	200K			hrs		
Safety Approvals	UL 60950-1, 2nd Ed.	CAN/CSA C22.2 No. 60950-1-07, 2nd Ed. UL 60950-1, 2nd Ed. IEC 60950-1:2005 (2nd Edition); EN 60950-1:2006 +A11					
Input Fuse	Power Supply has internal 20A/2	Power Supply has internal 20A/250V fast blow fuse on the AC line input					
Material Flammability	UL 94V-0	UL 94V-0					
Switching Frequency	90KHz for Boost PFC Converter 165KHz for Main Output Converter 200KHz for Standby Output Converter						
Weight	5.7 lbs (2.6kg)	5.7 lbs (2.6kg)					

PROTECT	ION CHARACTERISTICS					
Output Voltage	Parameter	Conditions	Min.	Тур.	Max.	Units
	Overtemperature	Autorestart	55		65	°C
12V	Overvoltage	Latching	13		14	V
120	Overcurrent	Latching	107		122	Α
3.3Vsb	Overvoltage	Latching	3.57		4.02	V
3.3780	Overcurrent	Latching	6.5		8	Α
T\/ab	Overvoltage	Latching	5.6		6	V
5Vsb	Overcurrent	Latching	5		7	Α


ISOLATION CHARACTERISTICS							
Parameter	Conditions	Min.	Тур.	Max.	Units		
Insulation Safety Rating / Test Voltage	Input to Output - Reinforced	3000			Vrms		
	Input to Chassis - Basic	1500			Vrms		
Isolation	Output to Chassis						
	Output to Output						
Grounding	Main Output Return and Standby Output R capacitor is connected between Return ar the System Chassis.	Main Output Return and Standby Output Return are connected internally. 100kΩ resistor parallel with 100nF capacitor is connected between Return and power supply chassis. Main Output Return should be connected to the System Chassis.					



AC/DC Front End Power Supply


STATUS INDICATORS AND CONTROL SIGNALS		
Status	Conditions	Description
	Off	No AC input to all PS
LED	Flashing Yellow	Power Supply Failure
LED	Flashing Green	Main Output Absent
	Green	Power Supply Good
		Short PS_ON to GND (required)
PS_ON	To enable main output	Short SENSE+ to 12 main at point of load (optional for better regulation)
		Short SENSE- to Output GND at point of load (optional for better regulation)

EMISSIONS AND IMMUNITY		
Characteristic	Standard	Compliance
Input Current Harmonics	IEC/EN 61000-3-2	Complies
Voltage Fluctuation and Flicker	IEC/EN 61000-3-3	Complies
Conducted Emissions	FCC 47 CFR Part 15/CISPR 22/EN55022	Class A, 6dB margin
Radiated Emissions	FCC 47 CFR Part 15/CISPR 22/EN55022	Class A, 6dB margin
		4kV contact discharge
ESD Immunity	IEC/EN 61000-4-2	8kV operational air discharge
		15kV non-operational air discharge
Radiated Field Immunity	IEC/EN 61000-4-3	Complies
Electrical Fast Transients/Burst Immunity	IEC/EN 61000-4-4	Complies
Surge Immunity	IEC/EN 61000-4-5	1kV/2kV, Performance Criteria B
RF Conducted Immunity	IEC/EN 61000-4-6	3 Vac, 80% AM, 1kHz, Performance Criteria A
Magnetic Field Immunity	IEC/EN 61000-4-8	3 A/m
Voltage Dips, Interruptions	IEC/EN 61000-4-11	Complies





AC/DC Front End Power Supply



CURRENT SHARING NOTES


Main Output: Current sharing is achieved using the active current share method. (See wiring diagram for connection details.)

The total combined load must be below 1200W at startup. Current sharing can be achieved with or without remote sense connected to the common load. V_SB outputs can be tied together for redundancy but total combined output power must not exceed 20W. The V_SB output has internal ORing MOSFET for additional redundancy / internal short protection.

The current share pin 5 is a connection between the two units. It is input and/or output as the voltage on the line controls the current share. A power supply will respond to a change in this voltage but a power supply can also change the voltage depending on the load drawn from it. On a single unit this would read 8V at 100% load. For two units sharing load then this should read 4V for perfect current sharing.

Up to 3 units can be paralleled together. Please consult your Murata sales representative if operation with more than three units in parallel is needed.

AC/DC Front End Power Supply



Murata Power Solutions, Inc.
11 Cabot Boulevard, Mansfield, MA 02048-1151 U.S.A.
ISO 9001 and 14001 REGISTERED

2-Pole terminal Block for AC Line and Neutral Stud on Chassis for earth

13

14

15

16

GND

GND

GND

GND

12V Main Output GND



This product is subject to the following <u>operating requirements</u> and the <u>Life and Safety Critical Application Sales Policy</u>:

A Refer to: http://www.murata-ps.com/requirements/

Murata Power Solutions, Inc. makes no representation that the use of its products in the circuits described herein, or the use of other technical information contained herein, will not infringe upon existing or future patent rights. The described herein do not imply the granting of licenses to make, use, or sell equipment constructed in accordance therewith. Specificans are subject to change without notice.

Output Terminal M5 Studs

Signal Connector