

# **LME Series**

## Isolated 250mW Single Output DC-DC Converters



### **FEATURES**

- Single output rail
- 1kVDC isolation 'Hi Pot Test'
- High efficiency for low power applications
- SIP & DIP package styles
- 5V & 12V inputs
- 5V, 9V, 12V & 15V outputs
- Internal SMD construction
- No external components required
- MTTF up to 2.7 million hours
- Custom solutions available
- Pin compatible with CME, CRE1, NKE, NME, NML, MEE1 & MEE3 series

#### **PRODUCT OVERVIEW**

The LME series of DC-DC converters are optimised for low-power operation. They are ideally suited to generating a negative supply where only a positive rail exists.

SELECTION (	GUIDE							
Order Code	Nominal Input Voltage	Output Voltage	Output Current	Efficiency	Isolation Capacitance	MTTF1	Package Style	Recommended Alternative
	V	V	mA	%	pF	kHrs		
			D	iscontin	ued			
LME0505SC	5	5	50	70	29	2279	SIP	CRE1S0505SC
LME0505DC	5	5	50	70	29	2279	DIP	CME0505DC
LME0509SC	5	9	28	75	37	1139	SIP	NME0509SC
LME0509DC	5	9	28	75	37	1139	DIP	NME0509SC
LME0512SC	5	12	21	75	41	624	SIP	CME0512SC
LME0512DC	5	12	21	75	41	624	DIP	NME0512DC
LME0515SC	5	15	16	75	40	357	SIP	CRE1S0515SC
LME0515DC	5	15	16	75	40	357	DIP	NME0515SC
LME1205SC	12	5	50	70	38	536	SIP	CRE1S1205SC
LWE1205DC	12	5	50	70	38	536	DIP	NME1205DC
LME1209SC	12	9	28	75	37	1139	SIP	NKE1209SC
LME1209DC	12	9	28	75	40	434	DIP	MEE1S1209DC
LME1212SC	12	12	21	75	43	330	SIP	CRE1S1212SC
LME1212DC	12	12	21	75	43	330	DIP	NME1212DC
LME1215SC	12	15	16	75	45	237	SIP	CRE1S1212SC
LME1215DC	12	15	16	75	45	237	DIP	NME1215SC

INPUT CHARACTERISTICS					
Parameter	Conditions	Min.	Тур.	Max.	Units
Voltago rongo	Continuous operation, 5V input types	4.5	5.0	5.5	W
Voltage range	Continuous operation, 12V input types	10.8	12	13.2	V

GENERAL CHARACTERISTICS					
Parameter	Conditions	Min.	Тур.	Max.	Units
Switching frequency	All input types		100		kHz

OUTPUT CHARACTERISTICS						
Parameter	Conditions	Min.	Тур.	Max.	Units	
Rated Power	T <sub>A</sub> =0°C to 70°C, see derating graph			0.25	W	
Voltage Set Point Accuracy	See tolerance envelope					
Line regulation	High V <sub>IN</sub> to low V <sub>IN</sub>		1.0	1.2	%/%	
Load Pagulation	10% load to rated load, 5V output types			15	%	
Load Regulation	10% load to rated load, all other types			10	70	
Ripple and Noise	BW=DC to 20MHz, all output types			100	mV p-p	

ISOLATION CHARACTERISTICS						
Parameter	Conditions	Min.	Тур.	Max.	Units	
Isolation test voltage	Flash tested for 1 second	1000			VDC	
Resistance	Viso= 500VDC	1			GΩ	





Calculated using MIL-HDBK-217F with nominal input voltage at full load.

All appointment voltage at T. 2000, persion input voltage and rated output aurent.

 $All \ specifications \ typical \ at \ T_A=25^{\circ}C, \ nominal \ input \ voltage \ and \ rated \ output \ current \ unless \ otherwise \ specified.$ 



# **LME Series**

# Isolated 250mW Single Output DC-DC Converters

TEMPERATURE CHARACTERISTICS					
Parameter	Conditions	Min.	Тур.	Max.	Units
Specification	All output types (see safety approval section for limitations)	0		70	00
Storage		-50		130	
Cooling	Free air convection				

ABSOLUTE MAXIMUM RATINGS	
Lead temperature 1.5mm from case for 10 seconds	260°C
Wave Solder	Wave Solder profile not to exceed the profile recommended in IEC 61760-1 Section 6.1.3. Please refer to application notes for further information.
Input voltage V <sub>IN</sub> , LME05 types	7V
Input voltage V <sub>IN</sub> , LME12 types	15V



#### **TECHNICAL NOTES**

#### **ISOLATION VOLTAGE**

'Hi Pot Test', 'Flash Tested', 'Withstand Voltage', 'Proof Voltage', 'Dielectric Withstand Voltage' & 'Isolation Test Voltage' are all terms that relate to the same thing, a test voltage, applied for a specified time, across a component designed to provide electrical isolation, to verify the integrity of that isolation.

Murata Power Solutions LME series of DC-DC converters are all 100% production tested at their stated isolation voltage. This is 1kVDC for 1 second.

A question commonly asked is, "What is the continuous voltage that can be applied across the part in normal operation?"

For a part holding no specific agency approvals, such as the LME series, both input and output should normally be maintained within SELV limits i.e. less than 42.4V peak, or 60VDC. The isolation test voltage represents a measure of immunity to transient voltages and the part should never be used as an element of a safety isolation system. The part could be expected to function correctly with several hundred volts offset applied continuously across the isolation barrier; but then the circuitry on both sides of the barrier must be regarded as operating at an unsafe voltage and further isolation/insulation systems must form a barrier between these circuits and any user-accessible circuitry according to safety standard requirements.

#### REPEATED HIGH-VOLTAGE ISOLATION TESTING

It is well known that repeated high-voltage isolation testing of a barrier component can actually degrade isolation capability, to a lesser or greater degree depending on materials, construction and environment. The LME series has toroidal isolation transformers, with no additional insulation between primary and secondary windings of enamelled wire. While parts can be expected to withstand several times the stated test voltage, the isolation capability does depend on the wire insulation. Any material, including this enamel (typically polyurethane) is susceptible to eventual chemical degradation when subject to very high applied voltages thus implying that the number of tests should be strictly limited. We therefore strongly advise against repeated high voltage isolation testing, but if it is absolutely required, that the voltage be reduced by 20% from specified test voltage.

This consideration equally applies to agency recognised parts rated for better than functional isolation where the wire enamel insulation is always supplemented by a further insulation system of physical spacing or barriers.


#### **ROHS COMPLIANT INFORMATION**



This series is compatible with RoHS soldering systems with a peak wave solder temperature of 260°C for 10 seconds. Please refer to <u>application notes</u> for further information. The pin termination finish on the SIP package type is Tin Plate, Hot Dipped over Matte Tin with Nickel Preplate. The DIP types are Matte Tin over Nickel Preplate. Both types in this series are backward compatible with Sn/Pb soldering systems.

For further information, please visit www.murata.com/en-global/products/power/rohs

# PART NUMBER STRUCTURE




#### **APPLICATION NOTES**

#### Minimum Load


The minimum load to meet datasheet specification is 10% of the full rated load across the specified input voltage range. Lower than 10% minimum loading will result in an increase in output voltage, which may rise to typically double the specified output voltage if the output load falls to less than 5%.

# TOLERANCE ENVELOPES

The voltage tolerance envelope shows typical load regulation characteristics for this product series. The tolerance envelope is the maximum output voltage variation due to changes in output loading.




### TEMPERATURE DERATING GRAPH
















# **LME Series**

## Isolated 250mW Single Output DC-DC Converters

#### DISCLAIMER

Unless otherwise stated in the datasheet, all products are designed for standard commercial and industrial applications and NOT for safety-critical and/or life-critical applications.

Particularly for safety-critical and/or life-critical applications, i.e. applications that may directly endanger or cause the loss of life, inflict bodily harm and/or loss or severe damage to equipment/property, and severely harm the environment, a prior explicit written approval from Murata is strictly required. Any use of Murata standard products for any safety-critical, life-critical or any related applications without any prior explicit written approval from Murata shall be deemed unauthorised use.

These applications include but are not limited to:

- Aircraft equipment
- Aerospace equipment
- Undersea equipment
- Power plant control equipment
- Medical equipment
- Transportation equipment (automobiles, trains, ships, etc.)
- Traffic signal equipment
- Disaster prevention / crime prevention equipment
- Data Processing equipment

Murata makes no express or implied warranty, representation, or guarantee of suitability, fitness for any particular use/purpose and/or compatibility with any application or device of the buyer, nor does Murata assume any liability whatsoever arising out of unauthorised use of any Murata product for the application of the buyer. The suitability, fitness for any particular use/purpose and/or compatibility of Murata product with any application or device of the buyer remain to be the responsibility and liability of the buyer.

Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm, and take appropriate remedial actions. Buyer will fully indemnify and hold Murata, its affiliated companies, and its representatives harmless against any damages arising out of unauthorised use of any Murata products in any safety-critical and/or life-critical applications.

Remark: Murata in this section refers to Murata Manufacturing Company and its affiliated companies worldwide including, but not limited to, Murata Power Solutions.



This product is subject to the following <u>operating requirements</u> and the <u>Life and Safety Critical Application Sales Policy</u>:

Refer to: https://www.murata.com/en-eu/products/power/requirements

Murata Power Solutions (Milton Keynes) Ltd. makes no representation that the use of its products in the circuits described herein, or the use of other technical information contained herein, will not infringe upon existing or future patent rights. The descriptions contained herein do not imply the partining of licenses to make, use, or sell equipment constructed in accordance therewith. Specifications are subject to change without notice.