



FEATURES

- 8000v Isolation Test Voltage
- No External Parts Required
- Remote On/Off
- Low-Barrier Capacitance
- RoHS Compliant
- Synchronizable

APPLICATIONS

- Biomedical Data Acquisition
- Industrial Process Equipment
- Data Acquisition
- Test Equipment
- Portable Equipment

DESCRIPTION

The PWR1726AC is a single-channel, bipolar output DC/DC/ converter designed for those applications where high-isolation voltage and low-barrier capacitance are critical for system reliability and integrity.

Calculated mean-time-to-failure (MTTF) is in excess of 100 years at an ambient temperature of +25°C and at rated output power. The performance of the PWR1726AC is not derated over its entire specified temperature range of -25°C to +85°C.

Synchronization of the PWR1726AC may be accomplished simply by connecting the Sync-In pin of one unit to the Sync-In pin of another unit. Up to 8 converters may be synchronized in this manner.

The PWR1726AC provides a plus and minus output voltage that is approximately equal to the magnitude of the input voltage. The unit operates over an input voltage range of 7VDC to 16VDC.

Each PWR1726AC isolation barrier is tested per the method set forth by UL544, VDE750, and CSA C22.2.




COMMON SPECIFICATIONS

Specifications typical at $T_A = +25^{\circ}\text{C}$, $V_{IN} = 15\text{VDC}$, $I_{LOAD} = \pm 50\text{mA}$ and in free-running mode unless otherwise noted.

PARAMETER	CONDITIONS	MIN	TYP	MAX	UNITS
INPUT					
Rated Voltage			12		V _{DC}
Voltage Range		7		16	V _{DC}
Input Current	$I_{LOAD} = 0$		30		mA
	$I_{LOAD} = \text{Rated Load}$		145	165	mA
	Short Circuit		115		mA
Ripple Current	$I_{LOAD} = \text{Rated Load}$		15		mAp-p
ISOLATION					
Voltage Rated Continuous		3500			V _{rms}
AC, 60Hz		5000			V _{DC}
DC		8000			V _{pk}
Test Voltage	60sec, 60Hz				GΩ
Resistance			10		pF
Capacitance			10		μA
Leakage Current	$V_{ISO} = 240\text{VAC}$, 60Hz		1	2	
OUTPUT					
Rated Voltage	$I_{LOAD} = \text{Rated Load}$		±15		V _{DC}
Voltage Range	$I_{LOAD} = \text{Rated Load}$	±14.25		±15.75	V _{DC}
	$I_{LOAD} = 0\text{mA}$	±16.0		±18.0	V _{DC}
Rated Current	Balanced Loads		±50		mA
Current Range	Balanced Loads	0		±90	mA
	Single Ended	0		180	mA
Line Regulation	$7\text{VDC} < V_{IN} < 18\text{VDC}$		1.16		mV/mV
Load Regulation	No Load $< I_{OUT} < \pm 50\text{mA}$			0.3	%/mA
Ripple Voltage	BW = DC to 10MHz				mVp-p
	$I_{LOAD} = 0$		15		mVp-p
	$I_{LOAD} = \text{Rated Load}$		50		(referenced to common)
GENERAL					
MTTF	Calculated per MIL - HDBK - 217 Rev. E Ground, Benign 25° C		1.2		MHr
Switching Frequency			120		kHz
TEMPERATURE					
Specification		-25	+25	+85	°C
Operation		-40		+100	°C
Storage		-55		+110	°C

NOTE: Other input and output voltages may be available upon request. Please consult the factory.

MECHANICAL



PIN CONNECTIONS	
1	-Vout
14	-Vin
15	Sync-In
16	+Vin
18	REMOTE ON/OFF
30	COMMON
32	+Vout

NOTES:

All dimensions are in inches (millimeters).

GRID: 0.100 inches (2.54 millimeters)

PIN PLACEMENT TOLERANCE: ±0.015"


To ensure proper operation, the remote on/off pin should be connected to +Vin when the unit is on.

MATERIAL: Units are encapsulated in a low thermal resistance molding compound which has excellent chemical resistance, wide operating temperature range, and good electrical properties under high humidity environments. The encapsulant and outer shell of the unit have UL94V-0 ratings. Lead material is brass; lead finish is matte Sn (100 microinches minimum) over Ni (40-80 microinches)

ABSOLUTE MAXIMUM RATINGS

Input Voltage16Vdc
 Output Short-Circuit DurationContinuous
 Internal Power Dissipation..... 2W
 Lead Temperature (soldering, 10 seconds max)+300°C


ORDERING INFORMATION




TYPICAL PERFORMANCE CURVES

TA=+25°C, Rated Input Voltage, Rated Output Current unless otherwise noted

OUTPUT VOLTAGE VS. OUTPUT CURRENT



OUTPUT VOLTAGE VS. INPUT VOLTAGE



THROUGH-HOLE SOLDERING INFORMATION

These devices are intended for wave soldering or manual soldering. **They are not intended to be subject to surface mount processes under any circumstances.**

The normal wave soldering process can be used with these devices where the device is subjected to a maximum wave temperature of 260°C for a period of no more than 10 seconds. Within this time and temperature range, the integrity of the device's plastic body will not be compromised and internal temperatures within the converter will not exceed 175°C. Care should be taken to control manual soldering limits identical to that of wave soldering.

SYNCHRONIZATION INFORMATION

The unit may be synchronized to an external clock. Recommended frequency is a minimum of 110kHz and a maximum of 250kHz. The sync signal must be a square wave pulse with a peak of 7.5V min to 12V max, the amplitude being referenced to -Vin.

Murata Power Solutions, Inc.
 129 Flanders Road, Westborough, MA 01581 U.S.A.
 ISO 9001 and 14001 REGISTERED



This product is subject to the following [operating requirements](http://www.murata-ps.com/requirements/) and the [Life and Safety Critical Application Sales Policy](#): Refer to: <http://www.murata-ps.com/requirements/>

Murata Power Solutions, Inc. makes no representation that the use of its products in the circuits described herein, or the use of other technical information contained herein, will not infringe upon existing or future patent rights. The descriptions contained herein do not imply the granting of licenses to make, use, or sell equipment constructed in accordance therewith. Specifications are subject to change without notice. © 2018 Murata Power Solutions, Inc.