

---

**Technical Data of Crystal Unit**

---

---

**MURATA Part No.: XRCGB16M000FXN20R0**

---

---

**Applied to TLSR8267**

---

Oscillation circuit is compatible to below IC.


TLSR8262  
TLSR8266  
TLSR8269  
TLSR86xx

## Evaluation Data of Oscillation Circuit for Crystal Unit

muRata

## Murata's recommendation 推奨回路定数

Item		Condition	
IC name		IC名	
Parts Number of		村田品名	
Circuit Parameter		External	
load capacitance		负载电容 CL1	10pF
Feedback resistance		负载电容 CL2	10pF
Damping resistance		反馈电阻 Rf	No mount
Supply Voltage Range		阻尼电阻 Rd	0ohm
Temp. Range		电源电压范围	5V
		温度范围	-30 to 85deg.C



## Characteristics of oscillation circuit on above condition 推奨定数での発振回路特性

Circuit Characteristics 特性	Value 測定値	Remarks 備考
<b>Center Frequency and Difference</b> 起振回路上起振频率与偏差量 (*1) (Typical sample at Vdd=5V,+25deg.C)	15.999980 [MHz] -1 [ppm]	Oscillating frequency and its shift against nominal frequency 在起振回路上的频率以及相对于公称频率之间的偏差量
<b>Load Capacitance on your PCB</b> 负载容量值 (Typical sample at Vdd=5V,+25deg.C)	8.2 [pF]	This value shows load capacitance the evaluated circuit has 在起振回路上等价于连接在谐振器两端的容量
<b>Negative Resistance and Oscillation margin</b> 负性电阻/起振余裕度 (at Vdd=5V,+25deg.C)	[-R] 1641 [Ω] Ratio 6.1 [Times]	The details is explained in page 2 详细内容参见下页说明
<b>Drive Level</b> 激励功率 (Typical sample at Vdd=5V,+25deg.C)	53 [uW]	Drive power of crystal under circuit condition 起振回路在工作状态下谐振器消耗的功率
<b>Oscillating Voltage</b> 起振电压 (Typical sample at Vdd=5V,+25deg.C)	VINp-p 1.0 [V] VOUtp-p 1.0 [V]	Swing level at input side 输入端起振振幅 (VIN_H - VIN_L) Swing level at output side 输出端起振振幅 (VOUT_H - VOUT_L)
<b>Oscillation Start up Time</b> 启动时间 (*2) (Typical sample at Vdd=5V,+25deg.C)	29.98 [ms]	The time takes steady amplitude of Vout(Xout) 达到稳定状态振幅所需要时间

\*1 Frequency difference means the oscillating frequency difference between your PCB and Murata's frequency sorting circuit.  
 频率偏差指在贵公司基板上的测定频率与本公司标准回路上测定频率间的偏差。

\*2 The measurement results is affected by the rise-up characteristics of supplied voltage on your PCB.  
 测定结果受安装基板上电源启动方式的影响。

## Notes

The characteristics of the crystal oscillation circuit is affected by the circuit constants and actual mounting conditions and so on. Therefore, it is possible to get the different results from above one due to the production variation of the crystal oscillator circuitry. In your company, please use this results after confirmation of the matching between our crystal unit and oscillator circuit. And furthermore, since the above-mentioned evaluation results evaluate only an oscillating circuit block, please confirm the checking of operations of a set in your company.

## 注意事项

起振回路的特性收到回路常数和安装状态等的影响。上述结果由于回路基板的偏差可能会有所不同。请贵公司在确认水晶谐振器与起振回路的匹配结果后进行使用。同时上述评价结果仅针对于起振回路部分的评价，整块基板的动作请贵公司确认。

Murata Manufacturing Co., Ltd.

**■ Test Data : Characteristics of recommended conditions**
**Center frequency 15.999980 MHz**

Center frequency difference -1 ppm from 16MHz

This frequency difference causes imbalance of initial frequency tolerance on your PCB, because of load capacitance difference.

**Load capacitance of the circuit 8.2 pF**

This value shows load capacitance the evaluated circuit has.

Our crystal proposed in this report is sorted with 8pF as load capacitance

**Negative resistance**

Ratio of negative resistance  $|-R|$  to  $R1_{spec}$ .

**Ratio 6.1 times**

Ratio =  $|-R| / R1_{spec}$ .

$|-R|$  1640 ohm  
 Negative resistance  $|-R| = R_{s\_max} + R_e$

$R_{s\_max}$ : 1500 ohm  
 Maximum series resistance for Crystal Unit to keep oscillation

$R_e$ : 140.5 ohm  
 Effective resistance of Crystal Unit at actual oscillation frequency

$R1_{spec}$ : 270 ohm  
 Equivalent series resistance

**Drive level**

Drive power of crystal under circuit condition shown in page 1

**Drive level 53 uW**

Drive level =  $I^2 \times R1$


$I$ : 0.66 mA (RMS)  
 Current through Crystal Unit measured by current probe

$R1$ : 123.1 ohm

■ Test Data : Characteristics of recommended conditions

**Oscillation waveform**

MODEL : XRCGB16M000FXN20R0 with TLSR8267



VIN [V]			VOUT [V]		
High	Low	p-p	High	Low	p-p
0.9	-0.1	1.0	0.9	-0.1	1.0


Typical sample at Vdd=5V, +25deg.C

[VIN] Vertical: 0.5V/div., Horizontal: 20ns/div.

[VOUT] Vertical: 0.5V/div., Horizontal: 20ns/div.

**Oscillation start up waveform**

MODEL : XRCGB16M000FXN20R0 with TLSR8267



**Start up time**

The time takes steady amplitude of Vout(Xout) after power is applied.

Typical sample at Vdd=5V, +25deg.C

[VOUT] Vertical: 0.5V/div., Horizontal: 5ms/div.