

Type	Frequency	Part Number	Size (mm)	Appearance ^{※1}	SPL(Typ.) (dB) [±1.5Vo-p, SquareWave,10cm]
Piezoelectric Diaphragms		7BB-20-6	φ20×0.42		-
Piezoelectric Sounders (Pin Type)	2kHz	PKM17EPP-2002-B0	φ17×9.8		79
		PKM22EPH2001 ^{※2}	Φ22×11		85
		PKM22EPPH2001-B0 ^{※2}	φ22×12		79
	4kHz	PKM13EPYH4002-B0	φ12.6x6.9		78
		PKM13EPYH4000-A0 (Taping)			
		PKM17EPPH4001-B0 ^{※2}	φ17×8.2		79
		PKM22EPPH4001-B0 ^{※2}	Φ22×8.2		87
		PKM22EPPH4005-B0			86
		PKM22EPPH4007-B0			92
		PKM22EPPH4012-B0	φ22×12		92
Piezoelectric Sounders (SMD Type)	2kHz	PKMCS1818E20A0-R1	18×18×8		100 [12Vo-p,10cm]
		PKLCS1212E2000-R1(For Consume) PKLCS1212E20A0-R1(For Automotive)			76
	2.4kHz	PKLCS1212E2400-R1(For Consumer) PKLCS1212E24A0-R1(For Automotive)	12×12×3		80
		PKLCS1212E4001-R1(For Consumer) PKLCS1212E40A1-R1(For Automotive)			84
	4kHz	PKMCS0909E4000-R1	9×9×1.9		72
Piezoelectric Buzzer (Pin Type)		PKB24SPCH3601-B0	Φ24×9.7		90(min.) [12Vdc,10cm]

※1 Appearance is not a full scale.

※2 Another lead length is available.

Product specifications are as of June 2017. They are subject to change without notice.

Copyright © Murata Manufacturing Co., Ltd. All rights reserved. No.VPPT-1706-0007-D