

PKGS-00GXP1-R




Applications

Unsuitable Applications	Please be sure to read and comply with these "Precautions for use."
Specific Applications	HDD Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product.

Packaging Information

Packaging	Specifications	Standard Packing Quantity
R	180mm Embossed Tape	3000

Appearance & Shape



Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

PKGS-00GXP1-R



Specifications

Operating Temperature Range	-40°C to 85°C
Primary Axis Inclined Angle	0°
Sensitivity(typ.)	0.35pC/G
Capacitance(typ.)	390pF
Insulation Resistance(min.)	500MΩ
Non-linearity(typ.)	1%
Shock Resistance	3000G (0.3ms duration)
Sensitivity Type	Electric charge sensitivity type
Resonance Frequency	31kHz
Storage Temperature Range	-40°C to 85°C

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.


2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.


PKGS-00GXP1-R



Product Data



Freq. Characteristics



Primary axis inclined angle

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.