

Product Search Data Sheet

NCG18WF104F0SRB

Note: This datasheet may be out of date. Please download the latest datasheet of NCG18WF104F0SRB from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=NCG18WF104F0SRB




### Applications

Unsuitable	Please be sure to read and comply with
Applications	these "Precautions for use."
	Automotive powertrain/safety equipment
	Please refer to Our Website and
	specifications, etc. for information about
Specific	the performance, functions, quality,
Specific	management, and safety required for
Applications	the above applications, and use
	Products after confirming the
	performance and reliability of the actual
	Product.

### Appearance & Shape





## Packaging Information

Packaging	Specifications	Standard Packing Quantity
RB	180mm Paper Tape	4000



- 1. Excellent solderability and high stability in environment
- 2. Excellent long time aging stability
- 3. High accuracy in resistance and B-constant
- 4. Glue mounting possible

1 of 3

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





## NCG18WF104F0SRB

Note: This datasheet may be out of date. Please download the latest datasheet of NCG18WF104F0SRB from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=NCG18WF104F0SRB

### Specifications

Resistance (25°C)	100kΩ
Resistance Value Tolerance (at 25°C)	±1%
B-Constant (25/50°C)	4200K
B-Constant (25/50°C) Tolerance	±1%
B-Constant(25/80°C) (Reference Value)	4255K
B-Constant(25/85°C) (Reference Value)	4260K
B-Constant(25/100°C) (Reference Value)	4282K
Max. Voltage	5V
Maximum Operating Current (25°C)	0.031mA
Typical Dissipation Constant (25°C)	1mW/°C
Operating Temperature Range	-55℃ to 150℃
Size Code (in mm)	1.6x0.8mm
Size Code (in inch)	0.6x0.3inch
Shape	SMD
Mass	0.0047g
MSL	1

Glossary of NTC thermistors

Related documents (UL, RoHS, etc.)

### 2 of 3

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.






Product Search Data Sheet

# NCG18WF104F0SRB


Note: This datasheet may be out of date. Please download the latest datasheet of NCG18WF104F0SRB from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=NCG18WF104F0SRB






**Resistance-Temperature Characteristics** 



Max. Voltage, Max. Operating Voltage/Current Reduction Curve



**Temperature Error Characteristics** 

3 of 3

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering

