

MHR0622SA106F70



Packaging Information

Packaging	Specifications	Minimum Order Quantity
-	Bulk(Bag)	1000

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

MHR0622SA106F70

Specifications

Power Rating	1.5W
Shape	Lead
Maximum Working Voltage	3.8kVdc
Resistance	10.0MΩ
Resistance Deviation	±1%
Single Use/Mold Use	Single use
Length	22.7mm
Height H	9.0mm
Lead Pitch P	20.32mm

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.