

# NTSD1XM202FPB40

Discontinued

RoHS

REACH

## Applications

|                         |  |
|-------------------------|--|
| Unsuitable Applications | Please be sure to read and comply with these "Precautions for use."  |
| Specific Applications   | Industrial Equipment<br>Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product. |

## Appearance & Shape



## Packaging Information

| Packaging | Specifications | Standard Packing Quantity |
|-----------|----------------|---------------------------|
| -         | Bulk(Bag)      | 200                       |

## Features

1. Electric insulation on lead wire
2. Excellent bending resistance due to suitable hardness of surface coating
3. Easy handling due to most suitable hardness of surface of coating
4. +/-1% of resistance and +/-0.5% of B-Constant is realized due to technical advantages of the material and manufacturing process.

### Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.  
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# NTSD1XM202FPB40



## Specifications

|  |                 |
|--|-----------------|
| Resistance (25°C)                      | 2kΩ             |
| Resistance Value Tolerance (at 25°C)   | ±1%             |
| B-Constant (25/50°C)                   | 3500K           |
| B-Constant (25/50°C) Tolerance         | ±0.5%           |
| B-Constant(25/80°C) (Reference Value)  | 3523K           |
| B-Constant(25/85°C) (Reference Value)  | 3526K           |
| B-Constant(25/100°C) (Reference Value) | 3543K           |
| Maximum Operating Current (25°C)       | 0.32mA          |
| Rated Electric Power (25°C)            | 21.0mW          |
| Typical Dissipation Constant (25°C)    | 2.1mW/°C        |
| Operating Temperature Range            | -40°C to 125°C  |
| Thermal Time Constant                  | 7s              |
| Lead Shape                             | Insulation type |
| Shape                                  | Lead            |
| Mass                                   | 0.13g           |
| MSL                                    | N               |

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# NTSD1XM202FPB40



## Product Data



### Temperature Tolerance-Temperature Characteristics

#### Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.  
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.