


# XRCHJ36M000F1QA0P0

In Production RoHS REACH

## Appearance & Shape



## Features

Standard package size (2520) product with seam sealing technology.  
Robust package gives high reliability and high impact resistance.  
They are suitable for various types of digital communication equipment requiring high reliability.

## Applications

Other Usage	Consumer
-------------	----------

## Packaging Information

Packaging	Specifications	Minimum Order Quantity
P0	180mm Plastic Tape	3000

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.  
2.This datasheet has only typical specifications because there is no space for detailed specifications.  
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# XRCHJ36M000F1QA0P0

## Specifications

Type	TDS-2520F
Frequency	36.0000MHz
Frequency Tolerance	±10ppm max. (25±3°C)
Operating Temperature Range	-30°C to 85°C
Frequency Shift by Temperature	±15ppm max.
Frequency Aging	±3ppm max./year
Wash	Not available
Load Capacitance	8pF
Equivalent Series Resistance(max.)	80Ω
Drive Level(max.)	30μW
Shape	SMD
L x W (size)	2.5x2.0mm

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.