



XRCLK14M745F1QB6J1

In Production RoHS REACH

Appearance & Shape



Features

Standard package size (5032) product with seam sealing technology. Robust package gives high reliability and high impact resistance. They are suitable for various types of digital communication equipment requiring high reliability.

Applications

Other Usage Consumer

Packaging Information

Packaging	Specifications	Minimum Order Quantity
J1	255mm Plastic Tape	2000

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

XRCLK14M745F1QB6J1



Specifications

Type	TSS-5032A
Frequency	14.7456MHz
Frequency Tolerance	±10ppm max. (25±3°C)
Operating Temperature Range	-30°C to 85°C
Frequency Shift by Temperature	±15ppm max.
Frequency Aging	±3ppm max./year
Wash	Not available
Load Capacitance	8pF
Equivalent Series Resistance(max.)	60Ω
Drive Level(max.)	60μW
Shape	SMD
L x W (size)	5.0x3.2mm

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.