

mybsp00502abf

In Production

Recommended

RoHS

Appearance & Shape



Features

- 10W, 5Vo/2A isolated DC-DC converter for PoE
- Support IEEE802.3af/ PoE class0
- Input voltage ranges from 37 to 57V
- Small package, 26 x 14.8 x 6.2mm
- Surface mount module
- 2250Vdc Input-Output Isolation

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

mybsp00502abf



Specifications

Output power (W)Max	10W
Vin(V)	37V to 57V
Vin(V)typ	48V
Vout(V)	5V
Vout(V)typ	5V
Isolation Voltage (V)	2250V
Efficiency (%)	80%
Size(mm)W	26.0mm
Size(mm)L	14.8mm
Size(mm)T	6.2mm
Operatingtemperature(degC)	-40°C to 85°C
Outputs (#)	1
Iout(A)Max	2A
Package	SMD
Application	PoE
Productseries	MYB
Product Series Features	MYBSP series is isolated DC-DC converter for PoE
Brand	Murata

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.