

# GRT188C80J106ME13#

“#” at the end indicates the package specification code.



## < List of part numbers with package codes >

GRT188C80J106ME13D  
GRT188C80J106ME13V

GRT188C80J106ME13W

GRT188C80J106ME13J

## Applications

Unsuitable Applications	Please be sure to read and comply with these "Precautions for use."
Specific Applications	Automotive infotainment/comfort equipment, Industrial Equipment, Medical equipment [GHTF A/B/C] except for implant equipment Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product.

## Notices

Derating1

## Appearance & Shape



## References

Packaging	Specifications	Standard Packing Quantity
D	φ180mm Reel Paper Tape	4000
W	φ180mm Reel W8P2 Paper Tape	8000
J	φ330mm Reel Paper Tape	10000
V	φ330mm Reel W8P2 Paper Tape	30000

Mass (typ.)	
1 piece	9.1mg

### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# GRT188C80J106ME13#

“#” at the end indicates the package specification code.



## Specifications

Length	1.6±0.2mm
Width	0.8±0.2mm
Thickness	0.8±0.2mm
Capacitance	10μF ±20%
Distance between external terminals g	0.6mm min.
External terminal size e	0.2 to 0.55mm
Operating Temperature Range	-55°C to 105°C
Rated Voltage	6.3Vdc
Size code in inch(mm)	0603 (1608M)
Capacitance change rate	±22.0%
Temperature characteristics (complied standard)	X6S(EIA)
Temperature range of temperature characteristics	-55°C to 105°C

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





# GRT188C80J106ME13#

“#” at the end indicates the package specification code.



## Characteristic Data

The charts below may show another part number which shares its characteristics.



### Attention



1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# GRT188C80J106ME13#

“#”at the end indicates the package specification code.



**Attention**

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.  
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.