

18R334C

Radial Lead Inductors



Applications

Unsuitable Applications	Please be sure to read and comply with these "Precautions for use."
Specific Applications	Industrial Equipment Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product.

References

Packaging	Specifications	Standard Packing Quantity
-	Bulk(Bag)	100

Mass (typ.)	
1 piece	4.6g

Appearance & Shape



Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

18R334C



Specifications

L size	13.7mm
W size	13.7mm
T size	15.9mm
Inductance	330 μ H \pm 10%
Max. of DC resistance	0.335 Ω
Operating Temperature Range(Self-temperature rise is not included)	0°C to 70°C
Class of magnetic shield	Unshielded
Brand	Murata Power Solutions
Rated Current	0.73A
Series	1800R

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.