

LQP03TN1N8BZ2#

“#”at the end indicates the package specification code.

Size Code 0603 (0201) in mm (in inch), High Q, Wide Variation

In Production

AEC-Q200

RoHS

REACH

125 °C max.

Film

Tight Tolerance

Reflow OK


< List of part numbers with package codes >

LQP03TN1N8BZ2B LQP03TN1N8BZ2D LQP03TN1N8BZ2J

Applications

Unsuitable Applications	Please be sure to read and comply with these "Precautions for use."
Specific Applications	Consumer equipment, Automotive infotainment/comfort equipment, Medical equipment [GHTE A/B/C] except for implant & surgery & auto injector, Industrial equipment except for transportation & facility & energy equipment Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product.
Recommended Applications	Automotive infotainment/comfort equipment

Appearance & Shape



Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

LQP03TN1N8BZ2#

“#”at the end indicates the package specification code.



References

Packaging	Specifications	Standard Packing Quantity
B	Bulk(Bag)	500
D	180mm Paper Tape	15000
J	330mm Paper Tape	50000

Mass (typ.)	
1 piece	0.2mg

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

LQP03TN1N8BZ2#

“#” at the end indicates the package specification code.



Specifications

L size	0.6±0.03mm
W size	0.3±0.03mm
T size	0.3±0.03mm
Size code inch (mm)	0201 (0603)
Inductance	1.8nH±0.1nH
Inductance Test Frequency	500MHz
Rated current (Itemp) (Based on Temperature rise)	600mA
Max. of DC resistance	0.15Ω
Operating Temperature Range(Self-temperature rise is not included)	-55°C to 125°C
Class of magnetic shield	Non-Shielded
Q(min.)	14
Q Test Frequency	500MHz
Self resonance frequency (min.)	15000MHz
Brand	Murata
Series	LQP03TN_Z2

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.




LQP03TN1N8BZ2#

“#” at the end indicates the package specification code.



Characteristic Data

The charts below may show another part number which shares its characteristics.



Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.