

RHS7G2A101J0A2H01B




Applications

| | |
|-------------------------|--|
| Unsuitable Applications | Please be sure to read and comply with these "Precautions for use." |
| Specific Applications | Automotive powertrain/safety equipment, Automotive infotainment/comfort equipment, Medical equipment [GHTE A/B/C] except for implant equipment Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product. |

Notices

HF(Halogen Free)、Derating5

Appearance & Shape



References

| Packaging | Specifications | Standard Packing Quantity |
|-----------|----------------|---------------------------|
| B | Bulk(Bag) | 500 |

| Mass (typ.) | |
|-------------|------|
| 1 piece | 0.1g |

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

RHS7G2A101J0A2H01B



Specifications

| | |
|--|--|
| L size or Outer diameter D | 3.9mm max. |
| Width | 3.5mm max. |
| T size | 2.6mm max. |
| Lead spacing F | 2.5±0.8mm |
| Lead diameter d | 0.5±0.05mm |
| Paint dripping e | 2.0mm max. |
| Capacitance | 100pF ±5% |
| Rated voltage | 100Vdc |
| Temperature characteristics | CCG(MURATA) |
| Temperature range of temperature characteristics | -55°C to 200°C |
| Operating Temperature Range | -55°C to 200°C |
| TC | -55°C to 25°C: 0+30/-72ppm/°C 25°C to 125°C: 0±30ppm/°C 125°C to 200°C: 0+72/-30ppm/°C |

Attention


1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

RHS7G2A101J0A2H01B

Characteristic Data



Capacitance - temperature characteristics

Impedance - frequency characteristics

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.