

MER1S4812SC

In Production

Recommended

RoHS

Appearance & Shape



Features

12V 84mA, Isolated 1W Single Output 1kVDC, DC-DC Converter,
43.2V-52.8V Input


Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

MER1S4812SC



Specifications

Output power (W)Max	1W
Vin(V)	43.2V to 52.8V
Vin(V)typ	48V
Vout(V)	12V
Vout(V)typ	12V
LineRegulation (%)	-1.1% to 1.1%
LoadRegulation (%)	2.4%
Isolation Voltage (V)	1000V
Efficiency (%)	82.5%
Size(mm)W	19.65mm
Size(mm)L	7.65mm
Size(mm)T	10.15mm
Operatingtemperature(degC)	-40°C to 85°C
Outputs (#)	1
Iout(A)Max	0.084A
Package	SIP
Productseries	MER
Product Series Features	1kVDC Isolated 1W Single Output DC-DC Converters
Regulation	Unregulated
Safety Approval	UL60950
Brand	Murata Power Solutions

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.