

XRCGB32M000F1S1BR0

In Production

Recommended

RoHS

REACH

Applications

| | |
|-------------------------|---|
| Unsuitable Applications | Please be sure to read and comply with these "Precautions for use." |
| Specific Applications | <p>Consumer equipment, Industrial equipment except for transportation & facility & energy equipment, Medical equipment [GHTF A/B], Mobile Electronics</p> <p>Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product.</p> |


Packaging Information

| Packaging | Specifications | Standard Packing Quantity |
|-----------|--------------------|---------------------------|
| R0 | 180mm Plastic Tape | 3000 |

Features

The crystal unit that realized small package and highly accurate frequency.
Based on Murata's excellent package technology and high grade quartz crystal elements, achieving small size and high accuracy resonators.

Appearance & Shape



Features

1. The series is available in the applications to be necessary for high accuracy resonator. Especially, it is the best for the communication clocks such as Wi-Fi and Bluetooth®*.
2. The resonator is extremely small size (2.0 x 1.6 x 0.7 (mm)), and contribute to reduction in mounting area.
3. The series complies to RoHS directive, being lead-free (phase 3).

*Note: This product doesn't have a Bluetooth® function.

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

XRCGB32M000F1S1BR0



Specifications

| | |
|------------------------------------|----------------------------|
| Product Type | Crystal Unit |
| Series | XRCGB |
| Type | HCR2016 |
| Frequency | 32.0000MHz |
| Frequency Tolerance | +/-10ppm max. (30+/-0.5°C) |
| Operating Temperature Range | -30°C~85°C |
| Frequency Shift by Temperature | +/-10ppm max. |
| Frequency Aging | +/-2ppm max./year |
| Equivalent Series Resistance (ESR) | 50ohm max. |
| Drive Level (DL) | 300μW max. |
| Load Capacitance (Cs) | 8pF |
| Shape | SMD |
| Wash | Not available |
| L x W (size) | 2.0x1.6mm |
| Mass | 6.9mg |

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.