


# RHE5G1H391J0M1H03A



## Appearance & Shape



## References

Packaging	Specifications	Minimum Order Quantity
A	Ammo Pack	2000

Mass (typ.)	
1 piece	0.098g

## Notices

Meet LF(Lead Free)[※LF : Lead content is less than 1000 ppm.], HF(Halogen Free)

### Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# RHE5G1H391J0M1H03A



## Specifications

L size or Outer diameter D	3.6mm max.
Width	3.5mm max.
T size	2.5mm max.
Lead spacing F	5.0+0.6/-0.2mm
Lead diameter d	0.5±0.05mm
Capacitance	390pF ±5%
Rated voltage	50Vdc
Temperature characteristics	X8G(MURATA)
Temperature range of temperature characteristics	-55°C to 150°C
Operating Temperature Range	-55°C to 150°C
TC	20 to 150°C: 0±30ppm/°C-55 to 25°C: 0+30/-72ppm/°C
W1 size	6.0mm

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.


2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.


# RHE5G1H391J0M1H03A

## Characteristic Data


The charts below may show another part number which shares its characteristics.




■ RHE5G1H391J0M1H03A |Z| DCOV, 25degC



■ RHE5G1H391J0M1H03A R DCOV, 25degC



■ RHE5G1H391J0M1H03A C-DC bias capchange, 25.0degC, AC1




■ RHE5G1H391J0M1H03A C-AC Voltage capchange, DCOV, 25.0

**Attention**

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.


# RHE5G1H391J0M1H03A

Temperature Characteristics



■ RHE5G1H391J0M1H03A C-Temp. capchange, DCOV, AC1Vrms

S Parameter S21



■ RHE5G1H391J0M1H03A S21 DCOV, 25degC

**Attention**

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.