

XRCLH10M000F1QA4P0

Discontinued


RoH

REACH

Applications

Unsuitable Applications	Please be sure to read and comply with these "Precautions for use."
Specific Applications	Industrial Equipment Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product.

Appearance & Shape



Packaging Information

Packaging	Specifications	Standard Packing Quantity
P0	255mm Plastic Tape	2000

Features

With unique metal sealing technology, this product realizes an excellent frequency stability over temperature. They are suitable for various types of digital communication equipment.

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

XRCLH10M000F1QA4P0



Specifications

Product Type	Crystal Unit
Series	XRCLH
Type	TAS-5032F
Frequency	10.0000MHz
Frequency Tolerance	+/-10ppm max. (25+/-3°C)
Operating Temperature Range	-30°C~85°C
Frequency Shift by Temperature	+/-15ppm max.
Frequency Aging	+/-1ppm max./year(+/-3ppm max./5years)
Equivalent Series Resistance (ESR)	60ohm max.
Drive Level (DL)	30μW
Load Capacitance (Cs)	8pF
Shape	SMD
Wash	Not available
L x W (size)	5.0x3.2mm
Mass	45.76mg

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.