

LQM18PN1R5NC0#

“#” at the end indicates the package specification code.

Size Code 1608 (0603) in mm (in inch), 0.55mm max. Thickness




< List of part numbers with package codes >

LQM18PN1R5NC0B LQM18PN1R5NC0L

Applications

| | |
|--------------------------|--|
| Unsuitable Applications | Please be sure to read and comply with these "Precautions for use." |
| Specific Applications | Consumer equipment, Medical equipment [GHF A/B/C] except for implant & surgery & auto injector, Industrial equipment except for transportation & facility & energy equipment Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product. |
| Recommended Applications | Consumer equipment |

Appearance & Shape



(in mm)

References

| Packaging | Specifications | Standard Packing Quantity |
|-----------|------------------|---------------------------|
| B | Bulk(Bag) | 1000 |
| L | 180Embossed Tape | 4000 |

| Mass (typ.) | |
|-------------|--------|
| 1 piece | 0.003g |

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

LQM18PN1R5NC0#

“#”at the end indicates the package specification code.



Specifications

| | |
|--|-------------------------|
| L size | 1.6±0.15mm |
| W size | 0.8±0.15mm |
| T size | 0.5±0.05mm |
| Size code inch (mm) | 0603 (1608) |
| Inductance | 1.5μH±30% |
| Inductance Test Frequency | 1MHz |
| Rated current (Itemp) (Based on Temperature rise) | 720mA |
| Max. of DC resistance | 0.275Ω |
| DC resistance | 0.22Ω±25% |
| Class of magnetic shield | Shielded (Ferrite Core) |
| Self resonance frequency (min.) | 50MHz |
| Brand | Murata |
| Operating Temperature Range | -55°C to 125°C |
| Series | LQM18PN_C0 |

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





LQM18PN1R5NC0#

“#”at the end indicates the package specification code.



Characteristic Data

The charts below may show another part number which shares its characteristics.




Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

LQM18PN1R5NC0#

“#”at the end indicates the package specification code.



Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.