

PV32N105A01B00



Specifications

Power Rating	0.5W	Operating Temperature Range	-55°C to 125°C
Shape	Lead	Mass	0.65g
Maximum Working Voltage	300Vdc		
Adjustment Direction	Side		
Size	6mm		
Auto Adjustment	No		
Number of Turns (Effective Rotation Angle)	1(230°±5°)		
Mechanical Rotation Angle	270+/-5 deg.		
Total Resistance Value	1MΩ		
Total Resistance Value Tolerance	±20%		
Temperature Coefficient of Resistance	±100ppm/°C		
Resistance Taper	B (Linear)		
Contact Resistance Variation	Less than 3% of total resistance value or 3ohm, whichever is greater		
Residual Resistance	2ohm max.		
Soldering Method	Flow Soldering Iron		
Torque	1.96 to 19.6mN m		
Measure Condition of RatedPower	70°C		

Attention


1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

PV32N105A01B00

Product Data



Constructions

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.