

# RHS7G2A101J0DGH01A

To be discontinued

AEC-Q200

RoHS

REACH

200  
°C max.

Low acoustic noise

Deflecting crack

Soldering crack

Flow OK

Welding

Derating  
5


## Applications

|                         |  |
|-------------------------|--|
| Unsuitable Applications | Please be sure to read and comply with these "Precautions for use."  |
| Specific Applications   | Automotive powertrain/safety equipment, Automotive infotainment/comfort equipment, Medical equipment [GHTF A/B/C] except for implant equipment<br>Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product. |

## Notices

HF(Halogen Free)、Derating5

## Appearance & Shape



## References

| Packaging | Specifications | Standard Packing Quantity |
|-----------|----------------|---------------------------|
| A         | Ammo Pack      | 2000                      |

| Mass (typ.) |      |
|-------------|------|
| 1 piece     | 0.1g |

### Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.  
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# RHS7G2A101J0DGH01A



## Specifications

|  |  |
|--|--|
| L size or Outer diameter D                       | 3.9mm max.   |
| Width  | 3.5mm max.   |
| T size   | 2.6mm max.   |
| Lead spacing F                                   | 2.5+0.4/-0.2mm   |
| Lead diameter d                                  | 0.5±0.05mm   |
| Capacitance                                      | 100pF ±5%  |
| Rated voltage                                    | 100Vdc   |
| Temperature characteristics                      | CCG(MURATA)  |
| Temperature range of temperature characteristics | -55°C to 200°C   |
| Operating Temperature Range                      | -55°C to 200°C   |
| TC   | -55°C to 25°C: 0+30/-72ppm/°C 25°C to 125°C: 0±30ppm/°C 125°C to 200°C: 0+72/-30ppm/°C |

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# RHS7G2A101J0DGH01A

## Characteristic Data



Capacitance - temperature characteristics

Impedance - frequency characteristics

**Attention**

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.