

# CME0505DPC

In Production

Recommended

RoHS


## Applications

Unsuitable Applications	Please be sure to read and comply with these "Precautions for use."
Specific Applications	Consumer equipment, Industrial Equipment Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product.

## Features

5V, Isolated 0.75W Input Single Output 1kVDC, DC-DC Converter, 4.5 - 5.5V Input

## Appearance & Shape



**Attention**  
1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.  
2.This datasheet has only typical specifications because there is no space for detailed specifications.  
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# CME0505DPC



## Specifications

Output power (W)Max	0.75W
Vin(V)	4.5V to 5.5V
Vin(V)typ	5V
Vout(V)	5V
Vout(V)typ	5V
LineRegulation (%)	-1.2% to 1.2%
LoadRegulation (%)	9%
Isolation Voltage (V)	1000V
Efficiency (%)	76.5%
Size(mm)W	11.6mm
Size(mm)L	9.9mm
Size(mm)T	6.9mm
Operatingtemperature(degC)	-40°C to 85°C
Outputs (#)	1
Iout(A)Max	0.15A
Package	DIP
Productseries	CME
Product Series Features	Isolated 0.75W Single Output Isolated DC-DC Converters
Regulation	Unregulated
Safety Approval	UL60950
Brand	Murata Power Solutions

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.