

RHS7J2H151J2K1H01B

To be discontinued

AEC-Q200

RoHS

REACH

200 °C max.

Low acoustic noise

Deflecting crack

Soldering crack

Flow OK

Welding

Derating 5


Applications

| | |
|-------------------------|--|
| Unsuitable Applications | Please be sure to read and comply with these "Precautions for use." |
| Specific Applications | Automotive powertrain/safety equipment, Automotive infotainment/comfort equipment, Medical equipment [GHTE A/B/C] except for implant equipment Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product. |

Notices

HF(Halogen Free)、Derating5

Appearance & Shape



References

| Packaging | Specifications | Standard Packing Quantity |
|-----------|----------------|---------------------------|
| B | Bulk(Bag) | 500 |

| Mass (typ.) | |
|-------------|-------|
| 1 piece | 0.14g |

Attention
1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

RHS7J2H151J2K1H01B



Specifications

| | |
|--|--|
| L size or Outer diameter D | 5.5mm max. |
| Width | 4.0mm max. |
| T size | 3.3mm max. |
| Lead spacing F | 5.0±0.8mm |
| Lead diameter d | 0.5±0.05mm |
| Paint dripping e | Up to the end of crimp |
| Capacitance | 150pF ±5% |
| Rated voltage | 500Vdc |
| Temperature characteristics | UNJ(MURATA) |
| Temperature range of temperature characteristics | -55°C to 200°C |
| Operating Temperature Range | -55°C to 200°C |
| TC | -55°C to 25°C: -750+120/-347ppm/°C 25°C to 125°C: -750±120ppm/°C 125°C to 200°C: -750+347/-120ppm/°C |
| W1 size | 6.0mm max. |

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

RHS7J2H151J2K1H01B



Characteristic Data



Capacitance - temperature characteristics

Impedance - frequency characteristics

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.