

# GRM1554C2A1R3WA01#

“#” at the end indicates the package specification code.



## < List of part numbers with package codes >

GRM1554C2A1R3WA01D      GRM1554C2A1R3WA01W      GRM1554C2A1R3WA01J  
GRM1554C2A1R3WA01V

## Applications


Unsuitable Applications	Please be sure to read and comply with these "Precautions for use."
Specific Applications	Consumer equipment, Industrial Equipment, Mobile Electronics, Medical equipment [GHF A/B/C] except for implant equipment, Automotive infotainment/comfort equipment Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product.

## References

Packaging	Specifications	Standard Packing Quantity
D	φ180mm Reel Paper Tape	10000
W	φ180mm Reel W8P1 Paper Tape	20000
J	φ330mm Reel Paper Tape	50000
V	φ330mm Reel W8P1 Paper Tape	100000

Mass (typ.)	
1 piece	1.6mg

## Appearance & Shape



### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
2. This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# GRM1554C2A1R3WA01#

“#” at the end indicates the package specification code.



## Specifications

Length	1.0±0.05mm
Width	0.5±0.05mm
Thickness	0.5±0.05mm
Capacitance	1.3pF ±0.05pF
Distance between external terminals g	0.3mm min.
External terminal size e	0.15 to 0.35mm
Operating Temperature Range	-55°C to 125°C
Rated Voltage	100Vdc
Size code in inch(mm)	0402 (1005M)
TC	0±250ppm/°C
Temperature characteristics (complied standard)	CK(JIS)
Temperature range of temperature characteristics	20°C to 125°C

### Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.  
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.


# GRM1554C2A1R3WA01#

“#” at the end indicates the package specification code.




## Characteristic Data


The charts below may show another part number which shares its characteristics.




GRM1554C2A1R3WA01 |Z| DCOV, 20degC



GRM1554C2A1R3WA01 R DCOV, 20degC



GRM1554C2A1R3WA01 C-DC bias capchange, 20.0C





GRM1554C2A1R3WA01 C-AC Voltage capchange, Dc

### Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.  
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# GRM1554C2A1R3WA01#

“#” at the end indicates the package specification code.



## Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.  
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.