

GRT1885C1E122JA02#

“#” at the end indicates the package specification code.



< List of part numbers with package codes >

GRT1885C1E122JA02D

GRT1885C1E122JA02W

GRT1885C1E122JA02J

GRT1885C1E122JA02V


Applications

Unsuitable Applications	Please be sure to read and comply with these "Precautions for use."
Specific Applications	Automotive infotainment/comfort equipment, Industrial Equipment, Medical equipment [GHTF A/B/C] except for implant equipment Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product.

Notices

Derating1

Appearance & Shape



References

Packaging	Specifications	Standard Packing Quantity
D	φ180mm Reel Paper Tape	4000
W	φ180mm Reel W8P2 Paper Tape	8000
J	φ330mm Reel Paper Tape	10000
V	φ330mm Reel W8P2 Paper Tape	30000

Mass (typ.)	
1 piece	6.3mg

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

GRT1885C1E122JA02#

“#” at the end indicates the package specification code.



Specifications

Length	1.6±0.1mm
Width	0.8±0.1mm
Thickness	0.8±0.1mm
Capacitance	1200pF ±5%
Distance between external terminals g	0.5mm min.
External terminal size e	0.2 to 0.5mm
Operating Temperature Range	-55°C to 125°C
Rated Voltage	25Vdc
Size code in inch(mm)	0603 (1608M)
TC	0±30ppm/°C
Temperature characteristics (complied standard)	C0G(EIA)
Temperature range of temperature characteristics	25°C to 125°C

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.


Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

GRT1885C1E122JA02#


“#” at the end indicates the package specification code.

Characteristic Data


The charts below may show another part number which shares its characteristics.




GRT1885C1E122JA02 |Z| DCOV,25degC



GRT1885C1E122JA02 R DCOV,25degC



GRT1885C1E122JA02 C-DC bias capchange, 25.0C




GRT1885C1E122JA02 C-AC Voltage capchange, Dc

Attention


- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

GRT1885C1E122JA02#

“#” at the end indicates the package specification code.



GRT1885C1E122JA02 C-Temp. capchange, DCOV, 1



GRT1885C1E122JA02 S21 DCOV, 25degC

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.