

PRF21BA471QB1RA

Discontinued

RoHS

REACH

Applications

| | |
|-------------------------|--|
| Unsuitable Applications | Please be sure to read and comply with these "Precautions for use." |
| Specific Applications | Consumer equipment, Industrial Equipment Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product. |

Appearance & Shape



| Part Number | Dimensions (mm) | | | | |
|-------------|-----------------|----------|----------|------------|----------|
| | L | W | T | e | g |
| PRF03_RL | 0.6±0.05 | 0.3±0.05 | 0.3±0.05 | 0.1 to 0.2 | - |
| PRF15_RC | 1.0±0.05 | 0.5±0.05 | 0.5±0.05 | 0.1 to 0.4 | 0.3 min. |
| PRF18_RB | 1.6±0.15 | 0.8±0.15 | 0.8±0.15 | 0.1 to 0.6 | - |
| PRF21_RA | 2.0±0.2 | 1.25±0.2 | 0.9±0.2 | 0.2 min. | 0.5 min. |

Packaging Information

| Packaging | Specifications | Standard Packing Quantity |
|-----------|---------------------|---------------------------|
| RA | 180mm Embossed Tape | 4000 |

Features

1. SMD type is helpful for miniaturizing circuits because of its small size and light weight.
2. Excellent thermal response due to small size
3. Solid-state construction provides excellent resistance to mechanical vibration and impact resistance.
4. Contactless operation provides noiseless operation.
5. ULcertified product. (UL1434, File No. E137188)

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

PRF21BA471QB1RA



Specifications

| | |
|--|----------------|
| Max. Voltage | 32V |
| Sensing Temperature | 125°C |
| Sensing Temperature Tolerance | ±5°C |
| Measure Condition of Sensing Temperature | at 4.7k ohm |
| Resistance (25°C) | 470Ω |
| Resistance Value Tolerance (at 25°C) | ±50% |
| Operating Temperature Range | -20°C to 140°C |
| Size Code (in mm) | 2.0x1.25mm |
| Size Code (in inch) | 0.8x0.5inch |
| Shape | SMD |
| Mass | 0.011g |
| MSL | 1 |

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.


Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

PRF21BA471QB1RA

Product Data



Resistance-Temperature Characteristics



Resistance-Temperature Characteristics Range (Reference)

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.