

# PVZ2R224C04B00

Discontinued

RoHS

REACH

## Appearance & Shape



## Features

1. Ultra-small and thin external dimensions of 2.1(W)x4.8(L)x0.9 max. (T)mm. (Rear adjustment type: PVZ2R\_C04 Series)
2. Au plated termination achieves a high-density PCB mounting.
3. Cross-shaped driver slot allows for in-process automatic adjustment and it provides superior adjustability.
4. Two-piece parts construction achieves low cost and excellent quality.

## Packaging Information

| Packaging | Specifications | Standard Packing Quantity |
|-----------|----------------|---------------------------|
| B00       | Bulk(Bag)      | 1000                      |

**Attention**  
1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.  
2.This datasheet has only typical specifications because there is no space for detailed specifications.  
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# PVZ2R224C04B00



## Specifications

|  |   |
|--|---|
| Power Rating                               | 0.05W                                     |
| Shape                                      | SMD                                       |
| Maximum Working Voltage                    | 50Vdc                                     |
| Adjustment Direction                       | Rear                                      |
| Size                                       | 2mm                                       |
| Auto Adjustment                            | Yes                                       |
| Number of Turns (Effective Rotation Angle) | 1(240°±10°)                               |
| Mechanical Rotation Angle                  | Endless                                   |
| Total Resistance Value                     | 220kΩ                                     |
| Total Resistance Value Tolerance           | ±30%                                      |
| Temperature Coefficient of Resistance      | ±500ppm/°C                                |
| Resistance Taper                           | B (Linear)                                |
| Contact Resistance Variation               | 5% max. of nominal total resistance value |
| Residual Resistance                        | 2% max. of nominal total resistance value |
| Soldering Method                           | Reflow,Soldering Iron                     |
| Torque                                     | 1.0 to 9.8mN · m                          |
| Measure Condition of RatedPower            | 50°C                                      |
| Operating Temperature Range                | -25°C to 85°C                             |
| Mass                                       | 0.013g                                    |

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# PVZ2R224C04B00



## Product Data



## Constructions

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.