


XTCJH26M000TJEB4P0

Discontinued

Applications

| | |
|-------------------------|--|
| Unsuitable Applications | Please be sure to read and comply with these "Precautions for use." |
| Specific Applications | Industrial Equipment Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product. |

Appearance & Shape



Packaging Information

| Packaging | Specifications | Standard Packing Quantity |
|-----------|--------------------|---------------------------|
| P0 | 180mm Plastic Tape | 3000 |

Features

Based on long experience and activity, Murata's Crystal Oscillator consists of high quality quartz crystal unit and excellent temperature compensation circuit, which are packaged with high circuit technology and high adjusting technology. They are suitable for communication equipment, business radios, GPS(GNSS) system and survey equipment.

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

XTCJH26M000TJEB4P0



Specifications

| | |
|--------------------------------|---------------------------|
| Shape | SMD |
| Frequency | 26.0000MHz |
| Operating Temperature Range | -30°C to 85°C |
| Supply Voltage | +3.0±5% (Vcc) |
| Current Consumption(max.) | 2mA |
| Output Voltage | 0.8Vp-p / min. |
| Load Impedance/Capacitance | (10Kohm//10pF)±10% |
| Frequency Shift by Temperature | ±0.5ppmmax. |
| Frequency Aging | ±1ppmmax./year |
| Frequency Tolerance | ±1ppmmax. (25±3°C) |
| Frequency Controlled Range | ±5ppm min. to ±15ppm max. |
| Mass | 25.575mg |

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.