

# GCM188R91H333KA37J

“#” at the end indicates the package specification code.



## < List of part numbers with package codes >

GCM188R91H333KA37D      GCM188R91H333KA37W      GCM188R91H333KA37J  
GCM188R91H333KA37V

## Applications

Unsuitable Applications	Please be sure to read and comply with these "Precautions for use."
Specific Applications	Automotive powertrain/safety equipment, Automotive infotainment/comfort equipment, Medical equipment [GHF A/B/C] except for implant equipment Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product.

## References

Packaging	Specifications	Standard Packing Quantity
D	φ180mm Reel Paper Tape	4000
W	φ180mm Reel W8P2 Paper Tape	8000
J	φ330mm Reel Paper Tape	10000
V	φ330mm Reel W8P2 Paper Tape	30000

Mass (typ.)	
1 piece	6.3mg

## Appearance & Shape



### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
2. This datasheet has only typical specifications because there is no space for detailed specifications.  
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# GCM188R91H333KA37J

“#” at the end indicates the package specification code.



## Specifications

Length	1.6±0.1mm
Width	0.8±0.1mm
Thickness	0.8±0.1mm
Capacitance	33000pF ±10%
Distance between external terminals g	0.5mm min.
External terminal size e	0.2 to 0.5mm
Operating Temperature Range	-55°C to 150°C
Rated Voltage	50Vdc
Size code in inch(mm)	0603 (1608M)
Capacitance change rate	±15.0%
Temperature characteristics (complied standard)	X8R(EIA)
Temperature range of temperature characteristics	-55°C to 150°C

### Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.  
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.