

Chip Common Mode Choke Coil

Reference Specification

1. Scope

This reference specification applies to Chip Common Mode Choke Coil DLW21SN SK Series.

2. Part Numbering

(ex.) <u>DL W 21 S N</u> 501 S K 2 L (6) (7) (8) (9) (10) (2) (3) (4) (5)

- (1) Chip Common Mode Choke Coil
- (2) Structure (W: Winding Type)
- (3) Dimension (L×W)
- (4) Type
- (5) Category

- - (6) Impedance (Typ. at 100MHz)
 - (7) Circuit
 - (8) Features
 - (9) Number of Line
 - (10) Packaging Code L: Taping / B: Bulk

3. Rating

		Common Mode Impedance	Rated	Withstanding	Rated	DC	Insulation
Customer	Murata	(at 100MHz,Under Standard	Voltage	Voltage	Current	Resistance	Resistance
Part Number	Part Number	Testing Condition)	V(DC)	V(DC)	(mA)	(Ω max.)	$(M\Omega min.)$
		(Ω)					
	DLW21SN501SK2L	500 ± 25 %			250	0.5	
	DLW21SN501SK2B	300 ± 23 %	50	125	230	0.5	10
	DLW21SN921SK2L	920 ± 25 %	50	125	160	0.95	10
	DI W21SN921SK2B	920 ± 25 %			100	0.95	

Operating Temperature : -40 to +85°C Storage Temperature : -40 to +85°C


4. Standard Testing Condition

<Unless otherwise specified>

Temperature: Ordinary Temperature 15 to 35°C

Humidity: Ordinary Humidity 25 to 85%(RH)


5. Style and Dimensions



<In case of doubt> Temperature : 20 ± 2°C Humidity: 60 to 70%(RH)

Atmospheric Pressure: 86 to 106kPa

■ Equivalent Circuits



No polarity

■ Unit Mass (Typical value)

0.011g

6. Marking


No Marking.

7 <u>. Elec</u> t	trical Performance	e	
No.	Item	Specification	Test Method
7.1	Common Mode Impedance (Zc)	Meet item 3.	Measuring Equipment : KEYSIGHT 4291A or the equivalent Measuring Frequency : 100±1MHz(ref.item 10,11)
7.2	Withstanding Voltage	Products shall not be damaged.	Test Voltage: 2.5 times for Rated Voltage Time: 1 to 5 seconds Charge Current: 1 mA max. (ref.item 10)
7.3	DC Resistance (Rdc)	Meet item 3.	Measuring current : 100mA max. (ref.item 10) (In case of doubt in the above mentioned standard condition, measure by 4 terminal method.)
7.4	Insulation Resistance (I.R.)		Measuring voltage: Rated Voltage Measuring time: 1 minute max. (ref.item 10)



8. Mechanical Performance

No.	Item	Specification	Test Method
8.1	Appearance and Dimensions	Meet item 5.	Visual Inspection and measured with Slide Calipers.
8.2	Bonding Strength	No evidence of coming off substrate. Products shall not be mechanical damaged.	It shall be soldered on the substrate. Applying Force(F): 5N Applying Time: 5±1seconds Pressure Substrate Product Test board fixture
8.3	Bending Strength	Meet Table 1. Table 1 Appearance No damaged Common Mode Impedance Within ±20% Change I.R. 10MΩ min.	It shall be soldered on the Glass-epoxy substrate. Deflection: 2mm (t=1.0mm) Keeping time: 5 seconds Speed of Applying Force: 0.5mm/s Pressure jig Deflection 45 Product
8.4	Drop	Withstanding No damaged Voltage	It shall be dropped on concrete or steel board. Method : free fall Height : 1 m The Number of Times : 3 times
8.5	Vibration		It shall be soldered on the substrate. Oscillation Frequency: 10 to 55 to 10Hz for 1 minute Total Amplitude: 1.5mm Testing Time: A period of 2 hours in each of 3 mutually perpendicular directions. (Total 6 hours)
8.6		The electrodes shall be at least 90% covered with new solder coating.	Flux:Ethanol solution of rosin,25(wt)% includes activator equivalent to 0.06 to 0.10(wt)% chlorine Pre-Heating: 80 to 120°C 1minute Solder: Sn-3.0Ag-0.5Cu Solder Temperature: 245±3°C Immersion Time: 4±1 seconds Immersion and emersion rates: 25mm/s Stainless tweezers Please hold product except these part.
8.7	Resistance to Soldering Heat	Meet Table 1.	Flux: Ethanol solution of rosin,25(wt)% includes activator equipment to 0.06 to 0.10(wt)% chlorine Pre-Heating: 80 to 120°C, 1minute Solder: Sn-3.0Ag-0.5Cu Solder Temperature: 260±5°C Immersion Time: 5±0.5 seconds Immersion and emersion rates: 25mm/s Then measured after exposure in the room condition for 4 to 48 hours.



9. Environmental Performance(Products shall be soldered on the substrate.)

No.	Item	Specification	Test Method	
9.1	Temperature Cycle	Meet Table 1.	1 Cycle Step 1 -40°C(+0°C,-3°C) / 30±3 min Step 2 Ordinary Temp. / 10 to 15 minutes Step 3 +85°C(+3°C,-0°C) / 30±3 min Step 4 Ordinary Temp. / 10 to 15 minutes	
			Total of 100 cycles Then measured after exposure in the room condition for 4 to 48 hours	
9.2	Humidity		Temperature: 40±2°C Humidity: 90~95%(RH) Time: 1000(+48 hours,-0 hours) Then measured after exposure in the room condition for 4 to 48 hours.	
9.3	Heat life		Temperature: 85±2°C Applying Voltage: 2times for Rated Voltage Time: 1000(+48 hours,-0 hours) Then measured after exposure in the room condition for 4 to 48 hours. (ref.item 10)	
9.4	Cold Resistance		Temperature: -40± 2°C Time: 1000(+48 hours,-0 hours) Then measured after exposure in the room condition for 4 to 48 hours.	

10. Terminal to be Tested.

When measuring and supplying the voltage, the following terminal is applied.

No.	Item	Terminal to be Tested
10.1	Common Mode Impedance (Measurement Terminal)	Terminal • Terminal
10.2	Withstanding Voltage (Measurement Terminal)	Terminal O
10.3	DC Resistance (Measurement Terminal)	Terminal O Terminal
10.4	Insulation Resistance (Measurement Terminal)	Terminal O O
10.5	Heat Life(Supply Terminal)	Terminal O \$\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\

11. Measuring method for common mode impedance.

Measured common mode impedance may be included measurement error due to stray capacitance, residual inductance of test fixture.

To correct this error, the common mode impedance should be calculate as follows;

- (1) Measure admittance of the fixture(opened), Go Bo.
- (2) Measure impedance of the fixture(shorted), Rs Xs.
- (3) Measure admittance of the specimen, Gm Bm.
- (4) Calculate corrected impedance | Z | using the formula below.

$$|Z| = (Rx^{2}+Xx^{2})^{1/2}$$
Where
$$Rx = \frac{Gm-Go}{(Gm-Go)^{2} + (Bm-Bo)^{2}} - Rs$$


$$Xx = \frac{-(Bm-Bo)}{(Gm-Go)^{2} + (Bm-Bo)^{2}} - Xs$$



12. P.C.B., Flux, Solder and Soldering condition


Test shall be done using P.C.B., Flux, Solder and Soldering condition which are specified in item 16 except the case of being specified special condition.

13. Impedance Frequency Characteristics(Typical)



14. Specification of Packaging

14.1 Appearance and Dimensions (8mm-wide,Plastic tape)



14.2 Specification of Taping

- (1)Packing quantity(Standard quantity) 2000 pcs. / reel
- (2)Packing Method

Products shall be packaged in each embossed cavity of plastic tape and sealed with cover tape.

(3) Spliced point

The cover tape have no spliced point.

(4) Sprocket Hole

The sprocket holes are to the right as the tape is pulled toward the user.

(5)Missing components number


Missing components number within 0.025% of the number per reel or 1 pc., whichever is greater, and are not continuous. The specified quantity per reel is kept.

14.3 Pull Strength of Plastic Tape

Plastic Tape	5N min.
Cover Tape	10N min.


14.4 Peeling off force of Cover Tape

0.2 to 0.7N(Minimum value is Typical) Speed of Peeling off: 300 mm / min



Reference Only

14.5 Dimensions of Leader-tape, Trailer and Reel



14.6 Marking for reel

Customer part number, MURATA part number, Inspection number(*1), RoHS Marking(*2), Quantity, etc

*1) « Expression of Inspection No. »

 $\begin{array}{c|c} \square \square & OOOO & \times \times \times \\ \hline (1) & (2) & (3) \end{array}$

(1) Factory Code

(2) Date First digit : Year / Last digit of year

Second digit : Month / Jan. to Sep. \rightarrow 1 to 9, Oct. to Dec. \rightarrow O,N,D

Third, Fourth digit: Day

(3) Serial No.

*2) « Expression of RoHS Marking»

 $ROHS - \underline{Y}_{(1)}(\underline{\Delta})$


(1) RoHS regulation conformity parts.

(2) MURATĂ classification number

14.7 Marking for Outside package

Customer name Purchasing Order Number, Customer Part Number, MURATA part number, RoHS Marking(*2), Quantity, etc

14.8 Specification of Outer Case



Outer Case Dimensions (mm)			Standard Reel Quantity in Outer Case
W	D	Н	(Reel)
186	186	93	5


* Above Outer Case size is typical. It depends on a quantity of an order.

15. \triangle Caution

15.1 Mounting Direction

Mount products in right direction.

Wrong direction which is 90° rotated from right direction causes not only open or short circuit but also flames or other serious trouble.



wong direction

15.2 Limitation of Applications

Please contact us before using our products for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property.

- (1) Aircraft equipment
- (2) Aerospace equipment
- (3) Undersea equipment
- (4) Power plant control equipment
- (5) Medical equipment
- (6) Transportation equipment (vehicles, trains, ships, etc.)
- (7) Traffic signal equipment
- (8) Disaster prevention / crime prevention equipment
- (9) Data-processing equipment
- (10) Applications of similar complexity and / or reliability requirements to the applications listed in the above.



15.3 Corrosive gas

Please refrain from use since contact with environments with corrosive gases (sulfur gas [hydrogen sulfide, sulfur dioxide, etc.], chlorine, ammonia, etc.) or oils (cutting oil, silicone oil, etc.) that have come into contact with the previously stated corrosive gas environment will result in deterioration of product quality or an open from deterioration due to corrosion of product electrode, etc. We will not bear any responsibility for use under these environments.

16. Notice

Products can only be soldered with reflow.

This product is designed for solder mounting.

Please consult us in advance for applying other mounting method such as conductive adhesive.

16.1 Flux and Solder

Flux	K	Use rosin-based flux,(with converting chlorine content 0.06 to 0.1(wt)%.), but not highly acidic flux (with Halogen content exceeding 0.2(wt)% conversion to chlorine). Do not use water-soluble flux.
Sol	der	Use Sn-3.0Ag-0.5Cu solder

16.2 Assembling

<Exclusive use of Reflow soldering>

Flow soldering may cause deterioration in insulation resistance.

So, reflow soldering shall be applied for this product.

16.3 Cleaning Conditions

Do not clean after soldering. Some cleaning agents may degrade bonding strength, and characteristics of products by detaching. If cleaning, please contact us.


16.4 Resin coating

The impedance value may change due to high cure-stress of resin to be used for coating/molding products. An open circuit issue may occur by mechanical stress caused by the resin, amount/cured shape of resin, or operating condition etc. Some resin contains some impurities or chloride possible to generate chlorine by hydrolysis under some operating condition may cause corrosion of wire of coil, leading to open circuit. So, please pay your careful attention when you select resin in case of coating/molding the products with the resin. Prior to use the coating resin, please make sure no reliability issue is observed by evaluating products mounted


16.5 Attention regarding P.C.B. bending

The following shall be considered when designing and laying out P.C.B.'s.

(1) P.C.B. shall be designed so that products are not subject to the mechanical stress due to warping the board.



on your board.




Products shall be location the sideways Direction (Length : a<b) to the mechanical Stress.

(2)Components location on P.C.B. separation.

It is effective to implement the following measures, to reduce stress in separating the board. It is best to implement all of the following three measures; however, implement as many measures as

t is best to implement all of the following three measures; nowever, implement as many measures as possible to reduce stress.

Contents of Measures	Stress Level
(1) Turn the mounting direction of the component parallel to the board separation surface.	A > D*1
(2) Add slits in the board separation part.	A > B
(3) Keep the mounting position of the component away from the board separation surface.	A > C




*1 A > D is valid when stress is added vertically to the perforation as with Hand Separation.

If a Cutting Disc is used, stress will be diagonal to the PCB, therefore A > D is invalid.

Reference Only

(3) Mounting Components Near Screw Holes

When a component is mounted near a screw hole, it may be affected by the board deflection that occurs during the tightening of the screw. Mount the component in a position as far away from the screw holes as possible.



16.6 Attention Regarding P.C.B. Design

< The Arrangement of Products >

P.C.B. shall be designed so that products are far from the portion of perforation.

The portion of perforation shall be designed as narrow as possible, and shall be designed so as not to be applied the stress in the case of P.C.B. separation.

Products shall not be arranged on the line of a series of holes when there are big holes in P.C.B.

(Because the stress concentrate on the line of holes.)

< Products Placing >


Support pins shall be set under P.C.B. to prevent causing a warp to P.C.B. during placing the products on the other side of P.C.B.

< P.C.B. Separation >


P.C.B. shall not be separated with hand.


P.C.B. shall be separated with the fixture so as not to cause P.C.B. bending.

16.7 Standard Land Dimensions (Reflow)



- *1 If the pattern is made with wider than 1.2mm. It will result to let component turn around, because melting speed is different. In the worst case, short circuit between lines may be occured.
- *2 If the pattern is made with less than 0.4mm, in the worst case, short circuit between lines may be occurred due to the spread of soldering paste or mount placing accuracy.
- *3 If the pattern is made with wider than 0.8mm, the strength of bending will be reduced.
- *4 Do not use gilded pattern. A copper wire may cause open by dissolution of metallization.






SpecNo.JEFL243C-0015D-01

Reference Only

16.8 Standard Soldering Condition

- 1.Reflow Soldering
- (1)Standard printing pattern of solder paste
 - Standard thickness of the solder paste should be 100 to 150µm.
 - Use the solder paste printing pattern of the right pattern.
 - For the resist and copper foil pattern, use standard land dimensions.
 - Use the Solder Sn-3.0Ag-0.5Cu for pattern printing.
 - Spread of soldering paste between lines may cause short circuit of lines.




(2) Soldering Temperature

Temperature difference between soldering and surface of components must be within 150°C, in preheating. When components are immersed in liquid after soldering, temperature difference should be within 100°C. If preheating is not enough, components may be cracked and cause deterioration in insulation resistance.

(3) Soldering Condition

Standard soldering profile and the limit soldering profile is as follows.

The excessive limit soldering conditions may cause leaching of the electrode and / or resulting in the deterioration of product quality.



	Standard Profile	Limit Profile
Pre-heating	150~180°C 、90s±30s	
Heating	above 220°C、30s∼60s	above 230°C、60s max.
Peak temperature	245±3°C	260°C、10s
Cycle of reflow	2 times	2 times

2. Reworking with Soldering iron

The following conditions must be strictly followed when using a soldering iron after being mounted by reflow soldering.

· Pre-heating: 150°C, 1 min · Soldering iron output: 30W max.

· Tip temperature: 350°C max. · Tip diameter:φ3mm max.

 \cdot Soldering time : 3(+1,-0) seconds. \cdot Times : 2times max.


Notes: Do not touch the products directly with the soldering iron.

SpecNo.JEFL243C-0015D-01

Reference Only

3. Solder Volume


Solder shall be used not to be exceeded the upper limits as shown below.



Accordingly increasing the solder volume, the mechanical stress to Chip is also increased. Exceeding solder volume may cause the failure of mechanical or electrical performance.

16.9 Caution for use


- •When you hold products with a tweezer, please hold like a figure of the right side, and sharp material, such as a pair of tweezers, shall not be touched to the winding portion to prevent the breaking of wire.
- Mechanical shock should not be applied to the products mounted on the board to prevent the breaking of the core.



16.10 Handling of a substrate

After mounting products on a substrate, do not apply any stress to the product caused by bending or twisting to the substrate when cropping the substrate, inserting and removing a connector from the substrate or tightening screw to the substrate.

Excessive mechanical stress may cause cracking in the product.



16.11 Brushing of neighborhood of products

When you clean the neighborhood of products such as connector pins, bristles of cleaning brush shall not be touched to the winding portion to prevent the breaking of wire.

16.12 Operating Environment

Do not use this product under the following environmental conditions, on deterioration of the performance, such as insulation resistance may result from the use.

- (1) in corrosive gases (acidic gases, alkaline gases, chlorine, sulfur gases, organic gases and etc.)
- (2) in the atmosphere where liquid such as organic solvent, may splash on the products.

16.13 Storage Condition

(1) Storage period

Use the products within 12 months after delivered.

Solderability should be checked if this period is exceeded.

(2) Storage environment conditions

Products should be stored in the warehouse on the following conditions.

Temperature : $-10 \sim +40$ °C

Humidity : 15 to 85% relative humidity No rapid change on temperature and humidity.

· Products should not be stored in corrosive gases, such as sulfureous, acid gases, alkaline gases, to prevent the following deterioration.

Poor solderability due to the oxidized electrode.

- · Products should be stored on the palette for the prevention of the influence from humidity,dust and so on.
- Products should be stored in the warehouse without heat shock, vibration, direct sunlight and so on.
- · Avoid storing the product by itself bare (i.e.exposed directly to air).

(3) Delivery

Care should be taken when transporting or handling product to avoid excessive vibration or mechanical shock.

17. **△** Note

- (1)Please make sure that your product has been evaluated in view of your specifications with our product being mounted to your product.
- (2)You are requested not to use our product deviating from the reference specifications.
- (3)The contents of this reference specification are subject to change without advance notice. Please approve our product specifications or transact the approval sheet for product specifications before ordering.