

GRT0335C1H2R0CA02#

“#” at the end indicates the package specification code.



< List of part numbers with package codes >

GRT0335C1H2R0CA02D

GRT0335C1H2R0CA02W

GRT0335C1H2R0CA02J

GRT0335C1H2R0CA02V

Applications

Unsuitable Applications	Please be sure to read and comply with these "Precautions for use."
Specific Applications	Automotive infotainment/comfort equipment, Industrial Equipment, Medical equipment [GHTF A/B/C] except for implant equipment Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product.

Notices

Derating1

Appearance & Shape



References

Packaging	Specifications	Standard Packing Quantity
D	φ180mm Reel Paper Tape	15000
W	φ180mm Reel W8P1 Paper Tape	30000
J	φ330mm Reel Paper Tape	50000
V	φ330mm Reel W8P1 Paper Tape	150000

Mass (typ.)	
1 piece	0.33mg

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

GRT0335C1H2R0CA02#

“#” at the end indicates the package specification code.



Specifications

Length	0.6±0.03mm
Width	0.3±0.03mm
Thickness	0.3±0.03mm
Capacitance	2.0pF ±0.25pF
Distance between external terminals g	0.2mm min.
External terminal size e	0.1 to 0.2mm
Operating Temperature Range	-55°C to 125°C
Rated Voltage	50Vdc
Size code in inch(mm)	0201 (0603M)
TC	0±30ppm/°C
Temperature characteristics (complied standard)	C0G(EIA)
Temperature range of temperature characteristics	25°C to 125°C

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.


GRT0335C1H2R0CA02#

“#” at the end indicates the package specification code.




Characteristic Data

The charts below may show another part number which shares its characteristics.



GRT0335C1H2R0CA02 |Z| DCOV, 25degC



GRT0335C1H2R0CA02 R DCOV, 25degC



GRT0335C1H2R0CA02 C-DC bias capchange, 25.0c



GRT0335C1H2R0CA02 C-AC Voltage capchange, Dc

Attention


1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

GRT0335C1H2R0CA02#

“#” at the end indicates the package specification code.



Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.