

PVG3A105C01B00

Discontinued

RoHS

REACH

Appearance & Shape



Features

1. Sealed construction protects the interior from dust and liquid, which achieves stable performance.
2. Driver plate with cross-slot is suitable for automatic adjustment.
3. Rotor with large diameter and deep groove improves driver insertion.
4. 3mm and 4mm land pattern can be used without change.
(Gull-wing is suitable for 4mm size land pattern.)

Packaging Information

| Packaging | Specifications | Standard Packing Quantity |
|-----------|----------------|---------------------------|
| B00 | Bulk(Bag) | 500 |

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

PVG3A105C01B00



Specifications

| | |
|--|--|
| Power Rating | 0.25W |
| Shape | SMD |
| Maximum Working Voltage | 200Vdc |
| Adjustment Direction | Top |
| Size | 3mm |
| Auto Adjustment | Yes |
| Number of Turns (Effective Rotation Angle) | 1(210°±10°) |
| Mechanical Rotation Angle | 250+/-10 deg. |
| Total Resistance Value | 1MΩ |
| Total Resistance Value Tolerance | ±20% |
| Temperature Coefficient of Resistance | ±150ppm/°C |
| Resistance Taper | B(Linear) |
| Contact Resistance Variation | 2% of standard total resistance or 3ohm max., whichever is greater |
| Residual Resistance | 1% of standard total resistance or 2ohm max., whichever is greater |
| Torque | 4.9mN · m max. |
| Measure Condition of RatedPower | 70°C |
| Operating Temperature Range | -55°C to 125°C |
| Mass | 0.06g |

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

PVG3A105C01B00



Product Data



Constructions

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.