

RHE5G2A122J0A2H03B

In Production

AEC-Q200

RoHS

REACH

150 °C max.

Low acoustic noise

Deflecting crack

Soldering crack

Flow OK

Welding

Applications

| | |
|-------------------------|--|
| Unsuitable Applications | Please be sure to read and comply with these "Precautions for use." |
| Specific Applications | Automotive powertrain/safety equipment, Automotive infotainment/comfort equipment, Medical equipment [GHTE A/B/C] except for implant equipment Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product. |

Notices

HF(Halogen Free)

Appearance & Shape



References

| Packaging | Specifications | Standard Packing Quantity |
|-----------|----------------|---------------------------|
| B | Bulk(Bag) | 500 |

| Mass (typ.) | |
|-------------|------|
| 1 piece | 0.1g |

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

RHE5G2A122J0A2H03B



Specifications

| | |
|--|--|
| L size or Outer diameter D | 3.6mm max. |
| Width | 3.5mm max. |
| T size | 2.5mm max. |
| Lead spacing F | 2.5±0.8mm |
| Lead diameter d | 0.5±0.05mm |
| Paint dripping e | 1.5mm max. |
| Capacitance | 1200pF ±5% |
| Rated voltage | 100Vdc |
| Temperature characteristics | X8G(MURATA) |
| Temperature range of temperature characteristics | -55°C to 150°C |
| Operating Temperature Range | -55°C to 150°C |
| TC | 25 to 150°C: 0±30ppm/°C -55 to 25°C: 0+30/-72ppm/°C |

Attention


- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

RHE5G2A122J0A2H03B




Characteristic Data


The charts below may show another part number which shares its characteristics.




RHE5G2A122J0A2H03B |Z| DCOV, 25degC



RHE5G2A122J0A2H03B R DCOV, 25degC



RHE5G2A122J0A2H03B C-DC bias capchange, 25.0





RHE5G2A122J0A2H03B C-AC Voltage capchange, 1

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

RHE5G2A122J0A2H03B



Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.